



## CURRENCY

Source: <http://www.etn.com/home/freeng/currency.html>

Eaton Global Standardization - CURRENCY

Based on Reuter's Worldwide Standards

### A

Afghanistan Afghni	AFA
Albanian Lek	ALL
Algerian Dinar	DZD
Andorran Franc	ADF
Andorran Peseta	ADP
Angolan New Kwanza	AON
Argentine Peso	ARS
Aruba Florin	AWG
Australian Dollar	AUD
Austrian Schilling	ATS

### B

Bahamian Dollar	BSD
Bahraini Dinar	BHD
Bangladesh Taka	BDT
Barbados Dollar	BBD
Belgian Franc	BEF
Belarussian Rouble	BYR
Belize Dollar	BZD
Bermuda Dollar	BMD
Bhutan Ngultrum	BTN
Botswana Pula	BWP
Bolivian Boliviano	BOB
Brunei Dollar	BND
Brazilian Real	BRL
British Pound	GBP
Bulgarian Lev	BGL
Burundi Franc	BIF

### C

Cambodia Riel	KHR
Canadian Dollar	CAD
Cape Verde Escudo	CVE
Cayman Islands Dollar	KYD
CFA Franc	XAF
CFA Franc	XOF
Chilean Peso	CLP
Chinese Renminbi	CNY
Colombian Peso	COP
Comoro Franc	KMF
Costa Rica Colon	CRC
Croatian Kuna	HRK
Cuban Peso	CUP
Cyprus Pound	CYP

Czech Koruna CZK

D

Danish Krone DKK

Djibouti Franc DJF

Dominican Peso DOP

Dutch Guilder NLG

E

Ecuadorian Sucre ECS

Egyptian Pound EGP

El Salvador Colon SVC

Estonian Kroon EEK

Ethiopian Birr ETB

European Currency Unit ECU

Euro EUR

F

Falkland Islands Pound FKP

Fiji Dollar FJD

Finnish Mark FIM

French Franc FRF

G

Gambian Dalasi GMD

German Mark DEM

Ghanian Cedi GHC

Gibraltar Pound GIP

Greek Drachma GRD

Gold XAU

Guatemala Quetzal GTQ

Guinea-Bissau Peso GWP

Guinea Franc GNF

Guyana Dollar GYD

H

Haiti Gourde HTG

Honduras Lempira HNL

Hong Kong Dollar HKD

Hungarian Forint HUF

I

Iceland Krona ISK

Indian Rupee INR

Indonesian Rupiah IDR

Iranian Rial IRR

Iraqi Dinar IQD

Irish Punt IEP

Israeli Shekel ILS

Italian Lira ITL

J

Jamaican Dollar	JMD
Japanese Yen	JPY
Jordanian Dinar	JOD

#### K

Kazakhstan Tenge	KZT
Kenyan Shilling	KES
Korean Won	KRW
Kuwaiti Dinar	KWD

#### L

Lao Kip	LAK
Latvian Lat	LVL
Lebanese Pound	LBP
Lesotho Loti	LSL
Liberian Dollar	LRD
Lithuanian Lita	LTL
Luxembourg Franc	LUF
Lybian Dollar	LYD

#### M

Macau Pataca	MOP
Malagasy Franc	MGF
Malaysian Ringgit	MYR
Malawi Kwacha	MWK
Maldives Rufiyaa	MVR
Maltese Lira	MTL
Mauritania Ougulya	MRO
Mauritius Rupee	MUR
Mexican Nuevo Peso	MXN
Molodovan Leu	MDL
Mongolian Tugrik	MNT
Moroccan Dirham	MAD
Mozambique Metical	MZM
Myanmar Kyat	MMK

#### N

Namibian Dollar	NAD
Nepalese Rupee	NPR
Neth. Antilles Guilder	ANG
New Zealand Dollar	NZD
Nicaragua Cordoba	NIO
Nigerian Naira	NGN
North Korean Won	KPW
Norwegian Krone	NOK

#### O

Omani Rial	OMR
------------	-----

#### P

Pakistani Rupee	PKR
Palladium	XPD

Panama Balboa	PAB
Papua New Guinea Kina	PGK
Paraguayan Guarani	PYG
Peruvian Nuevo Sol	PEN
Philippine Peso	PHP
Platinum	XPT
Polish Zloty	PLN
Portuguese Escudo	PTE

## Q

Qatar Rial	QAR
------------	-----

## R

Romanian Leu	ROL
Russian Rouble	RUR
Russian Rouble Mkt. Rate	RURM

## S

Samoa Tala	WST
Sao Tome Dobra	STD
Saudi Arabian Riyal	SAR
Seychelles Rupee	SCR
Silver	ZAG
Sierra Leone Leone	SLL
Singapore Dollar	SGD
Slovak Koruna	SKK
Slovenian Tolar	SIT
Solomon Islands Dollar	SBD
Somali Shilling	SOS
South African Rand	ZAR
Spanish Peseta	ESP
Sri Lanka Rupee	LKR
St. Helena Pound	SHP
Sudanese Dinar	SDD
Sudanese Pound	SDP
Surinam Guilder	SRG
Swaziland Lilageni	SZL
Swedish Krona	SEK
Swiss Franc	CHF
Syrian Pound	SYP

## T

Taiwan Dollar	TWD
Tanzanian Shilling	TZS
Turkish Lira	TRL
Thai Baht	THB
Tonga Pa'anga	TOP
Trinidad & Tobago Dollar	TTD
Tunisian Dinar	TND
Turkish Lira	TRL

## U

UAE Dirham	AED
Ugandan Shilling	UGX
Ukraine Hryvnia	UAH
Uruguayan New Peso	UYU
United States Dollar	USD
Uzbekistan Sum	UZS

V

Vanuatu Vatu	VUV
Venezuelan Bolivar	VEB
Vietnam Dong	VND

W

X

Y

Yugoslav Dinar	YUN
----------------	-----

Z

Zaire New Zaire	ZRN
Zambian Kwacha	ZMK
Zimbabwe Dollar	ZWD