



# Weatherhead

## Weatherhead Crimp Specifications for Synflex hose

### WEATHERHEAD ET1000/T-420/T-480 CRIMP SPECIFICATIONS

Hose	Size	Hose Ends	Collet P/N	Spacer Ring Color	Spacer Ring P/N	Flat Side (Up/Down)	Crimp Diameter (+/- .005in)	Crimp Length (+/- .031in)
30CT	-03	903	ET1000DC-M095S	Light Green	ET1000SR-M190D	Up	0.478	0.813
30CT	-04	903	T-400-2C	Tan	T-400-112	Up	0.543	0.937
30CT	-05	903	ET400DC-M150S	Black	T-400-10	Down	0.630	0.875
30CT	-06	903	ET400DC-M150S	Light Green	ET1000SR-M190D	Up	0.675	1.125
30CT	-08	903	T-400-123C	Black/Tan	T-400-46R	Up	0.855	1.312
3130	-03	903	ET1000DC-M095S	Light Green	ET1000SR-M190D	Up	0.470	0.812
3130	-04	903	T-400-2C	Black	T-400-10	Down	0.555	0.937
3130	-05	903	ET400DC-M150S	Black	T-400-10	Down	0.630	0.875
3130	-06	903	ET400DC-M150S	Light Green	ET1000SR-M190D	Up	0.675	1.125
3130	-08	903	T-400-123C	Purple	ET1000SR-M100A	Up	0.825	1.063
3130 *	-12	903	T-420-85C	Brown	ET420SR-M495A	Up	1.080	1.375
3580	-04	903	T-400-2C	Black	T-400-10	Down	0.548	0.937
3580	-06	903	ET400DC-M150S	Silver	T-400-11	Up	0.707	1.125
3580	-08	903	T-400-123C	Purple	ET1000SR-M100A	Up	0.825	1.063
3580 *	-12	903	T-420-85C	Brown	ET420SR-M495A	Up	1.080	1.375
3R80	-03	90H	T-400-2C	Green	T-400-37	Up	0.516	0.750
3R80	-04	90H	ET400DC-M150S	Yellow	T-400-62	Up	0.655	0.937
3R30	-03	903	ET1000DC-M095S	Black/Tan	T-400-46R	Up	0.441	0.812
3R30	-04	903	T-400-2C	Tan	T-400-112	Up	0.543	0.937
3R30	-06	903	ET400DC-M150S	Light Green	ET1000SR-M190D	Up	0.665	1.125
3R30	-08	903	T-400-123C	Purple	ET1000SR-M100A	Up	0.825	1.063
37AL	-03	903	ET1000DC-M095S	Light Green	ET1000SR-M190D	Up	0.478	0.812
37AL	-04	903	T-400-2C	Tan	T-400-112	Up	0.543	0.937
37AL	-05	903	ET400DC-M150S	Black	T-400-10	Down	0.630	0.875
37AL	-06	903	ET400DC-M150S	Light Green	ET1000SR-M190D	Up	0.675	1.125
37AL	-08	903	T-400-123C	Purple	ET1000SR-M100A	Up	0.825	1.063
3750	-08	903	T-400-123C	Purple	ET1000SR-M100A	Up	0.825	1.063
3800	-03	903	ET1000DC-M095S	Light Green	ET1000SR-M190D	Up	0.478	0.812
3800	-04	903	T-400-121C	Magenta	ET1000SR-M215A	Up	0.568	0.937
3800	-06	903	ET400DC-M150S	Light Green	ET1000SR-M190D	Up	0.675	1.125
3800	-08	903	T-400-41C	Yellow	T-410-41	Up	0.840	1.187
3740	-04	903	T-400-2C	Black	T-400-10	Down	0.555	0.937
3740	-06	903	ET400DC-M150S	Light Green	ET1000SR-M190D	Up	0.675	1.125

\* -12 hose cannot be crimped with the ET1000 crimper

**Eaton**  
14615 Lone Oak Road  
Eden Prairie, MN 55344  
USA  
Tel: 952 937-9800  
Fax: 952 974-7722  
[www.hydraulics.eaton.com](http://www.hydraulics.eaton.com)

**Eaton**  
115 Lena Dr.  
Aurora, OH 44202  
USA  
Tel: (330) 274-3171  
Toll-Free: (800) 837-1467  
Fax: (330) 274-0473

© 2006 Eaton Corporation  
All Rights Reserved  
Printed in USA  
Document No. W-EQCR-TM018-E  
March 2007



**Weatherhead**