



CHALLENGER CROSS TO CUTLER-HAMMER BREAKERS

TD01201041E

CHALLENGER	C-H TYPE	CHALLENGER	C-H TYPE	CHALLENGER	C-H TYPE
12CSN	12NC	CK	HMCP-400	CSMDCGA	MDSCGA
1CKE	1KS	CKC	CKD	CSMDY	MDSY
1CLS	1LC	CKE	KS	CSMY	MCY
20CSP	20PC	CKES	KES	CSN	NC
25CSP	25PC	CKH	HKD	CSNY	NCY
2CKE	2KS	CKHC	CHKD	CSP	PC
30CSP	30PC	CKS	KDB	CSPC	PCC
3CLS	3LC	CKT	KT	CTB	FB-P
4CKE	4KS	CKV	KDC	CTL	LA-P
5CLS	4LC	CKVC	CHKDC	CTN	NB-P
6CLE	6LS	CL	LD	CTP	PB-P
6CLS	6LC	CL	HMCP-600	CXF	FCL
BQ	BAB	CLC	LDC	CXL	LCL
C	BR	CLE	LS	CXLG	LCLG
CB	CC	CLES	LES	HAGFHEP	QPGFEP
CBB	BAB	CLH	HLH	HCLL115	QCHW
CBBGF	QBGF	CLHC	CHLD	VCLL	QHCX
CBBGFEP	QBGFEP	CNH	HND		
CBBH	QBHW	CNHC	CHND	BQ	BAB
CBBHGF	QBHGF	CNV	NDC	QBH	CH
CBBHGFEP	QBHGFEP	CNVC	CNDC	COMMANDER CANADA	
CBBHW	QBHW-H	CQ	BQ	CMH	CSR
CBJ	BJ	CR	RD	CM	BW
CBJH	BJH	CRC	CRD		
CD	CA	CRE	RS		
CDH	CAH	CRV	RDC		
CDK	DK	CRVC	CRDC		
CDT	HCA	CSHL	HLC		
CE	EHD	CSHLA	HLCA		
CED	ED	CSHLC	HLCC		
CEH	EDH	CSHLC	HLCC		
CEV	EDC	CSHLG	HLCG		
CF	FD	CSHM	HMC		
CF	HMCP-150	CSHMC	HMCC		
CFH	HFD	CSHN	HNC		
CFS	FDB	CSL	LC		
CFV	FDC	CSLA	LCA		
CG	GB	CSLC	LCC		
CGL	GC	CSLCG	LCCG		
CH	GHB	CSLG	LCG		
CH(CANADIAN)	QBH	CSLGA	LCGA		
CHL	GHC	CSLY	LCY		
CJ	HMCP-250	CSLYG	LCYG		
CJ	JD	CSLYGA	LCYGA		
CJH	HJD	CSM	MC		
CJS	JDB	CSMC	MCC		
CJT	JT	CSMD	MDS		
CJV	JDC	CSMDC	MDSC		
CK	KD	CSMDCA	MDSCA		

REFER TO SA01211001E FOR CUTLER-HAMMER / WESTINGHOUSE PREFIXES