



Eaton

RT2SSEO200WLS3HIPB

Eaton Roundtech Medium Surface Safety
EFOCUS WLS 200 MNM 3H IP65 Black

Allgemeine Spezifikation

PRODUCT NAME	Eaton RoundTech MSSEO surface emergency luminaire
CATALOG NUMBER	RT2SSEO200WLS3HIPB
EAN	3660191823337
PRODUCT LENGTH/DEPTH	138 mm
PRODUCT HEIGHT	48 mm
PRODUCT WIDTH	138 mm
PRODUCT WEIGHT	0.295 kg
CERTIFICATIONS	CE
PRODUCT TYPE	Surface emergency luminaire

Produktspezifikationen

BATTERY QUALITY	Lithium-ion
PROTECTION CLASS	II
DEGREE OF PROTECTION	IP65
LAMP TYPE	LED not exchangeable
WITH LIGHT SOURCE	Yes
LAMP HOLDER	None
MONITORING EQUIPMENT	Safety module for monitoring (central feeded system)
POWER SUPPLY SYSTEM	Peripheral (individual battery)
VOLTAGE TYPE	AC
POWER FACTOR	0.61
WITH REMOTE SWITCH CONNECTION	No
ENERGY EFFICIENCY CLASS	A
CONNECTION TYPE	Plug-in connection
MAX. SYSTEM POWER	1.1 W
TYPE OF CONTROL GEAR	LED operating device current-controlled
TYPE OF WIRING	Suitable for through wiring
NOMINAL VOLTAGE AC - MAX	230 V
NOMINAL VOLTAGE AC - MIN	230 V
NOMINAL OPERATION TIME - MIN	3 hour
NOMINAL OPERATION TIME - MAX	3 hour
SUITABLE FOR STANDBY SWITCHING	No
SUITABLE FOR CONTINUOUS CIRCUIT	No
RAL-NUMBER (SIMILAR) HOUSING	9005
MOUNTING METHOD	Ceiling surface mounting
MATERIAL HOUSING	Plastic
COLOR HOUSING	Black
MATERIAL COVER	Without cover
PICTOGRAM INCLUDED	No
NUMBER OF POLES (NUMERIC)	3
IMPACT STRENGTH	IK04
RATED LUMINOUS FLUX	200 lm

Downloads

ACC. IEC 62722-2-1	
COLOR TEMPERATURE - MAX	5700 K
COLOR TEMPERATURE - MIN	5700 K
LIGHT DISTRIBUTOR	Focal lens
FUNCTION	Escape route lighting
LUMINAIRE WITH LIMITED SURFACE TEMPERATURE, SIGN D	No
LUMINOUS FLUX IN STANDBY MODE	60 lm
NUMBER OF LIGHTING HEADS	1
PRODUCT BRANDING	Eaton
WITH REMOTE CONTROL	No
CONSTANT LIGHT OUTPUT (CLO)	No
EXCHANGEABLE CONTROL GEAR	No

PROJEKTNAME:
PROJEKTNUMMER:
ERSTELLT VON:
DATUM:



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Irland
Eaton.com

© 2026 Eaton. Alle Rechte vorbehalten.

Folgen Sie uns in den sozialen Netzwerken und erhalten Sie aktuelle Produkt- und Supportinformationen.

