

Spécifications



La photo est représentative



Eaton HC9-4R3-R

Eaton HC9 inductor, 4.67 μ H, 13 A Irms, 19.1 A ISAT, 5.9 m Ω resistance, SMT mounting, Iron Powder, 2-pins, 450 qty.

Spécifications générales

PRODUCT NAME	Eaton HC9 inductor
CATALOG NUMBER	HC9-4R3-R
UPC	051712824002
PRODUCT LENGTH/DEPTH	0.555 in
PRODUCT HEIGHT	0.295 in
PRODUCT WIDTH	0.516 in
PRODUCT WEIGHT	0.013 lb
COMPLIANCES	RoHS Compliant



Powering Business Worldwide

Spécifications du produit

TYPE	Inductor
MOUNTING	SMT
IRMS	13 A
ISAT	19.1 A
PACKAGE QUANTITY	450
MATERIAL	Iron powder
FREQUENCY RATING	1 kHz to 500 kHz
CONTACT CONFIGURATION	Two-pin
TEMPERATURE RATING	-40 to 155 °C
RESISTANCE	5.9 mΩ
SERIES	HC9

Ressources

NOM DU PROJET:

NUMÉRO DU PROJET:

PRÉPARÉ PAR:

DATE:



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Irlande
Eaton.com

© 2026 Eaton. Tous droits réservés.

Suivez-nous sur les réseaux sociaux
pour connaître les dernières
informations concernant nos
produits.

