

Spécifications



Eaton KTK-R-4

Eaton Bussmann Series Class CC fuse, KTK-R, fast-acting, dual-element current limiting fuse, 4 A, rejection style fuse, interrupting rating of 200kA at 600Vac

Spécifications générales

PRODUCT NAME	Eaton Bussmann series KTK-R fuse
CATALOG NUMBER	KTK-R-4
EAN	5027590445672
UPC	051712420631
PRODUCT LENGTH/DEPTH	1.5 in
PRODUCT HEIGHT	0.41 in
PRODUCT WIDTH	0.41 in
PRODUCT WEIGHT	0.015 lb
COMPLIANCES	CE Marked
CERTIFICATIONS	UL Listed CSA Certified

Spécifications du produit

AMPERAGE RATING	4 A
NUMBER OF ELEMENTS	Dual
CLASS	Class CC
INTERRUPT RATING	200 kAIC
FUSE INDICATOR	Non-indicating
CONNECTION	Ferrule end x ferrule end Ferrule
RESPONSE TIME	See time current curve
MATERIAL	Melamine tube
PACKAGING TYPE	Standard
QUANTITY	10
VOLTAGE RATING	600 V
TYPE	Current-limiting fast-acting fuse
SPECIAL FEATURES	Rejection style
APPLICATION	Industrial controls panels and machinery, street lighting, general lighting, capacitors and distribution

Ressources

PEP ECO-PASSPORT	eaton-class-midget-fuses-pep-eato-00333-v0101-en.pdf
SCHÉMAS	DA-PD-Bus_Ele_DS_1015_KTK-R

NOM DU PROJET:

NUMÉRO DU PROJET:

PRÉPARÉ PAR:

DATE:



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Irlande
Eaton.com

© 2026 Eaton. Tous droits réservés.

Suivez-nous sur les réseaux sociaux
pour connaître les dernières
informations concernant nos
produits.

