

Specificaties



Eaton FNQ-R-1/2

Eaton Bussmann Series Class CC fuse, FNQ, time-delay, dual-element current limiting fuse, 0.5 A, rejection style fuse, interrupting rating of 200kA at 600Vac

Algemene specificaties

PRODUCT NAME	Eaton Bussmann series FNQ-R fuse
CATALOG NUMBER	FNQ-R-1/2
UPC	051712147019
PRODUCT LENGTH/DEPTH	1.5 in
PRODUCT HEIGHT	0.41 in
PRODUCT WIDTH	0.41 in
PRODUCT WEIGHT	0.15 lb
COMPLIANCES	CE Marked



Powering Business Worldwide

Productspecificaties

AMPERAGE RATING	0.5 A
CLASS	Class CC
INTERRUPT RATING	200 kAIC
FUSE INDICATOR	Non-indicating
CONNECTION	Ferrule end x ferrule end
RESPONSE TIME	12 sec at 200%
MATERIAL	Melamine tube
PACKAGING TYPE	Standard
VOLTAGE RATING	600 V
TYPE	Current-limiting high inrush time-delay fuse
SPECIAL FEATURES	Rejection style
APPLICATION	Line protection, small control transformers, industrial control, branch circuits

Documentatie

PROJECTNAAM:

PROJECTNUMMER:

BEREID DOOR:

DATUM:



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ierland
Eaton.com

© 2026 Eaton. Alle rechten voorbehouden.

Volg ons op sociale media om de laatste product- en ondersteuningsinformatie te ontvangen.

