

Especificações



A foto é representativa



Eaton FNQ-R-6-1/4

Eaton Bussmann Series Class CC fuse, FNQ, time-delay, dual-element current limiting fuse, 6.25 A, rejection style fuse, interrupting rating of 200kA at 600Vac

Especificações gerais

PRODUCT NAME	Eaton Bussmann series FNQ-R fuse
CATALOG NUMBER	FNQ-R-6-1/4
UPC	051712497015
EAN	5027590449793
PRODUCT LENGTH/DEPTH	1.5 in
PRODUCT HEIGHT	0.41 in
PRODUCT WIDTH	0.41 in
PRODUCT WEIGHT	0.015 lb
COMPLIANCES	CE Marked



Powering Business Worldwide

Especificações do produto

AMPERAGE RATING	6.25A
CLASS	Class CC
INTERRUPT RATING	200 kAIC
FUSE INDICATOR	Non-indicating
CONNECTION	Ferrule end x ferrule end
RESPONSE TIME	12 sec at 200%
MATERIAL	Melamine tube
PACKAGING TYPE	Standard
VOLTAGE RATING	600 V
TYPE	Current-limiting high inrush time-delay fuse
SPECIAL FEATURES	Rejection style
APPLICATION	Line protection, small control transformers, industrial control, branch circuits

Recursos

NOME DO PROJETO:

NÚMERO DO PROJETO:

PREPARADO POR:

DATA:



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Irlanda
Eaton.com

© 2026 Eaton. Todos os direitos reservados.

Siga-nos nas redes sociais para receber informações sobre suporte e os produtos mais recentes.

