

Especificações



A foto é representativa



Eaton FRN-R-25ID

Eaton Bussmann Series Class RK5 fuse, FRN-R, time-delay, dual-element, current limiting fuse, 25 A, indicating fuse, interrupting rating of 200 kA at 250 Vac and 20 kA at 125 Vdc

Especificações gerais

PRODUCT NAME	Eaton Bussmann series FRN-R fuse
CATALOG NUMBER	FRN-R-25ID
UPC	051712204415
PRODUCT LENGTH/DEPTH	2 in
PRODUCT HEIGHT	0.56 in
PRODUCT WIDTH	0.56 in
PRODUCT WEIGHT	0.5 lb
COMPLIANCES	CE Marked



Powering Business Worldwide

Especificações do produto

AMPERAGE RATING	25 A
NUMBER OF ELEMENTS	Dual
CLASS	Class RK5
INTERRUPT RATING	200 kAIC at 250 Vac 20 kAIC at 125 Vdc
FUSE INDICATOR	Non-indicating With Indicator
CONNECTION	Ferrule end x ferrule end
RESPONSE TIME	8 sec at 500%
PACKAGING TYPE	Standard
VOLTAGE RATING	250 Vac, 125 Vdc
TYPE	Current-limiting time-delay fuse
SPECIAL FEATURES	Finger safe, power loss 11.50 w
APPLICATION	Combination starters, motor control centers, machinery disconnects, power panelboards

Recursos

NOME DO PROJETO:

NÚMERO DO PROJETO:

PREPARADO POR:

DATA:



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Irlanda
Eaton.com

© 2026 Eaton. Todos os direitos reservados.

Siga-nos nas redes sociais para
receber informações sobre suporte e
os produtos mais recentes.

