

Caractéristiques



Eaton FH52

Eaton A200/B100 heater, Used with Starter Sizes 1, and 2, A200/B100 Heater, NEMA, Ambient 26.3-28.7, 30.4-33.3A, Non-Comp 24.4-26.6, 28.9-31.4A, Used with Starter Sizes 1, and 2, Type A and B, Thermal and Fast Trip

Spécifications générales

PRODUCT NAME	Eaton A200/B100 heater
CATALOG NUMBER	FH52
UPC	786678670423
PRODUCT LENGTH/DEPTH	0.21 in
PRODUCT HEIGHT	0.8 in
PRODUCT WIDTH	1.3 in
PRODUCT WEIGHT	0.03 lb
CERTIFICATIONS	UL Listed CSA Certified
CATALOG NOTES	Select heater coils based on full load current(FLA) shown on motor nameplate. Heater coils are rated to protect 40 degree C rise and a service factor of 1.15, Single-Phase requires 2 heaters, Three-Phase Requires 3 heaters.

Caractéristiques du produit

SPECIAL FEATURES	Used with Starter Sizes 1, and 2
TYPE	A200/B100 Heater
USED WITH	Used with Starter Sizes 1, and 2
DESIGN	NEMA
FULL LOAD CURRENT RANGE	Ambient 26.3-28.7, 30.4-33.3 A, Non-Comp 24.4-26.6, 28.9-31.4 A
OVERLOAD RELAY	Type A and B
TRIP TYPE	Thermal and fast trip

Ressources

CARACTÉRISTIQUES	Eaton Specification Sheet - FH52
INSTRUCTIONS D'INSTALLATION	Instructions for A200, A210, A250 size 6, two- or three-pole non-reversing or reversing motor controllers

NOM DU PROJET:

NUMÉRO DE PROJET:

PRÉPARÉ PAR:

DATE:



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Irlande
Eaton.com

© 2026 Eaton. Tous droits réservés.

Suivez-nous sur les médias sociaux pour nos plus récentes nouveautés.

