



Foto ist repräsentativ



Eaton KTK-R-3/10

Eaton Bussmann Series Class CC fuse, KTK-R, Fast-acting, Dual-Element Current Limiting Fuse, 0.3 A, rejection style fuse, interrupting rating of 200kA at 600Vac

General Specifications

PRODUCT NAME	Eaton Bussmann series KTK-R fuse
CATALOG NUMBER	KTK-R-3/10
EAN	5027590092296
UPC	051712420556
PRODUCT LENGTH/DEPTH	1.5 in
PRODUCT HEIGHT	0.41 in
PRODUCT WIDTH	0.41 in
PRODUCT WEIGHT	0.015 lb
COMPLIANCES	CE Marked
CERTIFICATIONS	UL Listed CSA Certified

Elektrische Nennwerte

AMPERAGE RATING	0.3 A
INTERRUPT RATING	200 kAIC
VOLTAGE RATING	600 V

Geräteangaben

MATERIAL	Melamine tube
PACKAGING TYPE	Standard
TYPE	Current-limiting fast-acting fuse

Allgemeine Informationen

APPLICATION	Industrial controls panels and machinery, street lighting, general lighting, capacitors and distribution
CLASS	Class CC
CONNECTION	Ferrule end x ferrule end Ferrule
QUANTITY	10
SPECIAL FEATURES	Rejection style

Downloads

PEP ECO-PASSPORT	eaton-class-midget-fuses-pep-eato-00333-v0101-en.pdf
------------------	--

PROJEKTNAME:

PROJEKTNUMMER:

ERSTELLT VON:

DATUM:



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Irland
Eaton.com

© 2026 Eaton. Alle Rechte vorbehalten.

Folgen Sie uns in den sozialen Netzwerken und erhalten Sie aktuelle Produkt- und Supportinformationen.

