

Eaton Residential Product Line



3/4" CH Breakers

- 1, 2, 3 pole breakers
- 10kAIC @ 120/240V
- HACR rated
- Trip flag
- Auto reset
- Lifetime warranty



1" BR Breakers

- 1, 2, 3 pole breakers
- 10, 22, or 42kAIC
- HACR rated
- 10 year warranty



Arc Fault Breakers

- Standard LED indicates one of seven trip codes to simplify circuit diagnostics (Optional for Type BR)
- Trip flag (CH only)
- Branch & combo type
- Auto reset (CH only)
- Plug-on neutral option (CH only)
- Lifetime warranty (CH only)



Ground Fault Breakers

- Available in 1" BR & 3/4" CH
- 1 pole 15-30A
- 2 pole 15-60A
- Plug-on neutral option (CH only)
- Trip flag (CH only)



1" UL Classified Breakers

- Type CL, 1 & 2 pole including Arc Fault & Ground Fault
- 10kAIC @ 120/240V
- For Square D Homeline, ITE/Siemens, Murray, GE, T & B, & Crouse Hinds panels
- 15 year warranty



3/4" UL Classified Breakers

- Type CHO, 1 & 2 pole including Ground Fault
- 10kAIC @ 120/240V
- For use in Square D QO panels
- 15 year warranty



CCV/CCVH, CV Circuit Breakers

- 2 & 3 pole
- 60-225A
- 10, 25, 42, 65, 100kAIC ratings @ 120/240V



CSR & CSH Main Breakers CH Panels

- 100 to 225A
- 25, 35kAIC @ 120/240V
- Meets UL 489, CSA
- Lifetime warranty



BW & CSR Main Breakers BR Panels

- 100 to 225A
- 10, 25kAIC @ 120/240V
- Meets UL 489, CSA,
- 10 year warranty



CH Loadcenters

- Plug-on neutral
- Surge ready
- Commercial grade 25kAIC rated main breaker (150A & above)
- Silver flash plated copper bus
- Full 60 circuit option
- Limited lifetime warranty
- Solar Power Centers available for solar applications



BR Loadcenters

- Metal backpan
- Single keyhole mounting
- Commercial grade 25kAIC rated main breaker (150A & above)
- Tin plated AL bus
- Min 150% neutral
- 10 year warranty



Flex Center Solutions

- Non-metallic enclosures
- Mechanical interlock covers
- OEM solutions
- Custom colors and configurations available
- Retrofit interiors (UL® listed versions)
- Single & three-phase versions



Power Outlet Panels

- Multiple configurations
- Temporary power
- RV parks
- Weather resistant/tamper resistant (WR/TR) receptacles



Generators

- Improved air cooled standby generators 8 - 20kW
- Liquid cooled standby generators 22- 150kW (single & three-phase)
- Portable generators 5500 - 17,500 watts
- Wireless monitor with smart device connectivity



Manual & Automatic Transfer Switches

- Complete home surge protection included (**Green** ATS)
- Universal **Green** ATS active load management system
- 50-400A
- Service entrance rated
- Listed to UL 1008 (UL67 for loadcenter/TS)
- NEMA Type 1 & 3R



Powering Business Worldwide



ECCN

- National network of service contractors
- Professional installation services
- Helping contractors grow their business
- Custom marketing programs/tools
- Training available



Meter Breakers

- Both BR & CH Type branch circuit styles available
- Available in Non-EUSERC & EUSERC (West Coast) designs
- 100-225A main breaker & main lug types
- Single-phase 3 wire, 120/240 applications
- Nema 3R rainproof construction
- OH/UG service applicable
- Solar Power Centers available for solar applications



Single Meter Sockets

- Available in 100, 200, & 320 Amp ratings
- Available in multiple service designs
- Available in single & multi-position configurations



Commercial Pedestals

- Time saving (all-inclusive) design
- Highest standard AIC ratings in the industry
- Standard copper bus and 3/4" interior design
- Custom configurations



Air Conditioning Disconnects

- 1 & 3 phase available
- Fusible & non-fusible
- Molded Case Switch
- Optional non-metallic enclosure



Pool Panel

- Up to 8 circuits
- Built-in timer for pump control
- Optional kits:
 - Timers, Transformers, & Freeze Control



Marine Power Pedestals

- Marine receptacles with circuit protection, communications, and water in weatherproof enclosures
- Standard LED lighting with photocell control
- Electric and water metering with optional wireless meter reading
- Custom colors available
- Limited lifetime housing warranty



Vehicle Power Pedestals

- Recreational vehicle receptacles with circuit protection, communications, and water in weatherproof enclosures
- Standard LED lighting with photocell control
- Electric and water metering with optional wireless meter reading
- Custom colors available
- Limited lifetime housing warranty



Distribution Substations

- 316 stainless steel, corrosion resistant, powder-coated enclosures with transformers and distribution panelboards
- Single-phase and three-phase transformers up to 500KVA
- 1200A distribution capability with main circuit breaker and GFCI protection
- Custom colors available
- Limited lifetime housing warranty



Pressure Switches

- Diaphragm Actuated Contacts for smooth operation
- Removable cover & ample wiring space for easy connection
- Adjustable cut-in, cut-out pressure to fit system requirements
- High impact molded cover for extra durability & increased life
- UL listed & CSA certified



Complete Home Surge Protection

- Type 2: complete home surge protection installed at the loadcenter
- Telephone, cable, and ac power protection available
- UL 1449 3rd Edition listed
- Surge breaker in 2-pole 30 & 50A designs



Electric Vehicle Supply Equipment

- Universal receptacle, level 1, and level 2 EV chargers
- Wall-mount, plug-connected, pedestal, and dual pedestal options
- 25ft J1772 cord
- Auto-restart on power outage feature
- Integration with home energy monitoring gateway
- LED site lighting optional

Eaton
 1000 Eaton Boulevard
 Cleveland, OH 44122
 United States
 877-ETN-CARE (877-386-2273)
 Eaton.com



Powering Business Worldwide

© 2014 Eaton
 All Rights Reserved
 Printed in USA
 Publication No. SA00415001E
 April 2014

UL is a registered trademark of Underwriters Laboratories.
 All other trademarks are property of their respective owners.