

Unique ATS Designed in Canada, CSA Approved for Canada

Solutions compatible with all major generator brands.



Metered Service Entrance (SE) Rated

- These switches combine the Meter socket, SE Disconnect and Automatic Transfer Switch (ATS) in one convenient enclosure.
- Available in two styles: Basic (EGSC line) and Advanced (EGS line with engine start).
- 100A and 200A solutions available.
- Quick, easy and attractive installation!

400A Service Entrance (SE) Rated

- These switches combine the SE Disconnect and Automatic Transfer Switch (ATS) in one convenient enclosure.
- Available in two styles: Basic (EGSC line) and Advanced (EGSCA line with load management and engine start).
- Can be mounted indoor or outdoor.
- The ONLY CSA 400 Amp Service rated ATS in Canada!



Service Entrance (SE) Rated

- These switches combine the SE Disconnect and Automatic Transfer Switch (ATS) in one convenient enclosure.
- Available in two styles: Basic (EGSC line) and Advanced (EGSCA line with load management and engine start).
- 100A and 200A solutions available.
- Can be mounted indoor or outdoor.



Powering Business Worldwide

As applicable, all products now standard with factory installed T1 Battery Charger Fuse Block.

3 Wire 120/240VAC Metered Combination Service Entrance Type 3 (Outdoor)

Product Selection

Main Breaker Rating	Catalogue Number	Control Style	Incoming	Dimensions (in)			Wire Size Range for Main CU/AL
				H	W	D	
100 Amp	EGSC100AMSE	Relay	OH/UG	36-1/8	18	7-7/8	(1) #6 AWG - 250 MCM
100 Amp	EGS100AMSE	ATC-100	OH/UG	36-1/8	18	7-7/8	(1) #6 AWG - 250 MCM
100 Amp	EGSC100AMSECLX	Relay	UG 1/2" Stud	40-7/8	18	7-7/8	(1) #6 AWG - 250 MCM
100 Amp	EGS100AMSECLX	ATC-100	UG 1/2" Stud	40-7/8	18	7-7/8	(1) #6 AWG - 250 MCM
200 Amp	EGSC200AMSE	Relay	OH/UG	36-1/8	18	7-7/8	(1) #6 AWG - 250 MCM
200 Amp	EGS200AMSE	ATC-100	OH/UG	36-1/8	18	7-7/8	(1) #6 AWG - 250 MCM
200 Amp	EGSC200AMSECLX	Relay	UG 1/2" Stud	40-7/8	18	7-7/8	(1) #6 AWG - 250 MCM
200Amp	EGS200AMSECLX	ATC-100	UG 1/2" Stud	40-7/8	18	7-7/8	(1) #6 AWG - 250 MCM

3 Wire 120/240VAC 400A Service Entrance Type 3 (Outdoor/Indoor)

Product Selection

Main Breaker Rating	Catalogue Number	Control Style	Incoming	Dimensions (in)			Wire Size Range for Main CU/AL
				H	W	D	
400 Amp	EGSC400ASE	Relay	OH or top RH LH	45-1/8	26-1/2	9-1/2	(1) 2/0 AWG - 500 MCM (2) 2/0 AWG - 250 MCM
400 Amp	EGSCA400ASE	RTC-100	OH or top RH LH	45-1/8	26-1/2	9-1/2	(1) 2/0 AWG - 500 MCM (2) 2/0 AWG - 250 MCM

3 Wire 120/240VAC 100/200A Service Entrance Type 3 (Outdoor/Indoor)

Product Selection

Main Breaker Rating	Catalogue Number	Control Style	Incoming	Dimensions (in)			Wire Size Range for Main CU/AL
				H	W	D	
100 Amp	EGSC100ASE	Relay	OH or top RH LH	29-1/2	14-3/8	5-3/8	(1) #2 AWG - 300 MCM
100 Amp	EGSCA100ASE	RTC-100	OH or top RH LH	29-1/2	14-3/8	5-3/8	(1) #2 AWG - 300 MCM
200 Amp	EGSC200ASE	Relay	OH or top RH LH	29-1/2	14-3/8	5-3/8	(1) #2 AWG - 300 MCM
200 Amp	EGSCA200ASE	RTC-100	OH or top RH LH	29-1/2	14-3/8	5-3/8	(1) #2 AWG - 300 MCM



Eaton
1000 Eaton Boulevard
Cleveland, Ohio 44122

Canadian Operations
5050 Mainway
Burlington, ON L7L 5Z1
Canada
1-800-268-3578
EatonCanada.ca

Pub Number: SA016013EN

© 2018 Eaton Corporation
All Rights Reserved
Printed in Canada
Publication No.
July 2018

Eaton is a registered trademark
of Eaton Corporation.
All trademarks are property of their
respective owners.