

Residential and Office



Eaton 3P Ellipse UPS

Stay protected – work and play worry-free



The 3P Ellipse UPS is Eaton's latest addition to its power protection solution portfolio. Sleek, attractively designed and silent in operation, this compact UPS offers an exceptional user experience for backup power in both residential and small business settings.

Power up with confidence

Enjoy up to **12% more power** than the previous Ellipse ECO models and a typical runtime of 15 to 20 minutes, ensuring you can **handle disruptions smoothly**.

Save yourself the hassle and the need for additional adapters, by plugging your equipment directly into the UPS using **FR, DIN/IT, and IEC outlet options**. This unique feature in a predominantly IEC-only market ensures convenience.

Operate any device with confidence, thanks to the **built-in surge protection** that meets the high-level **IEC 61643-11** standards.

Designed for your space

Complement any interior with 3P's contemporary good looks that also come with versatile usability. Flexible, **multi-position design** allows the UPS to fit seamlessly into any environment horizontally, vertically, as well as rack or wall-mounted (with optional kits).

Charge mobile devices whenever you need to using 3P's choice of **USB-A and USB-C charging ports**.

Watch, listen or work without distraction.

Enjoy a silent user experience in both residential and business settings thanks to 3P's discreet, no-fan engineering.

Control at your fingertips

Access status and notifications in real time via mobile app or web browser with an **optional CLOUD-PS card**. With remote now the 'new normal' for many small businesses, cloud connectivity brings added **control and peace of mind from any location**.



Powering Business Worldwide

Learn more:



Eaton 3P Ellipse

1. Slot for optional CLOUD-PS card
2. USB communication port
3. 3 outlets with surge protection and backup,
4. 1 socket with surge protection only
5. Circuit breaker reset button
6. Replaceable batteries



Eaton 3P Ellipse 900 USB FR

1. Slot for optional CLOUD-PS Card
2. USB communication port
3. 4 outlets with surge protection and backup
4. Circuit breaker reset button



Eaton 3P Ellipse 1700 USB FR

5. 4 outlets with surge protection
6. Replaceable batteries
7. USB charging ports

Technical specifications

	550	700	700 USB	900 USB	1300 USB	1700 USB
Rating (VA/W)	550VA/330W	700VA/420W	700VA/420W	900VA/540W	1300VA/840W	1700VA/1040W
Electrical Characteristics						
Technology	Standby					
Input voltage range	220-240V~ (Nominal) ; 184-264V~ adjustable to 160-284V~ (without using battery)					
Output voltage	230V (adjustable to 220V/230V/240V)					
Input frequency range	50 / 60 Hz (46 - 65 Hz working range)					
Input protection	10A resettable circuit breaker					
Surge protection	Compliant to IEC 61643-11 standard, Uoc=6000V, Up<1500V					
USB charge	-	-	2 USB charging ports (type A & type C)			
Connections						
Output connection (FR, DIN/IT, IEC models)	3 outlets with battery and surge protection + 1 outlet with surge protection				4 outlets with battery and surge protection + 4 outlets with surge protection	
Batteries						
Typical backup time for 1 PC	11 min	22 min	22 min	31 min	42 min	67 min
Typical backup time for 2 PC	-	8 min	8 min	13 min	20 min	30 min
Typical backup time for 3 PC	-	-	-	-	11 min	19 min
Battery management	Constant battery recharge, cold start, battery test, deep discharge protection, replaceable battery					
Communication						
Communication port	-	-	1 USB port			
Communication slot	-	-	Compatible with optional Cloud card			
Software	-	-	Eaton UPS Companion available on eaton.com			
Operating conditions, Compliances and Certifications						
Operating temperature	0 to 40°C					
Noise level	< 25dBA					
Compliances	IEC 62040-1; IEC 62040-2 C2; IEC 62040-3; IEC 61643-11; T3; RoHS; REACH. PEP Ecopassport					
Conformity	CE / Cm / UKCA (FR models) CE / Ukr / UKCA (DIN/IT models) CE / Cm / Ukr / UKCA (IEC models) CB report					
Dimensions DxHxW / Weight						
UPS Dimensions (mm)	235*263*81				312*305*81	
UPS Weight (kg)	3	3.7	3.9	4.4	7	7.8

Customer Service & Support

Warranty 3 years on electronics and 2 years on battery ; Unlimited warranty of connected equipment ; optional warranty+1 & warranty+3

* Backup times are approximate and may vary with equipment, configuration, battery age, temperature, etc.

Part Numbers	550	700	700 USB	900 USB	1300 USB	1700 USB
FR models	3P550F	3P700F	3P700UF	3P900UF	3P1300UF	3P1700UF
DIN/IT models	3P550D	3P700D	3P700UD	3P900UD	3P1300UD	3P1700UD
IEC models	3P550I	3P700I	3P700UI	3P900UI	3P1300UI	3P1700UI
Accessories						
19" rack mounting kit (2U)	ELRACK	ELRACK	ELRACK	ELRACK	ELRACK	ELRACK
Wall mounting kit	ELWALL	ELWALL	ELWALL	ELWALL	ELWALL	ELWALL

In the interests of continuous product improvement, all specifications are subject to change without notice.