

,EqptModel##other##,EqptDescription##other##,InputVoltage##electrical\_potential##volts,OutputVoltage##electrical\_potential##volts,BatteryVoltage##electrical\_potential##volts,NominalFrequencyRange##electrical\_frequency##hertz,NumberOfPhases##other##,PowerWatts##electrical\_power##watts,InputCurrent##electrical\_current##amperes,OutputCurrent##electrical\_current##amperes,BatteryCurrent##electrical\_current##amperes,Volume##volume##cubic\_meters,NominalHeight##length##millimeters,NominalDepth##length##millimeters,NominalWidth##length##millimeters,UnitWeight##unit\_weight##kilonewtons\_per\_cubic\_meter,UL924##other##,CommsOption##other##,Application##other##,BatteryConfiguration##other##,MaxHeatLoss##hvac\_power##watts,Protection##other##

1,9355-30,9355-20kVA UPS  
208V,208V,208V,216,50,3,18000,70,55,91,0.663,1684,761,494,3.041,Other,Power Expert Gateway Card,R/T (no output breaker),No Internal Battery (External Batteries Only),1981,Bypass Fuses

2,9355-30,9355-20kVA UPS  
208V,208V,208V,216,50,3,18000,70,55,91,0.663,1684,761,494,7.768,Other,Power Expert Gateway Card,R/T (no output breaker),3X Battery Shelves9Ah (108 Batteries),1981,Bypass Fuses

3,9355-30,9355-20kVA UPS  
208V,208V,208V,216,50,3,18000,70,55,91,0.663,1684,761,494,3.041,Other,Power Expert Gateway Card,Parallel (no output breaker),No Internal Battery (External Batteries Only),1981,Bypass Fuses

4,9355-30,9355-20kVA UPS  
208V,208V,208V,216,50,3,18000,70,55,91,0.663,1684,761,494,7.768,Other,Power Expert Gateway Card,Parallel (no output breaker),3X Battery Shelves9Ah (108 Batteries),1981,Bypass Fuses

5,9355-30,9355-20kVA UPS  
208V,208V,208V,216,50,3,18000,70,55,91,0.663,1684,761,494,3.041,Other,Power Expert Gateway Card,R/T with output breaker,No Internal Battery (External Batteries Only),1981,Bypass Fuses

6,9355-30,9355-20kVA UPS  
208V,208V,208V,216,50,3,18000,70,55,91,0.663,1684,761,494,7.768,Other,Power Expert Gateway Card,R/T with output breaker,3X Battery Shelves9Ah (108 Batteries),1981,Bypass Fuses

7,9355-30,9355-20kVA UPS  
208V,208V,208V,216,50,3,18000,70,55,91,0.663,1684,761,494,3.041,Other,Power Expert Gateway Card,Parallel with output breaker,No Internal Battery (External Batteries Only),1981,Bypass Fuses

8,9355-30,9355-20kVA UPS  
208V,208V,208V,216,50,3,18000,70,55,91,0.663,1684,761,494,7.768,Other,Power Expert Gateway Card,Parallel with output breaker,3X Battery Shelves9Ah (108 Batteries),1981,Bypass Fuses

9,9355-30,9355-20kVA UPS  
208V,208V,208V,216,50,3,18000,70,55,91,0.663,1684,761,494,3.041,Other,Power Expert Gateway Card,R/T - FAA (60 +/- 0.5 Hz) (no output breaker),No Internal Battery (External Batteries Only),1981,Bypass Fuses

10,9355-30,9355-20kVA UPS  
208V,208V,208V,216,50,3,18000,70,55,91,0.663,1684,761,494,7.768,Other,Power Expert Gateway Card,R/T - FAA (60 +/- 0.5 Hz) (no output breaker),3X Battery Shelves9Ah (108 Batteries),1981,Bypass Fuses

11,9355-30,9355-20kVA UPS  
208V,208V,208V,216,50,3,18000,70,55,91,0.663,1684,761,494,3.041,Other,Modbus Card,R/T (no output breaker),No Internal Battery (External Batteries Only),1981,Bypass Fuses

12,9355-30,9355-20kVA UPS  
208V,208V,208V,216,50,3,18000,70,55,91,0.663,1684,761,494,7.768,Other,Modbus Card,R/T (no output breaker),3X Battery Shelves9Ah (108 Batteries),1981,Bypass Fuses

13,9355-30,9355-20kVA UPS  
208V,208V,208V,216,50,3,18000,70,55,91,0.663,1684,761,494,3.041,Other,Modbus Card,Parallel (no output breaker),No Internal Battery (External Batteries Only),1981,Bypass Fuses

14,9355-30,9355-20kVA UPS  
208V,208V,208V,216,50,3,18000,70,55,91,0.663,1684,761,494,7.768,Other,Modbus Card,Parallel (no output breaker),3X Battery Shelves9Ah (108 Batteries),1981,Bypass Fuses

15,9355-30,9355-20kVA UPS  
208V,208V,208V,216,50,3,18000,70,55,91,0.663,1684,761,494,3.041,Other,Modbus Card,R/T

with output breaker, No Internal Battery (External Batteries Only), 1981, Bypass Fuses  
 16, 9355-30, 9355-20kVA UPS  
 208V, 208V, 208V, 216, 50, 3, 18000, 70, 55, 91, 0.663, 1684, 761, 494, 7.768, Other, Modbus Card, R/T  
 with output breaker, 3X Battery Shelves 9Ah (108 Batteries), 1981, Bypass Fuses  
 17, 9355-30, 9355-20kVA UPS  
 208V, 208V, 208V, 216, 50, 3, 18000, 70, 55, 91, 0.663, 1684, 761, 494, 3.041, Other, Modbus  
 Card, Parallel with output breaker, No Internal Battery (External Batteries  
 Only), 1981, Bypass Fuses  
 18, 9355-30, 9355-20kVA UPS  
 208V, 208V, 208V, 216, 50, 3, 18000, 70, 55, 91, 0.663, 1684, 761, 494, 7.768, Other, Modbus  
 Card, Parallel with output breaker, 3X Battery Shelves 9Ah (108 Batteries), 1981, Bypass  
 Fuses  
 19, 9355-30, 9355-20kVA UPS  
 208V, 208V, 208V, 216, 50, 3, 18000, 70, 55, 91, 0.663, 1684, 761, 494, 3.041, Other, Modbus Card, R/T -  
 FAA (60 +/- 0.5 Hz) (no output breaker), No Internal Battery (External Batteries  
 Only), 1981, Bypass Fuses  
 20, 9355-30, 9355-20kVA UPS  
 208V, 208V, 208V, 216, 50, 3, 18000, 70, 55, 91, 0.663, 1684, 761, 494, 7.768, Other, Modbus Card, R/T -  
 FAA (60 +/- 0.5 Hz) (no output breaker), 3X Battery Shelves 9Ah (108 Batteries), 1981, Bypass  
 Fuses  
 21, 9355-30, 9355-20kVA UPS  
 208V, 208V, 208V, 216, 50, 3, 18000, 70, 55, 91, 0.663, 1684, 761, 494, 3.041, Other, Relay Card, R/T (no  
 output breaker), No Internal Battery (External Batteries Only), 1981, Bypass Fuses  
 22, 9355-30, 9355-20kVA UPS  
 208V, 208V, 208V, 216, 50, 3, 18000, 70, 55, 91, 0.663, 1684, 761, 494, 7.768, Other, Relay Card, R/T (no  
 output breaker), 3X Battery Shelves 9Ah (108 Batteries), 1981, Bypass Fuses  
 23, 9355-30, 9355-20kVA UPS  
 208V, 208V, 208V, 216, 50, 3, 18000, 70, 55, 91, 0.663, 1684, 761, 494, 3.041, Other, Relay Card, Parallel  
 (no output breaker), No Internal Battery (External Batteries Only), 1981, Bypass Fuses  
 24, 9355-30, 9355-20kVA UPS  
 208V, 208V, 208V, 216, 50, 3, 18000, 70, 55, 91, 0.663, 1684, 761, 494, 7.768, Other, Relay Card, Parallel  
 (no output breaker), 3X Battery Shelves 9Ah (108 Batteries), 1981, Bypass Fuses  
 25, 9355-30, 9355-20kVA UPS  
 208V, 208V, 208V, 216, 50, 3, 18000, 70, 55, 91, 0.663, 1684, 761, 494, 3.041, Other, Relay Card, R/T with  
 output breaker, No Internal Battery (External Batteries Only), 1981, Bypass Fuses  
 26, 9355-30, 9355-20kVA UPS  
 208V, 208V, 208V, 216, 50, 3, 18000, 70, 55, 91, 0.663, 1684, 761, 494, 7.768, Other, Relay Card, R/T with  
 output breaker, 3X Battery Shelves 9Ah (108 Batteries), 1981, Bypass Fuses  
 27, 9355-30, 9355-20kVA UPS  
 208V, 208V, 208V, 216, 50, 3, 18000, 70, 55, 91, 0.663, 1684, 761, 494, 3.041, Other, Relay Card, Parallel  
 with output breaker, No Internal Battery (External Batteries Only), 1981, Bypass Fuses  
 28, 9355-30, 9355-20kVA UPS  
 208V, 208V, 208V, 216, 50, 3, 18000, 70, 55, 91, 0.663, 1684, 761, 494, 7.768, Other, Relay Card, Parallel  
 with output breaker, 3X Battery Shelves 9Ah (108 Batteries), 1981, Bypass Fuses  
 29, 9355-30, 9355-20kVA UPS  
 208V, 208V, 208V, 216, 50, 3, 18000, 70, 55, 91, 0.663, 1684, 761, 494, 3.041, Other, Relay Card, R/T -  
 FAA (60 +/- 0.5 Hz) (no output breaker), No Internal Battery (External Batteries  
 Only), 1981, Bypass Fuses  
 30, 9355-30, 9355-20kVA UPS  
 208V, 208V, 208V, 216, 50, 3, 18000, 70, 55, 91, 0.663, 1684, 761, 494, 7.768, Other, Relay Card, R/T -  
 FAA (60 +/- 0.5 Hz) (no output breaker), 3X Battery Shelves 9Ah (108 Batteries), 1981, Bypass  
 Fuses  
 31, 9355-30, 9355-20kVA UPS  
 208V, 208V, 208V, 216, 50, 3, 18000, 70, 55, 91, 0.663, 1684, 761, 494, 3.041, Other, Industrial Relay  
 Card, R/T (no output breaker), No Internal Battery (External Batteries Only), 1981, Bypass  
 Fuses  
 32, 9355-30, 9355-20kVA UPS  
 208V, 208V, 208V, 216, 50, 3, 18000, 70, 55, 91, 0.663, 1684, 761, 494, 7.768, Other, Industrial Relay  
 Card, R/T (no output breaker), 3X Battery Shelves 9Ah (108 Batteries), 1981, Bypass Fuses  
 33, 9355-30, 9355-20kVA UPS  
 208V, 208V, 208V, 216, 50, 3, 18000, 70, 55, 91, 0.663, 1684, 761, 494, 3.041, Other, Industrial Relay  
 Card, Parallel (no output breaker), No Internal Battery (External Batteries  
 Only), 1981, Bypass Fuses  
 34, 9355-30, 9355-20kVA UPS  
 208V, 208V, 208V, 216, 50, 3, 18000, 70, 55, 91, 0.663, 1684, 761, 494, 7.768, Other, Industrial Relay  
 Card, Parallel (no output breaker), 3X Battery Shelves 9Ah (108 Batteries), 1981, Bypass

**Fuses**

35,9355-30,9355-20kVA UPS

208V,208V,208V,216,50,3,18000,70,55,91,0.663,1684,761,494,3.041,Other,Industrial Relay Card,R/T with output breaker,No Internal Battery (External Batteries Only),1981,Bypass

**Fuses**

36,9355-30,9355-20kVA UPS

208V,208V,208V,216,50,3,18000,70,55,91,0.663,1684,761,494,7.768,Other,Industrial Relay Card,R/T with output breaker,3X Battery Shelves9Ah (108 Batteries),1981,Bypass Fuses

37,9355-30,9355-20kVA UPS

208V,208V,208V,216,50,3,18000,70,55,91,0.663,1684,761,494,3.041,Other,Industrial Relay Card,Parallel with output breaker,No Internal Battery (External Batteries

Only),1981,Bypass Fuses

38,9355-30,9355-20kVA UPS

208V,208V,208V,216,50,3,18000,70,55,91,0.663,1684,761,494,7.768,Other,Industrial Relay Card,Parallel with output breaker,3X Battery Shelves9Ah (108 Batteries),1981,Bypass

**Fuses**

39,9355-30,9355-20kVA UPS

208V,208V,208V,216,50,3,18000,70,55,91,0.663,1684,761,494,3.041,Other,Industrial Relay Card,R/T - FAA (60 +/- 0.5 Hz) (no output breaker),No Internal Battery (External

Batteries Only),1981,Bypass Fuses

40,9355-30,9355-20kVA UPS

208V,208V,208V,216,50,3,18000,70,55,91,0.663,1684,761,494,7.768,Other,Industrial Relay Card,R/T - FAA (60 +/- 0.5 Hz) (no output breaker),3X Battery Shelves9Ah (108

Batteries),1981,Bypass Fuses

41,9355-30,9355-20kVA UPS

208V,208V,208V,216,50,3,18000,70,55,91,0.663,1684,761,494,3.041,Other,Modem Card,R/T (no output breaker),No Internal Battery (External Batteries Only),1981,Bypass Fuses

42,9355-30,9355-20kVA UPS

208V,208V,208V,216,50,3,18000,70,55,91,0.663,1684,761,494,7.768,Other,Modem Card,R/T (no output breaker),3X Battery Shelves9Ah (108 Batteries),1981,Bypass Fuses

43,9355-30,9355-20kVA UPS

208V,208V,208V,216,50,3,18000,70,55,91,0.663,1684,761,494,3.041,Other,Modem Card,Parallel (no output breaker),No Internal Battery (External Batteries Only),1981,Bypass Fuses

44,9355-30,9355-20kVA UPS

208V,208V,208V,216,50,3,18000,70,55,91,0.663,1684,761,494,7.768,Other,Modem Card,Parallel (no output breaker),3X Battery Shelves9Ah (108 Batteries),1981,Bypass Fuses

45,9355-30,9355-20kVA UPS

208V,208V,208V,216,50,3,18000,70,55,91,0.663,1684,761,494,3.041,Other,Modem Card,R/T with output breaker,No Internal Battery (External Batteries Only),1981,Bypass Fuses

46,9355-30,9355-20kVA UPS

208V,208V,208V,216,50,3,18000,70,55,91,0.663,1684,761,494,7.768,Other,Modem Card,R/T with output breaker,3X Battery Shelves9Ah (108 Batteries),1981,Bypass Fuses

47,9355-30,9355-20kVA UPS

208V,208V,208V,216,50,3,18000,70,55,91,0.663,1684,761,494,3.041,Other,Modem Card,Parallel with output breaker,No Internal Battery (External Batteries Only),1981,Bypass Fuses

48,9355-30,9355-20kVA UPS

208V,208V,208V,216,50,3,18000,70,55,91,0.663,1684,761,494,7.768,Other,Modem Card,Parallel with output breaker,3X Battery Shelves9Ah (108 Batteries),1981,Bypass Fuses

49,9355-30,9355-20kVA UPS

208V,208V,208V,216,50,3,18000,70,55,91,0.663,1684,761,494,3.041,Other,Modem Card,R/T - FAA (60 +/- 0.5 Hz) (no output breaker),No Internal Battery (External Batteries

Only),1981,Bypass Fuses

50,9355-30,9355-20kVA UPS

208V,208V,208V,216,50,3,18000,70,55,91,0.663,1684,761,494,7.768,Other,Modem Card,R/T - FAA (60 +/- 0.5 Hz) (no output breaker),3X Battery Shelves9Ah (108 Batteries),1981,Bypass

**Fuses**

51,9355-30,9355-20kVA UPS

208V,208V,208V,216,60,3,18000,70,55,91,0.663,1684,761,494,3.041,Other,Power Expert Gateway Card,R/T (no output breaker),No Internal Battery (External Batteries

Only),1981,Bypass Fuses

52,9355-30,9355-20kVA UPS

208V,208V,208V,216,60,3,18000,70,55,91,0.663,1684,761,494,7.768,Other,Power Expert Gateway Card,R/T (no output breaker),3X Battery Shelves9Ah (108 Batteries),1981,Bypass

**Fuses**

53,9355-30,9355-20kVA UPS

208V,208V,208V,216,60,3,18000,70,55,91,0.663,1684,761,494,3.041,Other,Power Expert

Gateway Card,Parallel (no output breaker),No Internal Battery (External Batteries Only),1981,Bypass Fuses  
 54,9355-30,9355-20kVA UPS  
 208V,208V,208V,216,60,3,18000,70,55,91,0.663,1684,761,494,7.768,Other,Power Expert  
 Gateway Card,Parallel (no output breaker),3X Battery Shelves9Ah (108 Batteries),1981,Bypass Fuses  
 55,9355-30,9355-20kVA UPS  
 208V,208V,208V,216,60,3,18000,70,55,91,0.663,1684,761,494,3.041,Other,Power Expert  
 Gateway Card,R/T with output breaker,No Internal Battery (External Batteries Only),1981,Bypass Fuses  
 56,9355-30,9355-20kVA UPS  
 208V,208V,208V,216,60,3,18000,70,55,91,0.663,1684,761,494,7.768,Other,Power Expert  
 Gateway Card,R/T with output breaker,3X Battery Shelves9Ah (108 Batteries),1981,Bypass Fuses  
 57,9355-30,9355-20kVA UPS  
 208V,208V,208V,216,60,3,18000,70,55,91,0.663,1684,761,494,3.041,Other,Power Expert  
 Gateway Card,Parallel with output breaker,No Internal Battery (External Batteries Only),1981,Bypass Fuses  
 58,9355-30,9355-20kVA UPS  
 208V,208V,208V,216,60,3,18000,70,55,91,0.663,1684,761,494,7.768,Other,Power Expert  
 Gateway Card,Parallel with output breaker,3X Battery Shelves9Ah (108 Batteries),1981,Bypass Fuses  
 59,9355-30,9355-20kVA UPS  
 208V,208V,208V,216,60,3,18000,70,55,91,0.663,1684,761,494,3.041,Other,Power Expert  
 Gateway Card,R/T - FAA (60 +/- 0.5 Hz) (no output breaker),No Internal Battery (External Batteries Only),1981,Bypass Fuses  
 60,9355-30,9355-20kVA UPS  
 208V,208V,208V,216,60,3,18000,70,55,91,0.663,1684,761,494,7.768,Other,Power Expert  
 Gateway Card,R/T - FAA (60 +/- 0.5 Hz) (no output breaker),3X Battery Shelves9Ah (108 Batteries),1981,Bypass Fuses  
 61,9355-30,9355-20kVA UPS  
 208V,208V,208V,216,60,3,18000,70,55,91,0.663,1684,761,494,3.041,Other,Modbus Card,R/T (no output breaker),No Internal Battery (External Batteries Only),1981,Bypass Fuses  
 62,9355-30,9355-20kVA UPS  
 208V,208V,208V,216,60,3,18000,70,55,91,0.663,1684,761,494,7.768,Other,Modbus Card,R/T (no output breaker),3X Battery Shelves9Ah (108 Batteries),1981,Bypass Fuses  
 63,9355-30,9355-20kVA UPS  
 208V,208V,208V,216,60,3,18000,70,55,91,0.663,1684,761,494,3.041,Other,Modbus Card,Parallel (no output breaker),No Internal Battery (External Batteries Only),1981,Bypass Fuses  
 64,9355-30,9355-20kVA UPS  
 208V,208V,208V,216,60,3,18000,70,55,91,0.663,1684,761,494,7.768,Other,Modbus Card,Parallel (no output breaker),3X Battery Shelves9Ah (108 Batteries),1981,Bypass Fuses  
 65,9355-30,9355-20kVA UPS  
 208V,208V,208V,216,60,3,18000,70,55,91,0.663,1684,761,494,3.041,Other,Modbus Card,R/T with output breaker,No Internal Battery (External Batteries Only),1981,Bypass Fuses  
 66,9355-30,9355-20kVA UPS  
 208V,208V,208V,216,60,3,18000,70,55,91,0.663,1684,761,494,7.768,Other,Modbus Card,R/T with output breaker,3X Battery Shelves9Ah (108 Batteries),1981,Bypass Fuses  
 67,9355-30,9355-20kVA UPS  
 208V,208V,208V,216,60,3,18000,70,55,91,0.663,1684,761,494,3.041,Other,Modbus Card,Parallel with output breaker,No Internal Battery (External Batteries Only),1981,Bypass Fuses  
 68,9355-30,9355-20kVA UPS  
 208V,208V,208V,216,60,3,18000,70,55,91,0.663,1684,761,494,7.768,Other,Modbus Card,Parallel with output breaker,3X Battery Shelves9Ah (108 Batteries),1981,Bypass Fuses  
 69,9355-30,9355-20kVA UPS  
 208V,208V,208V,216,60,3,18000,70,55,91,0.663,1684,761,494,3.041,Other,Modbus Card,R/T - FAA (60 +/- 0.5 Hz) (no output breaker),No Internal Battery (External Batteries Only),1981,Bypass Fuses  
 70,9355-30,9355-20kVA UPS  
 208V,208V,208V,216,60,3,18000,70,55,91,0.663,1684,761,494,7.768,Other,Modbus Card,R/T - FAA (60 +/- 0.5 Hz) (no output breaker),3X Battery Shelves9Ah (108 Batteries),1981,Bypass Fuses

71,9355-30,9355-20kVA UPS  
208V,208V,208V,216,60,3,18000,70,55,91,0.663,1684,761,494,3.041,Other,Relay Card,R/T (no output breaker),No Internal Battery (External Batteries Only),1981,Bypass Fuses

72,9355-30,9355-20kVA UPS  
208V,208V,208V,216,60,3,18000,70,55,91,0.663,1684,761,494,7.768,Other,Relay Card,R/T (no output breaker),3X Battery Shelves9Ah (108 Batteries),1981,Bypass Fuses

73,9355-30,9355-20kVA UPS  
208V,208V,208V,216,60,3,18000,70,55,91,0.663,1684,761,494,3.041,Other,Relay Card,Parallel (no output breaker),No Internal Battery (External Batteries Only),1981,Bypass Fuses

74,9355-30,9355-20kVA UPS  
208V,208V,208V,216,60,3,18000,70,55,91,0.663,1684,761,494,7.768,Other,Relay Card,Parallel (no output breaker),3X Battery Shelves9Ah (108 Batteries),1981,Bypass Fuses

75,9355-30,9355-20kVA UPS  
208V,208V,208V,216,60,3,18000,70,55,91,0.663,1684,761,494,3.041,Other,Relay Card,R/T with output breaker,No Internal Battery (External Batteries Only),1981,Bypass Fuses

76,9355-30,9355-20kVA UPS  
208V,208V,208V,216,60,3,18000,70,55,91,0.663,1684,761,494,7.768,Other,Relay Card,R/T with output breaker,3X Battery Shelves9Ah (108 Batteries),1981,Bypass Fuses

77,9355-30,9355-20kVA UPS  
208V,208V,208V,216,60,3,18000,70,55,91,0.663,1684,761,494,3.041,Other,Relay Card,Parallel with output breaker,No Internal Battery (External Batteries Only),1981,Bypass Fuses

78,9355-30,9355-20kVA UPS  
208V,208V,208V,216,60,3,18000,70,55,91,0.663,1684,761,494,7.768,Other,Relay Card,Parallel with output breaker,3X Battery Shelves9Ah (108 Batteries),1981,Bypass Fuses

79,9355-30,9355-20kVA UPS  
208V,208V,208V,216,60,3,18000,70,55,91,0.663,1684,761,494,3.041,Other,Relay Card,R/T - FAA (60 +/- 0.5 Hz) (no output breaker),No Internal Battery (External Batteries Only),1981,Bypass Fuses

80,9355-30,9355-20kVA UPS  
208V,208V,208V,216,60,3,18000,70,55,91,0.663,1684,761,494,7.768,Other,Relay Card,R/T - FAA (60 +/- 0.5 Hz) (no output breaker),3X Battery Shelves9Ah (108 Batteries),1981,Bypass Fuses

81,9355-30,9355-20kVA UPS  
208V,208V,208V,216,60,3,18000,70,55,91,0.663,1684,761,494,3.041,Other,Industrial Relay Card,R/T (no output breaker),No Internal Battery (External Batteries Only),1981,Bypass Fuses

82,9355-30,9355-20kVA UPS  
208V,208V,208V,216,60,3,18000,70,55,91,0.663,1684,761,494,7.768,Other,Industrial Relay Card,R/T (no output breaker),3X Battery Shelves9Ah (108 Batteries),1981,Bypass Fuses

83,9355-30,9355-20kVA UPS  
208V,208V,208V,216,60,3,18000,70,55,91,0.663,1684,761,494,3.041,Other,Industrial Relay Card,Parallel (no output breaker),No Internal Battery (External Batteries Only),1981,Bypass Fuses

84,9355-30,9355-20kVA UPS  
208V,208V,208V,216,60,3,18000,70,55,91,0.663,1684,761,494,7.768,Other,Industrial Relay Card,Parallel (no output breaker),3X Battery Shelves9Ah (108 Batteries),1981,Bypass Fuses

85,9355-30,9355-20kVA UPS  
208V,208V,208V,216,60,3,18000,70,55,91,0.663,1684,761,494,3.041,Other,Industrial Relay Card,R/T with output breaker,No Internal Battery (External Batteries Only),1981,Bypass Fuses

86,9355-30,9355-20kVA UPS  
208V,208V,208V,216,60,3,18000,70,55,91,0.663,1684,761,494,7.768,Other,Industrial Relay Card,R/T with output breaker,3X Battery Shelves9Ah (108 Batteries),1981,Bypass Fuses

87,9355-30,9355-20kVA UPS  
208V,208V,208V,216,60,3,18000,70,55,91,0.663,1684,761,494,3.041,Other,Industrial Relay Card,Parallel with output breaker,No Internal Battery (External Batteries Only),1981,Bypass Fuses

88,9355-30,9355-20kVA UPS  
208V,208V,208V,216,60,3,18000,70,55,91,0.663,1684,761,494,7.768,Other,Industrial Relay Card,Parallel with output breaker,3X Battery Shelves9Ah (108 Batteries),1981,Bypass Fuses

89,9355-30,9355-20kVA UPS  
208V,208V,208V,216,60,3,18000,70,55,91,0.663,1684,761,494,3.041,Other,Industrial Relay Card,R/T - FAA (60 +/- 0.5 Hz) (no output breaker),No Internal Battery (External Batteries Only),1981,Bypass Fuses

90,9355-30,9355-20kVA UPS  
 208V,208V,208V,216,60,3,18000,70,55,91,0.663,1684,761,494,7.768,Other,Industrial Relay Card,R/T - FAA (60 +/- 0.5 Hz) (no output breaker),3X Battery Shelves9Ah (108 Batteries),1981,Bypass Fuses

91,9355-30,9355-20kVA UPS  
 208V,208V,208V,216,60,3,18000,70,55,91,0.663,1684,761,494,3.041,Other,Modem Card,R/T (no output breaker),No Internal Battery (External Batteries Only),1981,Bypass Fuses

92,9355-30,9355-20kVA UPS  
 208V,208V,208V,216,60,3,18000,70,55,91,0.663,1684,761,494,7.768,Other,Modem Card,R/T (no output breaker),3X Battery Shelves9Ah (108 Batteries),1981,Bypass Fuses

93,9355-30,9355-20kVA UPS  
 208V,208V,208V,216,60,3,18000,70,55,91,0.663,1684,761,494,3.041,Other,Modem Card,Parallel (no output breaker),No Internal Battery (External Batteries Only),1981,Bypass Fuses

94,9355-30,9355-20kVA UPS  
 208V,208V,208V,216,60,3,18000,70,55,91,0.663,1684,761,494,7.768,Other,Modem Card,Parallel (no output breaker),3X Battery Shelves9Ah (108 Batteries),1981,Bypass Fuses

95,9355-30,9355-20kVA UPS  
 208V,208V,208V,216,60,3,18000,70,55,91,0.663,1684,761,494,3.041,Other,Modem Card,R/T with output breaker,No Internal Battery (External Batteries Only),1981,Bypass Fuses

96,9355-30,9355-20kVA UPS  
 208V,208V,208V,216,60,3,18000,70,55,91,0.663,1684,761,494,7.768,Other,Modem Card,R/T with output breaker,3X Battery Shelves9Ah (108 Batteries),1981,Bypass Fuses

97,9355-30,9355-20kVA UPS  
 208V,208V,208V,216,60,3,18000,70,55,91,0.663,1684,761,494,3.041,Other,Modem Card,Parallel with output breaker,No Internal Battery (External Batteries Only),1981,Bypass Fuses

98,9355-30,9355-20kVA UPS  
 208V,208V,208V,216,60,3,18000,70,55,91,0.663,1684,761,494,7.768,Other,Modem Card,Parallel with output breaker,3X Battery Shelves9Ah (108 Batteries),1981,Bypass Fuses

99,9355-30,9355-20kVA UPS  
 208V,208V,208V,216,60,3,18000,70,55,91,0.663,1684,761,494,3.041,Other,Modem Card,R/T - FAA (60 +/- 0.5 Hz) (no output breaker),No Internal Battery (External Batteries Only),1981,Bypass Fuses

100,9355-30,9355-20kVA UPS  
 208V,208V,208V,216,60,3,18000,70,55,91,0.663,1684,761,494,7.768,Other,Modem Card,R/T - FAA (60 +/- 0.5 Hz) (no output breaker),3X Battery Shelves9Ah (108 Batteries),1981,Bypass Fuses

101,9355-30,9355-20kVA UPS  
 220V,220V,220V,216,50,3,18000,70,53,91,0.663,1684,761,494,3.041,Other,Power Expert Gateway Card,R/T (no output breaker),No Internal Battery (External Batteries Only),1981,Bypass Fuses

102,9355-30,9355-20kVA UPS  
 220V,220V,220V,216,50,3,18000,70,53,91,0.663,1684,761,494,7.768,Other,Power Expert Gateway Card,R/T (no output breaker),3X Battery Shelves9Ah (108 Batteries),1981,Bypass Fuses

103,9355-30,9355-20kVA UPS  
 220V,220V,220V,216,50,3,18000,70,53,91,0.663,1684,761,494,3.041,Other,Power Expert Gateway Card,Parallel (no output breaker),No Internal Battery (External Batteries Only),1981,Bypass Fuses

104,9355-30,9355-20kVA UPS  
 220V,220V,220V,216,50,3,18000,70,53,91,0.663,1684,761,494,7.768,Other,Power Expert Gateway Card,Parallel (no output breaker),3X Battery Shelves9Ah (108 Batteries),1981,Bypass Fuses

105,9355-30,9355-20kVA UPS  
 220V,220V,220V,216,50,3,18000,70,53,91,0.663,1684,761,494,3.041,Other,Power Expert Gateway Card,R/T with output breaker,No Internal Battery (External Batteries Only),1981,Bypass Fuses

106,9355-30,9355-20kVA UPS  
 220V,220V,220V,216,50,3,18000,70,53,91,0.663,1684,761,494,7.768,Other,Power Expert Gateway Card,R/T with output breaker,3X Battery Shelves9Ah (108 Batteries),1981,Bypass Fuses

107,9355-30,9355-20kVA UPS  
 220V,220V,220V,216,50,3,18000,70,53,91,0.663,1684,761,494,3.041,Other,Power Expert Gateway Card,Parallel with output breaker,No Internal Battery (External Batteries Only),1981,Bypass Fuses

108,9355-30,9355-20kVA UPS  
 220V,220V,220V,216,50,3,18000,70,53,91,0.663,1684,761,494,7.768,Other,Power Expert

Gateway Card,Parallel with output breaker,3X Battery Shelves9Ah (108 Batteries),1981,Bypass Fuses  
 109,9355-30,9355-20kVA UPS  
 220V,220V,220V,216,50,3,18000,70,53,91,0.663,1684,761,494,3.041,Other,Power Expert  
 Gateway Card,R/T - FAA (60 +/- 0.5 Hz) (no output breaker),No Internal Battery (External Batteries Only),1981,Bypass Fuses  
 110,9355-30,9355-20kVA UPS  
 220V,220V,220V,216,50,3,18000,70,53,91,0.663,1684,761,494,7.768,Other,Power Expert  
 Gateway Card,R/T - FAA (60 +/- 0.5 Hz) (no output breaker),3X Battery Shelves9Ah (108 Batteries),1981,Bypass Fuses  
 111,9355-30,9355-20kVA UPS  
 220V,220V,220V,216,50,3,18000,70,53,91,0.663,1684,761,494,3.041,Other,Modbus Card,R/T (no output breaker),No Internal Battery (External Batteries Only),1981,Bypass Fuses  
 112,9355-30,9355-20kVA UPS  
 220V,220V,220V,216,50,3,18000,70,53,91,0.663,1684,761,494,7.768,Other,Modbus Card,R/T (no output breaker),3X Battery Shelves9Ah (108 Batteries),1981,Bypass Fuses  
 113,9355-30,9355-20kVA UPS  
 220V,220V,220V,216,50,3,18000,70,53,91,0.663,1684,761,494,3.041,Other,Modbus Card,Parallel (no output breaker),No Internal Battery (External Batteries Only),1981,Bypass Fuses  
 114,9355-30,9355-20kVA UPS  
 220V,220V,220V,216,50,3,18000,70,53,91,0.663,1684,761,494,7.768,Other,Modbus Card,Parallel (no output breaker),3X Battery Shelves9Ah (108 Batteries),1981,Bypass Fuses  
 115,9355-30,9355-20kVA UPS  
 220V,220V,220V,216,50,3,18000,70,53,91,0.663,1684,761,494,3.041,Other,Modbus Card,R/T with output breaker,No Internal Battery (External Batteries Only),1981,Bypass Fuses  
 116,9355-30,9355-20kVA UPS  
 220V,220V,220V,216,50,3,18000,70,53,91,0.663,1684,761,494,7.768,Other,Modbus Card,R/T with output breaker,3X Battery Shelves9Ah (108 Batteries),1981,Bypass Fuses  
 117,9355-30,9355-20kVA UPS  
 220V,220V,220V,216,50,3,18000,70,53,91,0.663,1684,761,494,3.041,Other,Modbus Card,Parallel with output breaker,No Internal Battery (External Batteries Only),1981,Bypass Fuses  
 118,9355-30,9355-20kVA UPS  
 220V,220V,220V,216,50,3,18000,70,53,91,0.663,1684,761,494,7.768,Other,Modbus Card,Parallel with output breaker,3X Battery Shelves9Ah (108 Batteries),1981,Bypass Fuses  
 119,9355-30,9355-20kVA UPS  
 220V,220V,220V,216,50,3,18000,70,53,91,0.663,1684,761,494,3.041,Other,Modbus Card,R/T - FAA (60 +/- 0.5 Hz) (no output breaker),No Internal Battery (External Batteries Only),1981,Bypass Fuses  
 120,9355-30,9355-20kVA UPS  
 220V,220V,220V,216,50,3,18000,70,53,91,0.663,1684,761,494,7.768,Other,Modbus Card,R/T - FAA (60 +/- 0.5 Hz) (no output breaker),3X Battery Shelves9Ah (108 Batteries),1981,Bypass Fuses  
 121,9355-30,9355-20kVA UPS  
 220V,220V,220V,216,50,3,18000,70,53,91,0.663,1684,761,494,3.041,Other,Relay Card,R/T (no output breaker),No Internal Battery (External Batteries Only),1981,Bypass Fuses  
 122,9355-30,9355-20kVA UPS  
 220V,220V,220V,216,50,3,18000,70,53,91,0.663,1684,761,494,7.768,Other,Relay Card,R/T (no output breaker),3X Battery Shelves9Ah (108 Batteries),1981,Bypass Fuses  
 123,9355-30,9355-20kVA UPS  
 220V,220V,220V,216,50,3,18000,70,53,91,0.663,1684,761,494,3.041,Other,Relay Card,Parallel (no output breaker),No Internal Battery (External Batteries Only),1981,Bypass Fuses  
 124,9355-30,9355-20kVA UPS  
 220V,220V,220V,216,50,3,18000,70,53,91,0.663,1684,761,494,7.768,Other,Relay Card,Parallel (no output breaker),3X Battery Shelves9Ah (108 Batteries),1981,Bypass Fuses  
 125,9355-30,9355-20kVA UPS  
 220V,220V,220V,216,50,3,18000,70,53,91,0.663,1684,761,494,3.041,Other,Relay Card,R/T with output breaker,No Internal Battery (External Batteries Only),1981,Bypass Fuses  
 126,9355-30,9355-20kVA UPS  
 220V,220V,220V,216,50,3,18000,70,53,91,0.663,1684,761,494,7.768,Other,Relay Card,R/T with output breaker,3X Battery Shelves9Ah (108 Batteries),1981,Bypass Fuses  
 127,9355-30,9355-20kVA UPS  
 220V,220V,220V,216,50,3,18000,70,53,91,0.663,1684,761,494,3.041,Other,Relay Card,Parallel

with output breaker, No Internal Battery (External Batteries Only), 1981, Bypass Fuses  
 128, 9355-30, 9355-20kVA UPS  
 220V, 220V, 220V, 216, 50, 3, 18000, 70, 53, 91, 0.663, 1684, 761, 494, 7.768, Other, Relay Card, Parallel  
 with output breaker, 3X Battery Shelves 9Ah (108 Batteries), 1981, Bypass Fuses  
 129, 9355-30, 9355-20kVA UPS  
 220V, 220V, 220V, 216, 50, 3, 18000, 70, 53, 91, 0.663, 1684, 761, 494, 3.041, Other, Relay Card, R/T -  
 FAA (60 +/- 0.5 Hz) (no output breaker), No Internal Battery (External Batteries  
 Only), 1981, Bypass Fuses  
 130, 9355-30, 9355-20kVA UPS  
 220V, 220V, 220V, 216, 50, 3, 18000, 70, 53, 91, 0.663, 1684, 761, 494, 7.768, Other, Relay Card, R/T -  
 FAA (60 +/- 0.5 Hz) (no output breaker), 3X Battery Shelves 9Ah (108 Batteries), 1981, Bypass  
 Fuses  
 131, 9355-30, 9355-20kVA UPS  
 220V, 220V, 220V, 216, 50, 3, 18000, 70, 53, 91, 0.663, 1684, 761, 494, 3.041, Other, Industrial Relay  
 Card, R/T (no output breaker), No Internal Battery (External Batteries Only), 1981, Bypass  
 Fuses  
 132, 9355-30, 9355-20kVA UPS  
 220V, 220V, 220V, 216, 50, 3, 18000, 70, 53, 91, 0.663, 1684, 761, 494, 7.768, Other, Industrial Relay  
 Card, R/T (no output breaker), 3X Battery Shelves 9Ah (108 Batteries), 1981, Bypass Fuses  
 133, 9355-30, 9355-20kVA UPS  
 220V, 220V, 220V, 216, 50, 3, 18000, 70, 53, 91, 0.663, 1684, 761, 494, 3.041, Other, Industrial Relay  
 Card, Parallel (no output breaker), No Internal Battery (External Batteries  
 Only), 1981, Bypass Fuses  
 134, 9355-30, 9355-20kVA UPS  
 220V, 220V, 220V, 216, 50, 3, 18000, 70, 53, 91, 0.663, 1684, 761, 494, 7.768, Other, Industrial Relay  
 Card, Parallel (no output breaker), 3X Battery Shelves 9Ah (108 Batteries), 1981, Bypass  
 Fuses  
 135, 9355-30, 9355-20kVA UPS  
 220V, 220V, 220V, 216, 50, 3, 18000, 70, 53, 91, 0.663, 1684, 761, 494, 3.041, Other, Industrial Relay  
 Card, R/T with output breaker, No Internal Battery (External Batteries Only), 1981, Bypass  
 Fuses  
 136, 9355-30, 9355-20kVA UPS  
 220V, 220V, 220V, 216, 50, 3, 18000, 70, 53, 91, 0.663, 1684, 761, 494, 7.768, Other, Industrial Relay  
 Card, R/T with output breaker, 3X Battery Shelves 9Ah (108 Batteries), 1981, Bypass Fuses  
 137, 9355-30, 9355-20kVA UPS  
 220V, 220V, 220V, 216, 50, 3, 18000, 70, 53, 91, 0.663, 1684, 761, 494, 3.041, Other, Industrial Relay  
 Card, Parallel with output breaker, No Internal Battery (External Batteries  
 Only), 1981, Bypass Fuses  
 138, 9355-30, 9355-20kVA UPS  
 220V, 220V, 220V, 216, 50, 3, 18000, 70, 53, 91, 0.663, 1684, 761, 494, 7.768, Other, Industrial Relay  
 Card, Parallel with output breaker, 3X Battery Shelves 9Ah (108 Batteries), 1981, Bypass  
 Fuses  
 139, 9355-30, 9355-20kVA UPS  
 220V, 220V, 220V, 216, 50, 3, 18000, 70, 53, 91, 0.663, 1684, 761, 494, 3.041, Other, Industrial Relay  
 Card, R/T - FAA (60 +/- 0.5 Hz) (no output breaker), No Internal Battery (External  
 Batteries Only), 1981, Bypass Fuses  
 140, 9355-30, 9355-20kVA UPS  
 220V, 220V, 220V, 216, 50, 3, 18000, 70, 53, 91, 0.663, 1684, 761, 494, 7.768, Other, Industrial Relay  
 Card, R/T - FAA (60 +/- 0.5 Hz) (no output breaker), 3X Battery Shelves 9Ah (108  
 Batteries), 1981, Bypass Fuses  
 141, 9355-30, 9355-20kVA UPS  
 220V, 220V, 220V, 216, 50, 3, 18000, 70, 53, 91, 0.663, 1684, 761, 494, 3.041, Other, Modem Card, R/T (no  
 output breaker), No Internal Battery (External Batteries Only), 1981, Bypass Fuses  
 142, 9355-30, 9355-20kVA UPS  
 220V, 220V, 220V, 216, 50, 3, 18000, 70, 53, 91, 0.663, 1684, 761, 494, 7.768, Other, Modem Card, R/T (no  
 output breaker), 3X Battery Shelves 9Ah (108 Batteries), 1981, Bypass Fuses  
 143, 9355-30, 9355-20kVA UPS  
 220V, 220V, 220V, 216, 50, 3, 18000, 70, 53, 91, 0.663, 1684, 761, 494, 3.041, Other, Modem Card, Parallel  
 (no output breaker), No Internal Battery (External Batteries Only), 1981, Bypass Fuses  
 144, 9355-30, 9355-20kVA UPS  
 220V, 220V, 220V, 216, 50, 3, 18000, 70, 53, 91, 0.663, 1684, 761, 494, 7.768, Other, Modem Card, Parallel  
 (no output breaker), 3X Battery Shelves 9Ah (108 Batteries), 1981, Bypass Fuses  
 145, 9355-30, 9355-20kVA UPS  
 220V, 220V, 220V, 216, 50, 3, 18000, 70, 53, 91, 0.663, 1684, 761, 494, 3.041, Other, Modem Card, R/T with  
 output breaker, No Internal Battery (External Batteries Only), 1981, Bypass Fuses  
 146, 9355-30, 9355-20kVA UPS



220V,220V,220V,216,50,3,18000,70,53,91,0.663,1684,761,494,7.768,Other,Modem Card,R/T with output breaker,3X Battery Shelves9Ah (108 Batteries),1981,Bypass Fuses

147,9355-30,9355-20kVA UPS

220V,220V,220V,216,50,3,18000,70,53,91,0.663,1684,761,494,3.041,Other,Modem Card,Parallel with output breaker,No Internal Battery (External Batteries Only),1981,Bypass Fuses

148,9355-30,9355-20kVA UPS

220V,220V,220V,216,50,3,18000,70,53,91,0.663,1684,761,494,7.768,Other,Modem Card,Parallel with output breaker,3X Battery Shelves9Ah (108 Batteries),1981,Bypass Fuses

149,9355-30,9355-20kVA UPS

220V,220V,220V,216,50,3,18000,70,53,91,0.663,1684,761,494,3.041,Other,Modem Card,R/T - FAA (60 +/- 0.5 Hz) (no output breaker),No Internal Battery (External Batteries Only),1981,Bypass Fuses

150,9355-30,9355-20kVA UPS

220V,220V,220V,216,50,3,18000,70,53,91,0.663,1684,761,494,7.768,Other,Modem Card,R/T - FAA (60 +/- 0.5 Hz) (no output breaker),3X Battery Shelves9Ah (108 Batteries),1981,Bypass Fuses

151,9355-30,9355-20kVA UPS

220V,220V,220V,216,60,3,18000,70,53,91,0.663,1684,761,494,3.041,Other,Power Expert Gateway Card,R/T (no output breaker),No Internal Battery (External Batteries Only),1981,Bypass Fuses

152,9355-30,9355-20kVA UPS

220V,220V,220V,216,60,3,18000,70,53,91,0.663,1684,761,494,7.768,Other,Power Expert Gateway Card,R/T (no output breaker),3X Battery Shelves9Ah (108 Batteries),1981,Bypass Fuses

153,9355-30,9355-20kVA UPS

220V,220V,220V,216,60,3,18000,70,53,91,0.663,1684,761,494,3.041,Other,Power Expert Gateway Card,Parallel (no output breaker),No Internal Battery (External Batteries Only),1981,Bypass Fuses

154,9355-30,9355-20kVA UPS

220V,220V,220V,216,60,3,18000,70,53,91,0.663,1684,761,494,7.768,Other,Power Expert Gateway Card,Parallel (no output breaker),3X Battery Shelves9Ah (108 Batteries),1981,Bypass Fuses

155,9355-30,9355-20kVA UPS

220V,220V,220V,216,60,3,18000,70,53,91,0.663,1684,761,494,3.041,Other,Power Expert Gateway Card,R/T with output breaker,No Internal Battery (External Batteries Only),1981,Bypass Fuses

156,9355-30,9355-20kVA UPS

220V,220V,220V,216,60,3,18000,70,53,91,0.663,1684,761,494,7.768,Other,Power Expert Gateway Card,R/T with output breaker,3X Battery Shelves9Ah (108 Batteries),1981,Bypass Fuses

157,9355-30,9355-20kVA UPS

220V,220V,220V,216,60,3,18000,70,53,91,0.663,1684,761,494,3.041,Other,Power Expert Gateway Card,Parallel with output breaker,No Internal Battery (External Batteries Only),1981,Bypass Fuses

158,9355-30,9355-20kVA UPS

220V,220V,220V,216,60,3,18000,70,53,91,0.663,1684,761,494,7.768,Other,Power Expert Gateway Card,Parallel with output breaker,3X Battery Shelves9Ah (108 Batteries),1981,Bypass Fuses

159,9355-30,9355-20kVA UPS

220V,220V,220V,216,60,3,18000,70,53,91,0.663,1684,761,494,3.041,Other,Power Expert Gateway Card,R/T - FAA (60 +/- 0.5 Hz) (no output breaker),No Internal Battery (External Batteries Only),1981,Bypass Fuses

160,9355-30,9355-20kVA UPS

220V,220V,220V,216,60,3,18000,70,53,91,0.663,1684,761,494,7.768,Other,Power Expert Gateway Card,R/T - FAA (60 +/- 0.5 Hz) (no output breaker),3X Battery Shelves9Ah (108 Batteries),1981,Bypass Fuses

161,9355-30,9355-20kVA UPS

220V,220V,220V,216,60,3,18000,70,53,91,0.663,1684,761,494,3.041,Other,Modbus Card,R/T (no output breaker),No Internal Battery (External Batteries Only),1981,Bypass Fuses

162,9355-30,9355-20kVA UPS

220V,220V,220V,216,60,3,18000,70,53,91,0.663,1684,761,494,7.768,Other,Modbus Card,R/T (no output breaker),3X Battery Shelves9Ah (108 Batteries),1981,Bypass Fuses

163,9355-30,9355-20kVA UPS

220V,220V,220V,216,60,3,18000,70,53,91,0.663,1684,761,494,3.041,Other,Modbus Card,Parallel (no output breaker),No Internal Battery (External Batteries Only),1981,Bypass Fuses

164,9355-30,9355-20kVA UPS  
 220V,220V,220V,216,60,3,18000,70,53,91,0.663,1684,761,494,7.768,Other,Modbus Card,Parallel (no output breaker),3X Battery Shelves9Ah (108 Batteries),1981,Bypass Fuses

165,9355-30,9355-20kVA UPS  
 220V,220V,220V,216,60,3,18000,70,53,91,0.663,1684,761,494,3.041,Other,Modbus Card,R/T with output breaker,No Internal Battery (External Batteries Only),1981,Bypass Fuses

166,9355-30,9355-20kVA UPS  
 220V,220V,220V,216,60,3,18000,70,53,91,0.663,1684,761,494,7.768,Other,Modbus Card,R/T with output breaker,3X Battery Shelves9Ah (108 Batteries),1981,Bypass Fuses

167,9355-30,9355-20kVA UPS  
 220V,220V,220V,216,60,3,18000,70,53,91,0.663,1684,761,494,3.041,Other,Modbus Card,Parallel with output breaker,No Internal Battery (External Batteries Only),1981,Bypass Fuses

168,9355-30,9355-20kVA UPS  
 220V,220V,220V,216,60,3,18000,70,53,91,0.663,1684,761,494,7.768,Other,Modbus Card,Parallel with output breaker,3X Battery Shelves9Ah (108 Batteries),1981,Bypass Fuses

169,9355-30,9355-20kVA UPS  
 220V,220V,220V,216,60,3,18000,70,53,91,0.663,1684,761,494,3.041,Other,Modbus Card,R/T - FAA (60 +/- 0.5 Hz) (no output breaker),No Internal Battery (External Batteries Only),1981,Bypass Fuses

170,9355-30,9355-20kVA UPS  
 220V,220V,220V,216,60,3,18000,70,53,91,0.663,1684,761,494,7.768,Other,Modbus Card,R/T - FAA (60 +/- 0.5 Hz) (no output breaker),3X Battery Shelves9Ah (108 Batteries),1981,Bypass Fuses

171,9355-30,9355-20kVA UPS  
 220V,220V,220V,216,60,3,18000,70,53,91,0.663,1684,761,494,3.041,Other,Relay Card,R/T (no output breaker),No Internal Battery (External Batteries Only),1981,Bypass Fuses

172,9355-30,9355-20kVA UPS  
 220V,220V,220V,216,60,3,18000,70,53,91,0.663,1684,761,494,7.768,Other,Relay Card,R/T (no output breaker),3X Battery Shelves9Ah (108 Batteries),1981,Bypass Fuses

173,9355-30,9355-20kVA UPS  
 220V,220V,220V,216,60,3,18000,70,53,91,0.663,1684,761,494,3.041,Other,Relay Card,Parallel (no output breaker),No Internal Battery (External Batteries Only),1981,Bypass Fuses

174,9355-30,9355-20kVA UPS  
 220V,220V,220V,216,60,3,18000,70,53,91,0.663,1684,761,494,7.768,Other,Relay Card,Parallel (no output breaker),3X Battery Shelves9Ah (108 Batteries),1981,Bypass Fuses

175,9355-30,9355-20kVA UPS  
 220V,220V,220V,216,60,3,18000,70,53,91,0.663,1684,761,494,3.041,Other,Relay Card,R/T with output breaker,No Internal Battery (External Batteries Only),1981,Bypass Fuses

176,9355-30,9355-20kVA UPS  
 220V,220V,220V,216,60,3,18000,70,53,91,0.663,1684,761,494,7.768,Other,Relay Card,R/T with output breaker,3X Battery Shelves9Ah (108 Batteries),1981,Bypass Fuses

177,9355-30,9355-20kVA UPS  
 220V,220V,220V,216,60,3,18000,70,53,91,0.663,1684,761,494,3.041,Other,Relay Card,Parallel with output breaker,No Internal Battery (External Batteries Only),1981,Bypass Fuses

178,9355-30,9355-20kVA UPS  
 220V,220V,220V,216,60,3,18000,70,53,91,0.663,1684,761,494,7.768,Other,Relay Card,Parallel with output breaker,3X Battery Shelves9Ah (108 Batteries),1981,Bypass Fuses

179,9355-30,9355-20kVA UPS  
 220V,220V,220V,216,60,3,18000,70,53,91,0.663,1684,761,494,3.041,Other,Relay Card,R/T - FAA (60 +/- 0.5 Hz) (no output breaker),No Internal Battery (External Batteries Only),1981,Bypass Fuses

180,9355-30,9355-20kVA UPS  
 220V,220V,220V,216,60,3,18000,70,53,91,0.663,1684,761,494,7.768,Other,Relay Card,R/T - FAA (60 +/- 0.5 Hz) (no output breaker),3X Battery Shelves9Ah (108 Batteries),1981,Bypass Fuses

181,9355-30,9355-20kVA UPS  
 220V,220V,220V,216,60,3,18000,70,53,91,0.663,1684,761,494,3.041,Other,Industrial Relay Card,R/T (no output breaker),No Internal Battery (External Batteries Only),1981,Bypass Fuses

182,9355-30,9355-20kVA UPS  
 220V,220V,220V,216,60,3,18000,70,53,91,0.663,1684,761,494,7.768,Other,Industrial Relay Card,R/T (no output breaker),3X Battery Shelves9Ah (108 Batteries),1981,Bypass Fuses

183,9355-30,9355-20kVA UPS

220V,220V,220V,216,60,3,18000,70,53,91,0.663,1684,761,494,3.041,Other,Industrial Relay Card,Parallel (no output breaker),No Internal Battery (External Batteries Only),1981,Bypass Fuses

184,9355-30,9355-20kVA UPS

220V,220V,220V,216,60,3,18000,70,53,91,0.663,1684,761,494,7.768,Other,Industrial Relay Card,Parallel (no output breaker),3X Battery Shelves9Ah (108 Batteries),1981,Bypass Fuses

185,9355-30,9355-20kVA UPS

220V,220V,220V,216,60,3,18000,70,53,91,0.663,1684,761,494,3.041,Other,Industrial Relay Card,R/T with output breaker,No Internal Battery (External Batteries Only),1981,Bypass Fuses

186,9355-30,9355-20kVA UPS

220V,220V,220V,216,60,3,18000,70,53,91,0.663,1684,761,494,7.768,Other,Industrial Relay Card,R/T with output breaker,3X Battery Shelves9Ah (108 Batteries),1981,Bypass Fuses

187,9355-30,9355-20kVA UPS

220V,220V,220V,216,60,3,18000,70,53,91,0.663,1684,761,494,3.041,Other,Industrial Relay Card,Parallel with output breaker,No Internal Battery (External Batteries Only),1981,Bypass Fuses

188,9355-30,9355-20kVA UPS

220V,220V,220V,216,60,3,18000,70,53,91,0.663,1684,761,494,7.768,Other,Industrial Relay Card,Parallel with output breaker,3X Battery Shelves9Ah (108 Batteries),1981,Bypass Fuses

189,9355-30,9355-20kVA UPS

220V,220V,220V,216,60,3,18000,70,53,91,0.663,1684,761,494,3.041,Other,Industrial Relay Card,R/T - FAA (60 +/- 0.5 Hz) (no output breaker),No Internal Battery (External Batteries Only),1981,Bypass Fuses

190,9355-30,9355-20kVA UPS

220V,220V,220V,216,60,3,18000,70,53,91,0.663,1684,761,494,7.768,Other,Industrial Relay Card,R/T - FAA (60 +/- 0.5 Hz) (no output breaker),3X Battery Shelves9Ah (108 Batteries),1981,Bypass Fuses

191,9355-30,9355-20kVA UPS

220V,220V,220V,216,60,3,18000,70,53,91,0.663,1684,761,494,3.041,Other,Modem Card,R/T (no output breaker),No Internal Battery (External Batteries Only),1981,Bypass Fuses

192,9355-30,9355-20kVA UPS

220V,220V,220V,216,60,3,18000,70,53,91,0.663,1684,761,494,7.768,Other,Modem Card,R/T (no output breaker),3X Battery Shelves9Ah (108 Batteries),1981,Bypass Fuses

193,9355-30,9355-20kVA UPS

220V,220V,220V,216,60,3,18000,70,53,91,0.663,1684,761,494,3.041,Other,Modem Card,Parallel (no output breaker),No Internal Battery (External Batteries Only),1981,Bypass Fuses

194,9355-30,9355-20kVA UPS

220V,220V,220V,216,60,3,18000,70,53,91,0.663,1684,761,494,7.768,Other,Modem Card,Parallel (no output breaker),3X Battery Shelves9Ah (108 Batteries),1981,Bypass Fuses

195,9355-30,9355-20kVA UPS

220V,220V,220V,216,60,3,18000,70,53,91,0.663,1684,761,494,3.041,Other,Modem Card,R/T with output breaker,No Internal Battery (External Batteries Only),1981,Bypass Fuses

196,9355-30,9355-20kVA UPS

220V,220V,220V,216,60,3,18000,70,53,91,0.663,1684,761,494,7.768,Other,Modem Card,R/T with output breaker,3X Battery Shelves9Ah (108 Batteries),1981,Bypass Fuses

197,9355-30,9355-20kVA UPS

220V,220V,220V,216,60,3,18000,70,53,91,0.663,1684,761,494,3.041,Other,Modem Card,Parallel with output breaker,No Internal Battery (External Batteries Only),1981,Bypass Fuses

198,9355-30,9355-20kVA UPS

220V,220V,220V,216,60,3,18000,70,53,91,0.663,1684,761,494,7.768,Other,Modem Card,Parallel with output breaker,3X Battery Shelves9Ah (108 Batteries),1981,Bypass Fuses

199,9355-30,9355-20kVA UPS

220V,220V,220V,216,60,3,18000,70,53,91,0.663,1684,761,494,3.041,Other,Modem Card,R/T - FAA (60 +/- 0.5 Hz) (no output breaker),No Internal Battery (External Batteries Only),1981,Bypass Fuses

200,9355-30,9355-20kVA UPS

220V,220V,220V,216,60,3,18000,70,53,91,0.663,1684,761,494,7.768,Other,Modem Card,R/T - FAA (60 +/- 0.5 Hz) (no output breaker),3X Battery Shelves9Ah (108 Batteries),1981,Bypass Fuses

201,9355-30,9355-30kVA UPS

208V,208V,208V,216,50,3,27000,100,83,136,0.663,1684,761,494,3.041,Other,Power Expert Gateway Card,R/T (no output breaker),No Internal Battery (External Batteries Only),2702,Bypass Fuses

202,9355-30,9355-30kVA UPS  
 208V,208V,208V,216,50,3,27000,100,83,136,0.663,1684,761,494,7.768,Other,Power Expert Gateway Card,R/T (no output breaker),3X Battery Shelves9Ah (108 Batteries),2702,Bypass Fuses

203,9355-30,9355-30kVA UPS  
 208V,208V,208V,216,50,3,27000,100,83,136,0.663,1684,761,494,3.041,Other,Power Expert Gateway Card,Parallel (no output breaker),No Internal Battery (External Batteries Only),2702,Bypass Fuses

204,9355-30,9355-30kVA UPS  
 208V,208V,208V,216,50,3,27000,100,83,136,0.663,1684,761,494,7.768,Other,Power Expert Gateway Card,Parallel (no output breaker),3X Battery Shelves9Ah (108 Batteries),2702,Bypass Fuses

205,9355-30,9355-30kVA UPS  
 208V,208V,208V,216,50,3,27000,100,83,136,0.663,1684,761,494,3.041,Other,Power Expert Gateway Card,R/T with output breaker,No Internal Battery (External Batteries Only),2702,Bypass Fuses

206,9355-30,9355-30kVA UPS  
 208V,208V,208V,216,50,3,27000,100,83,136,0.663,1684,761,494,7.768,Other,Power Expert Gateway Card,R/T with output breaker,3X Battery Shelves9Ah (108 Batteries),2702,Bypass Fuses

207,9355-30,9355-30kVA UPS  
 208V,208V,208V,216,50,3,27000,100,83,136,0.663,1684,761,494,3.041,Other,Power Expert Gateway Card,Parallel with output breaker,No Internal Battery (External Batteries Only),2702,Bypass Fuses

208,9355-30,9355-30kVA UPS  
 208V,208V,208V,216,50,3,27000,100,83,136,0.663,1684,761,494,7.768,Other,Power Expert Gateway Card,Parallel with output breaker,3X Battery Shelves9Ah (108 Batteries),2702,Bypass Fuses

209,9355-30,9355-30kVA UPS  
 208V,208V,208V,216,50,3,27000,100,83,136,0.663,1684,761,494,3.041,Other,Power Expert Gateway Card,R/T - FAA (60 +/- 0.5 Hz) (no output breaker),No Internal Battery (External Batteries Only),2702,Bypass Fuses

210,9355-30,9355-30kVA UPS  
 208V,208V,208V,216,50,3,27000,100,83,136,0.663,1684,761,494,7.768,Other,Power Expert Gateway Card,R/T - FAA (60 +/- 0.5 Hz) (no output breaker),3X Battery Shelves9Ah (108 Batteries),2702,Bypass Fuses

211,9355-30,9355-30kVA UPS  
 208V,208V,208V,216,50,3,27000,100,83,136,0.663,1684,761,494,3.041,Other,Modbus Card,R/T (no output breaker),No Internal Battery (External Batteries Only),2702,Bypass Fuses

212,9355-30,9355-30kVA UPS  
 208V,208V,208V,216,50,3,27000,100,83,136,0.663,1684,761,494,7.768,Other,Modbus Card,R/T (no output breaker),3X Battery Shelves9Ah (108 Batteries),2702,Bypass Fuses

213,9355-30,9355-30kVA UPS  
 208V,208V,208V,216,50,3,27000,100,83,136,0.663,1684,761,494,3.041,Other,Modbus Card,Parallel (no output breaker),No Internal Battery (External Batteries Only),2702,Bypass Fuses

214,9355-30,9355-30kVA UPS  
 208V,208V,208V,216,50,3,27000,100,83,136,0.663,1684,761,494,7.768,Other,Modbus Card,Parallel (no output breaker),3X Battery Shelves9Ah (108 Batteries),2702,Bypass Fuses

215,9355-30,9355-30kVA UPS  
 208V,208V,208V,216,50,3,27000,100,83,136,0.663,1684,761,494,3.041,Other,Modbus Card,R/T with output breaker,No Internal Battery (External Batteries Only),2702,Bypass Fuses

216,9355-30,9355-30kVA UPS  
 208V,208V,208V,216,50,3,27000,100,83,136,0.663,1684,761,494,7.768,Other,Modbus Card,R/T with output breaker,3X Battery Shelves9Ah (108 Batteries),2702,Bypass Fuses

217,9355-30,9355-30kVA UPS  
 208V,208V,208V,216,50,3,27000,100,83,136,0.663,1684,761,494,3.041,Other,Modbus Card,Parallel with output breaker,No Internal Battery (External Batteries Only),2702,Bypass Fuses

218,9355-30,9355-30kVA UPS  
 208V,208V,208V,216,50,3,27000,100,83,136,0.663,1684,761,494,7.768,Other,Modbus Card,Parallel with output breaker,3X Battery Shelves9Ah (108 Batteries),2702,Bypass Fuses

219,9355-30,9355-30kVA UPS  
 208V,208V,208V,216,50,3,27000,100,83,136,0.663,1684,761,494,3.041,Other,Modbus Card,R/T -

FAA (60 +/- 0.5 Hz) (no output breaker),No Internal Battery (External Batteries Only),2702,Bypass Fuses  
 220,9355-30,9355-30kVA UPS  
 208V,208V,208V,216,50,3,27000,100,83,136,0.663,1684,761,494,7.768,Other,Modbus Card,R/T -  
 FAA (60 +/- 0.5 Hz) (no output breaker),3X Battery Shelves9Ah (108 Batteries),2702,Bypass Fuses  
 221,9355-30,9355-30kVA UPS  
 208V,208V,208V,216,50,3,27000,100,83,136,0.663,1684,761,494,3.041,Other,Relay Card,R/T (no output breaker),No Internal Battery (External Batteries Only),2702,Bypass Fuses  
 222,9355-30,9355-30kVA UPS  
 208V,208V,208V,216,50,3,27000,100,83,136,0.663,1684,761,494,7.768,Other,Relay Card,R/T (no output breaker),3X Battery Shelves9Ah (108 Batteries),2702,Bypass Fuses  
 223,9355-30,9355-30kVA UPS  
 208V,208V,208V,216,50,3,27000,100,83,136,0.663,1684,761,494,3.041,Other,Relay Card,Parallel (no output breaker),No Internal Battery (External Batteries Only),2702,Bypass Fuses  
 224,9355-30,9355-30kVA UPS  
 208V,208V,208V,216,50,3,27000,100,83,136,0.663,1684,761,494,7.768,Other,Relay Card,Parallel (no output breaker),3X Battery Shelves9Ah (108 Batteries),2702,Bypass Fuses  
 225,9355-30,9355-30kVA UPS  
 208V,208V,208V,216,50,3,27000,100,83,136,0.663,1684,761,494,3.041,Other,Relay Card,R/T with output breaker,No Internal Battery (External Batteries Only),2702,Bypass Fuses  
 226,9355-30,9355-30kVA UPS  
 208V,208V,208V,216,50,3,27000,100,83,136,0.663,1684,761,494,7.768,Other,Relay Card,R/T with output breaker,3X Battery Shelves9Ah (108 Batteries),2702,Bypass Fuses  
 227,9355-30,9355-30kVA UPS  
 208V,208V,208V,216,50,3,27000,100,83,136,0.663,1684,761,494,3.041,Other,Relay Card,Parallel with output breaker,No Internal Battery (External Batteries Only),2702,Bypass Fuses  
 228,9355-30,9355-30kVA UPS  
 208V,208V,208V,216,50,3,27000,100,83,136,0.663,1684,761,494,7.768,Other,Relay Card,Parallel with output breaker,3X Battery Shelves9Ah (108 Batteries),2702,Bypass Fuses  
 229,9355-30,9355-30kVA UPS  
 208V,208V,208V,216,50,3,27000,100,83,136,0.663,1684,761,494,3.041,Other,Relay Card,R/T -  
 FAA (60 +/- 0.5 Hz) (no output breaker),No Internal Battery (External Batteries Only),2702,Bypass Fuses  
 230,9355-30,9355-30kVA UPS  
 208V,208V,208V,216,50,3,27000,100,83,136,0.663,1684,761,494,7.768,Other,Relay Card,R/T -  
 FAA (60 +/- 0.5 Hz) (no output breaker),3X Battery Shelves9Ah (108 Batteries),2702,Bypass Fuses  
 231,9355-30,9355-30kVA UPS  
 208V,208V,208V,216,50,3,27000,100,83,136,0.663,1684,761,494,3.041,Other,Industrial Relay Card,R/T (no output breaker),No Internal Battery (External Batteries Only),2702,Bypass Fuses  
 232,9355-30,9355-30kVA UPS  
 208V,208V,208V,216,50,3,27000,100,83,136,0.663,1684,761,494,7.768,Other,Industrial Relay Card,R/T (no output breaker),3X Battery Shelves9Ah (108 Batteries),2702,Bypass Fuses  
 233,9355-30,9355-30kVA UPS  
 208V,208V,208V,216,50,3,27000,100,83,136,0.663,1684,761,494,3.041,Other,Industrial Relay Card,Parallel (no output breaker),No Internal Battery (External Batteries Only),2702,Bypass Fuses  
 234,9355-30,9355-30kVA UPS  
 208V,208V,208V,216,50,3,27000,100,83,136,0.663,1684,761,494,7.768,Other,Industrial Relay Card,Parallel (no output breaker),3X Battery Shelves9Ah (108 Batteries),2702,Bypass Fuses  
 235,9355-30,9355-30kVA UPS  
 208V,208V,208V,216,50,3,27000,100,83,136,0.663,1684,761,494,3.041,Other,Industrial Relay Card,R/T with output breaker,No Internal Battery (External Batteries Only),2702,Bypass Fuses  
 236,9355-30,9355-30kVA UPS  
 208V,208V,208V,216,50,3,27000,100,83,136,0.663,1684,761,494,7.768,Other,Industrial Relay Card,R/T with output breaker,3X Battery Shelves9Ah (108 Batteries),2702,Bypass Fuses  
 237,9355-30,9355-30kVA UPS  
 208V,208V,208V,216,50,3,27000,100,83,136,0.663,1684,761,494,3.041,Other,Industrial Relay

Card,Parallel with output breaker,No Internal Battery (External Batteries Only),2702,Bypass Fuses  
 238,9355-30,9355-30kVA UPS  
 208V,208V,208V,216,50,3,27000,100,83,136,0.663,1684,761,494,7.768,Other,Industrial Relay  
 Card,Parallel with output breaker,3X Battery Shelves9Ah (108 Batteries),2702,Bypass Fuses  
 239,9355-30,9355-30kVA UPS  
 208V,208V,208V,216,50,3,27000,100,83,136,0.663,1684,761,494,3.041,Other,Industrial Relay  
 Card,R/T - FAA (60 +/- 0.5 Hz) (no output breaker),No Internal Battery (External Batteries Only),2702,Bypass Fuses  
 240,9355-30,9355-30kVA UPS  
 208V,208V,208V,216,50,3,27000,100,83,136,0.663,1684,761,494,7.768,Other,Industrial Relay  
 Card,R/T - FAA (60 +/- 0.5 Hz) (no output breaker),3X Battery Shelves9Ah (108 Batteries),2702,Bypass Fuses  
 241,9355-30,9355-30kVA UPS  
 208V,208V,208V,216,50,3,27000,100,83,136,0.663,1684,761,494,3.041,Other,Modem Card,R/T (no output breaker),No Internal Battery (External Batteries Only),2702,Bypass Fuses  
 242,9355-30,9355-30kVA UPS  
 208V,208V,208V,216,50,3,27000,100,83,136,0.663,1684,761,494,7.768,Other,Modem Card,R/T (no output breaker),3X Battery Shelves9Ah (108 Batteries),2702,Bypass Fuses  
 243,9355-30,9355-30kVA UPS  
 208V,208V,208V,216,50,3,27000,100,83,136,0.663,1684,761,494,3.041,Other,Modem Card,Parallel (no output breaker),No Internal Battery (External Batteries Only),2702,Bypass Fuses  
 244,9355-30,9355-30kVA UPS  
 208V,208V,208V,216,50,3,27000,100,83,136,0.663,1684,761,494,7.768,Other,Modem Card,Parallel (no output breaker),3X Battery Shelves9Ah (108 Batteries),2702,Bypass Fuses  
 245,9355-30,9355-30kVA UPS  
 208V,208V,208V,216,50,3,27000,100,83,136,0.663,1684,761,494,3.041,Other,Modem Card,R/T with output breaker,No Internal Battery (External Batteries Only),2702,Bypass Fuses  
 246,9355-30,9355-30kVA UPS  
 208V,208V,208V,216,50,3,27000,100,83,136,0.663,1684,761,494,7.768,Other,Modem Card,R/T with output breaker,3X Battery Shelves9Ah (108 Batteries),2702,Bypass Fuses  
 247,9355-30,9355-30kVA UPS  
 208V,208V,208V,216,50,3,27000,100,83,136,0.663,1684,761,494,3.041,Other,Modem Card,Parallel with output breaker,No Internal Battery (External Batteries Only),2702,Bypass Fuses  
 248,9355-30,9355-30kVA UPS  
 208V,208V,208V,216,50,3,27000,100,83,136,0.663,1684,761,494,7.768,Other,Modem Card,Parallel with output breaker,3X Battery Shelves9Ah (108 Batteries),2702,Bypass Fuses  
 249,9355-30,9355-30kVA UPS  
 208V,208V,208V,216,50,3,27000,100,83,136,0.663,1684,761,494,3.041,Other,Modem Card,R/T - FAA (60 +/- 0.5 Hz) (no output breaker),No Internal Battery (External Batteries Only),2702,Bypass Fuses  
 250,9355-30,9355-30kVA UPS  
 208V,208V,208V,216,50,3,27000,100,83,136,0.663,1684,761,494,7.768,Other,Modem Card,R/T - FAA (60 +/- 0.5 Hz) (no output breaker),3X Battery Shelves9Ah (108 Batteries),2702,Bypass Fuses  
 251,9355-30,9355-30kVA UPS  
 208V,208V,208V,216,60,3,27000,100,83,136,0.663,1684,761,494,3.041,Other,Power Expert Gateway Card,R/T (no output breaker),No Internal Battery (External Batteries Only),2702,Bypass Fuses  
 252,9355-30,9355-30kVA UPS  
 208V,208V,208V,216,60,3,27000,100,83,136,0.663,1684,761,494,7.768,Other,Power Expert Gateway Card,R/T (no output breaker),3X Battery Shelves9Ah (108 Batteries),2702,Bypass Fuses  
 253,9355-30,9355-30kVA UPS  
 208V,208V,208V,216,60,3,27000,100,83,136,0.663,1684,761,494,3.041,Other,Power Expert Gateway Card,Parallel (no output breaker),No Internal Battery (External Batteries Only),2702,Bypass Fuses  
 254,9355-30,9355-30kVA UPS  
 208V,208V,208V,216,60,3,27000,100,83,136,0.663,1684,761,494,7.768,Other,Power Expert Gateway Card,Parallel (no output breaker),3X Battery Shelves9Ah (108 Batteries),2702,Bypass Fuses

255,9355-30,9355-30kVA UPS  
 208V,208V,208V,216,60,3,27000,100,83,136,0.663,1684,761,494,3.041,Other,Power Expert Gateway Card,R/T with output breaker,No Internal Battery (External Batteries Only),2702,Bypass Fuses

256,9355-30,9355-30kVA UPS  
 208V,208V,208V,216,60,3,27000,100,83,136,0.663,1684,761,494,7.768,Other,Power Expert Gateway Card,R/T with output breaker,3X Battery Shelves9Ah (108 Batteries),2702,Bypass Fuses

257,9355-30,9355-30kVA UPS  
 208V,208V,208V,216,60,3,27000,100,83,136,0.663,1684,761,494,3.041,Other,Power Expert Gateway Card,Parallel with output breaker,No Internal Battery (External Batteries Only),2702,Bypass Fuses

258,9355-30,9355-30kVA UPS  
 208V,208V,208V,216,60,3,27000,100,83,136,0.663,1684,761,494,7.768,Other,Power Expert Gateway Card,Parallel with output breaker,3X Battery Shelves9Ah (108 Batteries),2702,Bypass Fuses

259,9355-30,9355-30kVA UPS  
 208V,208V,208V,216,60,3,27000,100,83,136,0.663,1684,761,494,3.041,Other,Power Expert Gateway Card,R/T - FAA (60 +/- 0.5 Hz) (no output breaker),No Internal Battery (External Batteries Only),2702,Bypass Fuses

260,9355-30,9355-30kVA UPS  
 208V,208V,208V,216,60,3,27000,100,83,136,0.663,1684,761,494,7.768,Other,Power Expert Gateway Card,R/T - FAA (60 +/- 0.5 Hz) (no output breaker),3X Battery Shelves9Ah (108 Batteries),2702,Bypass Fuses

261,9355-30,9355-30kVA UPS  
 208V,208V,208V,216,60,3,27000,100,83,136,0.663,1684,761,494,3.041,Other,Modbus Card,R/T (no output breaker),No Internal Battery (External Batteries Only),2702,Bypass Fuses

262,9355-30,9355-30kVA UPS  
 208V,208V,208V,216,60,3,27000,100,83,136,0.663,1684,761,494,7.768,Other,Modbus Card,R/T (no output breaker),3X Battery Shelves9Ah (108 Batteries),2702,Bypass Fuses

263,9355-30,9355-30kVA UPS  
 208V,208V,208V,216,60,3,27000,100,83,136,0.663,1684,761,494,3.041,Other,Modbus Card,Parallel (no output breaker),No Internal Battery (External Batteries Only),2702,Bypass Fuses

264,9355-30,9355-30kVA UPS  
 208V,208V,208V,216,60,3,27000,100,83,136,0.663,1684,761,494,7.768,Other,Modbus Card,Parallel (no output breaker),3X Battery Shelves9Ah (108 Batteries),2702,Bypass Fuses

265,9355-30,9355-30kVA UPS  
 208V,208V,208V,216,60,3,27000,100,83,136,0.663,1684,761,494,3.041,Other,Modbus Card,R/T with output breaker,No Internal Battery (External Batteries Only),2702,Bypass Fuses

266,9355-30,9355-30kVA UPS  
 208V,208V,208V,216,60,3,27000,100,83,136,0.663,1684,761,494,7.768,Other,Modbus Card,R/T with output breaker,3X Battery Shelves9Ah (108 Batteries),2702,Bypass Fuses

267,9355-30,9355-30kVA UPS  
 208V,208V,208V,216,60,3,27000,100,83,136,0.663,1684,761,494,3.041,Other,Modbus Card,Parallel with output breaker,No Internal Battery (External Batteries Only),2702,Bypass Fuses

268,9355-30,9355-30kVA UPS  
 208V,208V,208V,216,60,3,27000,100,83,136,0.663,1684,761,494,7.768,Other,Modbus Card,Parallel with output breaker,3X Battery Shelves9Ah (108 Batteries),2702,Bypass Fuses

269,9355-30,9355-30kVA UPS  
 208V,208V,208V,216,60,3,27000,100,83,136,0.663,1684,761,494,3.041,Other,Modbus Card,R/T - FAA (60 +/- 0.5 Hz) (no output breaker),No Internal Battery (External Batteries Only),2702,Bypass Fuses

270,9355-30,9355-30kVA UPS  
 208V,208V,208V,216,60,3,27000,100,83,136,0.663,1684,761,494,7.768,Other,Modbus Card,R/T - FAA (60 +/- 0.5 Hz) (no output breaker),3X Battery Shelves9Ah (108 Batteries),2702,Bypass Fuses

271,9355-30,9355-30kVA UPS  
 208V,208V,208V,216,60,3,27000,100,83,136,0.663,1684,761,494,3.041,Other,Relay Card,R/T (no output breaker),No Internal Battery (External Batteries Only),2702,Bypass Fuses

272,9355-30,9355-30kVA UPS  
 208V,208V,208V,216,60,3,27000,100,83,136,0.663,1684,761,494,7.768,Other,Relay Card,R/T (no output breaker),3X Battery Shelves9Ah (108 Batteries),2702,Bypass Fuses

273,9355-30,9355-30kVA UPS  
 208V,208V,208V,216,60,3,27000,100,83,136,0.663,1684,761,494,3.041,Other,Relay  
 Card,Parallel (no output breaker),No Internal Battery (External Batteries  
 Only),2702,Bypass Fuses  
 274,9355-30,9355-30kVA UPS  
 208V,208V,208V,216,60,3,27000,100,83,136,0.663,1684,761,494,7.768,Other,Relay  
 Card,Parallel (no output breaker),3X Battery Shelves9Ah (108 Batteries),2702,Bypass  
 Fuses  
 275,9355-30,9355-30kVA UPS  
 208V,208V,208V,216,60,3,27000,100,83,136,0.663,1684,761,494,3.041,Other,Relay Card,R/T  
 with output breaker,No Internal Battery (External Batteries Only),2702,Bypass Fuses  
 276,9355-30,9355-30kVA UPS  
 208V,208V,208V,216,60,3,27000,100,83,136,0.663,1684,761,494,7.768,Other,Relay Card,R/T  
 with output breaker,3X Battery Shelves9Ah (108 Batteries),2702,Bypass Fuses  
 277,9355-30,9355-30kVA UPS  
 208V,208V,208V,216,60,3,27000,100,83,136,0.663,1684,761,494,3.041,Other,Relay  
 Card,Parallel with output breaker,No Internal Battery (External Batteries  
 Only),2702,Bypass Fuses  
 278,9355-30,9355-30kVA UPS  
 208V,208V,208V,216,60,3,27000,100,83,136,0.663,1684,761,494,7.768,Other,Relay  
 Card,Parallel with output breaker,3X Battery Shelves9Ah (108 Batteries),2702,Bypass  
 Fuses  
 279,9355-30,9355-30kVA UPS  
 208V,208V,208V,216,60,3,27000,100,83,136,0.663,1684,761,494,3.041,Other,Relay Card,R/T -  
 FAA (60 +/- 0.5 Hz) (no output breaker),No Internal Battery (External Batteries  
 Only),2702,Bypass Fuses  
 280,9355-30,9355-30kVA UPS  
 208V,208V,208V,216,60,3,27000,100,83,136,0.663,1684,761,494,7.768,Other,Relay Card,R/T -  
 FAA (60 +/- 0.5 Hz) (no output breaker),3X Battery Shelves9Ah (108 Batteries),2702,Bypass  
 Fuses  
 281,9355-30,9355-30kVA UPS  
 208V,208V,208V,216,60,3,27000,100,83,136,0.663,1684,761,494,3.041,Other,Industrial Relay  
 Card,R/T (no output breaker),No Internal Battery (External Batteries Only),2702,Bypass  
 Fuses  
 282,9355-30,9355-30kVA UPS  
 208V,208V,208V,216,60,3,27000,100,83,136,0.663,1684,761,494,7.768,Other,Industrial Relay  
 Card,R/T (no output breaker),3X Battery Shelves9Ah (108 Batteries),2702,Bypass Fuses  
 283,9355-30,9355-30kVA UPS  
 208V,208V,208V,216,60,3,27000,100,83,136,0.663,1684,761,494,3.041,Other,Industrial Relay  
 Card,Parallel (no output breaker),No Internal Battery (External Batteries  
 Only),2702,Bypass Fuses  
 284,9355-30,9355-30kVA UPS  
 208V,208V,208V,216,60,3,27000,100,83,136,0.663,1684,761,494,7.768,Other,Industrial Relay  
 Card,Parallel (no output breaker),3X Battery Shelves9Ah (108 Batteries),2702,Bypass  
 Fuses  
 285,9355-30,9355-30kVA UPS  
 208V,208V,208V,216,60,3,27000,100,83,136,0.663,1684,761,494,3.041,Other,Industrial Relay  
 Card,R/T with output breaker,No Internal Battery (External Batteries Only),2702,Bypass  
 Fuses  
 286,9355-30,9355-30kVA UPS  
 208V,208V,208V,216,60,3,27000,100,83,136,0.663,1684,761,494,7.768,Other,Industrial Relay  
 Card,R/T with output breaker,3X Battery Shelves9Ah (108 Batteries),2702,Bypass Fuses  
 287,9355-30,9355-30kVA UPS  
 208V,208V,208V,216,60,3,27000,100,83,136,0.663,1684,761,494,3.041,Other,Industrial Relay  
 Card,Parallel with output breaker,No Internal Battery (External Batteries  
 Only),2702,Bypass Fuses  
 288,9355-30,9355-30kVA UPS  
 208V,208V,208V,216,60,3,27000,100,83,136,0.663,1684,761,494,7.768,Other,Industrial Relay  
 Card,Parallel with output breaker,3X Battery Shelves9Ah (108 Batteries),2702,Bypass  
 Fuses  
 289,9355-30,9355-30kVA UPS  
 208V,208V,208V,216,60,3,27000,100,83,136,0.663,1684,761,494,3.041,Other,Industrial Relay  
 Card,R/T - FAA (60 +/- 0.5 Hz) (no output breaker),No Internal Battery (External  
 Batteries Only),2702,Bypass Fuses  
 290,9355-30,9355-30kVA UPS  
 208V,208V,208V,216,60,3,27000,100,83,136,0.663,1684,761,494,7.768,Other,Industrial Relay



Card,R/T - FAA (60 +/- 0.5 Hz) (no output breaker),3X Battery Shelves9Ah (108 Batteries),2702,Bypass Fuses  
 291,9355-30,9355-30kVA UPS  
 208V,208V,208V,216,60,3,27000,100,83,136,0.663,1684,761,494,3.041,Other,Modem Card,R/T (no output breaker),No Internal Battery (External Batteries Only),2702,Bypass Fuses  
 292,9355-30,9355-30kVA UPS  
 208V,208V,208V,216,60,3,27000,100,83,136,0.663,1684,761,494,7.768,Other,Modem Card,R/T (no output breaker),3X Battery Shelves9Ah (108 Batteries),2702,Bypass Fuses  
 293,9355-30,9355-30kVA UPS  
 208V,208V,208V,216,60,3,27000,100,83,136,0.663,1684,761,494,3.041,Other,Modem Card,Parallel (no output breaker),No Internal Battery (External Batteries Only),2702,Bypass Fuses  
 294,9355-30,9355-30kVA UPS  
 208V,208V,208V,216,60,3,27000,100,83,136,0.663,1684,761,494,7.768,Other,Modem Card,Parallel (no output breaker),3X Battery Shelves9Ah (108 Batteries),2702,Bypass Fuses  
 295,9355-30,9355-30kVA UPS  
 208V,208V,208V,216,60,3,27000,100,83,136,0.663,1684,761,494,3.041,Other,Modem Card,R/T with output breaker,No Internal Battery (External Batteries Only),2702,Bypass Fuses  
 296,9355-30,9355-30kVA UPS  
 208V,208V,208V,216,60,3,27000,100,83,136,0.663,1684,761,494,7.768,Other,Modem Card,R/T with output breaker,3X Battery Shelves9Ah (108 Batteries),2702,Bypass Fuses  
 297,9355-30,9355-30kVA UPS  
 208V,208V,208V,216,60,3,27000,100,83,136,0.663,1684,761,494,3.041,Other,Modem Card,Parallel with output breaker,No Internal Battery (External Batteries Only),2702,Bypass Fuses  
 298,9355-30,9355-30kVA UPS  
 208V,208V,208V,216,60,3,27000,100,83,136,0.663,1684,761,494,7.768,Other,Modem Card,Parallel with output breaker,3X Battery Shelves9Ah (108 Batteries),2702,Bypass Fuses  
 299,9355-30,9355-30kVA UPS  
 208V,208V,208V,216,60,3,27000,100,83,136,0.663,1684,761,494,3.041,Other,Modem Card,R/T - FAA (60 +/- 0.5 Hz) (no output breaker),No Internal Battery (External Batteries Only),2702,Bypass Fuses  
 300,9355-30,9355-30kVA UPS  
 208V,208V,208V,216,60,3,27000,100,83,136,0.663,1684,761,494,7.768,Other,Modem Card,R/T - FAA (60 +/- 0.5 Hz) (no output breaker),3X Battery Shelves9Ah (108 Batteries),2702,Bypass Fuses  
 301,9355-30,9355-30kVA UPS  
 220V,220V,220V,216,50,3,27000,100,79,136,0.663,1684,761,494,3.041,Other,Power Expert Gateway Card,R/T (no output breaker),No Internal Battery (External Batteries Only),2702,Bypass Fuses  
 302,9355-30,9355-30kVA UPS  
 220V,220V,220V,216,50,3,27000,100,79,136,0.663,1684,761,494,7.768,Other,Power Expert Gateway Card,R/T (no output breaker),3X Battery Shelves9Ah (108 Batteries),2702,Bypass Fuses  
 303,9355-30,9355-30kVA UPS  
 220V,220V,220V,216,50,3,27000,100,79,136,0.663,1684,761,494,3.041,Other,Power Expert Gateway Card,Parallel (no output breaker),No Internal Battery (External Batteries Only),2702,Bypass Fuses  
 304,9355-30,9355-30kVA UPS  
 220V,220V,220V,216,50,3,27000,100,79,136,0.663,1684,761,494,7.768,Other,Power Expert Gateway Card,Parallel (no output breaker),3X Battery Shelves9Ah (108 Batteries),2702,Bypass Fuses  
 305,9355-30,9355-30kVA UPS  
 220V,220V,220V,216,50,3,27000,100,79,136,0.663,1684,761,494,3.041,Other,Power Expert Gateway Card,R/T with output breaker,No Internal Battery (External Batteries Only),2702,Bypass Fuses  
 306,9355-30,9355-30kVA UPS  
 220V,220V,220V,216,50,3,27000,100,79,136,0.663,1684,761,494,7.768,Other,Power Expert Gateway Card,R/T with output breaker,3X Battery Shelves9Ah (108 Batteries),2702,Bypass Fuses  
 307,9355-30,9355-30kVA UPS  
 220V,220V,220V,216,50,3,27000,100,79,136,0.663,1684,761,494,3.041,Other,Power Expert Gateway Card,Parallel with output breaker,No Internal Battery (External Batteries Only),2702,Bypass Fuses

308,9355-30,9355-30kVA UPS  
 220V,220V,220V,216,50,3,27000,100,79,136,0.663,1684,761,494,7.768,Other,Power Expert Gateway Card,Parallel with output breaker,3X Battery Shelves9Ah (108 Batteries),2702,Bypass Fuses

309,9355-30,9355-30kVA UPS  
 220V,220V,220V,216,50,3,27000,100,79,136,0.663,1684,761,494,3.041,Other,Power Expert Gateway Card,R/T - FAA (60 +/- 0.5 Hz) (no output breaker),No Internal Battery (External Batteries Only),2702,Bypass Fuses

310,9355-30,9355-30kVA UPS  
 220V,220V,220V,216,50,3,27000,100,79,136,0.663,1684,761,494,7.768,Other,Power Expert Gateway Card,R/T - FAA (60 +/- 0.5 Hz) (no output breaker),3X Battery Shelves9Ah (108 Batteries),2702,Bypass Fuses

311,9355-30,9355-30kVA UPS  
 220V,220V,220V,216,50,3,27000,100,79,136,0.663,1684,761,494,3.041,Other,Modbus Card,R/T (no output breaker),No Internal Battery (External Batteries Only),2702,Bypass Fuses

312,9355-30,9355-30kVA UPS  
 220V,220V,220V,216,50,3,27000,100,79,136,0.663,1684,761,494,7.768,Other,Modbus Card,R/T (no output breaker),3X Battery Shelves9Ah (108 Batteries),2702,Bypass Fuses

313,9355-30,9355-30kVA UPS  
 220V,220V,220V,216,50,3,27000,100,79,136,0.663,1684,761,494,3.041,Other,Modbus Card,Parallel (no output breaker),No Internal Battery (External Batteries Only),2702,Bypass Fuses

314,9355-30,9355-30kVA UPS  
 220V,220V,220V,216,50,3,27000,100,79,136,0.663,1684,761,494,7.768,Other,Modbus Card,Parallel (no output breaker),3X Battery Shelves9Ah (108 Batteries),2702,Bypass Fuses

315,9355-30,9355-30kVA UPS  
 220V,220V,220V,216,50,3,27000,100,79,136,0.663,1684,761,494,3.041,Other,Modbus Card,R/T with output breaker,No Internal Battery (External Batteries Only),2702,Bypass Fuses

316,9355-30,9355-30kVA UPS  
 220V,220V,220V,216,50,3,27000,100,79,136,0.663,1684,761,494,7.768,Other,Modbus Card,R/T with output breaker,3X Battery Shelves9Ah (108 Batteries),2702,Bypass Fuses

317,9355-30,9355-30kVA UPS  
 220V,220V,220V,216,50,3,27000,100,79,136,0.663,1684,761,494,3.041,Other,Modbus Card,Parallel with output breaker,No Internal Battery (External Batteries Only),2702,Bypass Fuses

318,9355-30,9355-30kVA UPS  
 220V,220V,220V,216,50,3,27000,100,79,136,0.663,1684,761,494,7.768,Other,Modbus Card,Parallel with output breaker,3X Battery Shelves9Ah (108 Batteries),2702,Bypass Fuses

319,9355-30,9355-30kVA UPS  
 220V,220V,220V,216,50,3,27000,100,79,136,0.663,1684,761,494,3.041,Other,Modbus Card,R/T - FAA (60 +/- 0.5 Hz) (no output breaker),No Internal Battery (External Batteries Only),2702,Bypass Fuses

320,9355-30,9355-30kVA UPS  
 220V,220V,220V,216,50,3,27000,100,79,136,0.663,1684,761,494,7.768,Other,Modbus Card,R/T - FAA (60 +/- 0.5 Hz) (no output breaker),3X Battery Shelves9Ah (108 Batteries),2702,Bypass Fuses

321,9355-30,9355-30kVA UPS  
 220V,220V,220V,216,50,3,27000,100,79,136,0.663,1684,761,494,3.041,Other,Relay Card,R/T (no output breaker),No Internal Battery (External Batteries Only),2702,Bypass Fuses

322,9355-30,9355-30kVA UPS  
 220V,220V,220V,216,50,3,27000,100,79,136,0.663,1684,761,494,7.768,Other,Relay Card,R/T (no output breaker),3X Battery Shelves9Ah (108 Batteries),2702,Bypass Fuses

323,9355-30,9355-30kVA UPS  
 220V,220V,220V,216,50,3,27000,100,79,136,0.663,1684,761,494,3.041,Other,Relay Card,Parallel (no output breaker),No Internal Battery (External Batteries Only),2702,Bypass Fuses

324,9355-30,9355-30kVA UPS  
 220V,220V,220V,216,50,3,27000,100,79,136,0.663,1684,761,494,7.768,Other,Relay Card,Parallel (no output breaker),3X Battery Shelves9Ah (108 Batteries),2702,Bypass Fuses

325,9355-30,9355-30kVA UPS  
 220V,220V,220V,216,50,3,27000,100,79,136,0.663,1684,761,494,3.041,Other,Relay Card,R/T with output breaker,No Internal Battery (External Batteries Only),2702,Bypass Fuses

326,9355-30,9355-30kVA UPS

220V,220V,220V,216,50,3,27000,100,79,136,0.663,1684,761,494,7.768,Other,Relay Card,R/T with output breaker,3X Battery Shelves9Ah (108 Batteries),2702,Bypass Fuses  
327,9355-30,9355-30kVA UPS

220V,220V,220V,216,50,3,27000,100,79,136,0.663,1684,761,494,3.041,Other,Relay Card,Parallel with output breaker,No Internal Battery (External Batteries Only),2702,Bypass Fuses  
328,9355-30,9355-30kVA UPS

220V,220V,220V,216,50,3,27000,100,79,136,0.663,1684,761,494,7.768,Other,Relay Card,Parallel with output breaker,3X Battery Shelves9Ah (108 Batteries),2702,Bypass Fuses  
329,9355-30,9355-30kVA UPS

220V,220V,220V,216,50,3,27000,100,79,136,0.663,1684,761,494,3.041,Other,Relay Card,R/T - FAA (60 +/- 0.5 Hz) (no output breaker),No Internal Battery (External Batteries Only),2702,Bypass Fuses  
330,9355-30,9355-30kVA UPS

220V,220V,220V,216,50,3,27000,100,79,136,0.663,1684,761,494,7.768,Other,Relay Card,R/T - FAA (60 +/- 0.5 Hz) (no output breaker),3X Battery Shelves9Ah (108 Batteries),2702,Bypass Fuses  
331,9355-30,9355-30kVA UPS

220V,220V,220V,216,50,3,27000,100,79,136,0.663,1684,761,494,3.041,Other,Industrial Relay Card,R/T (no output breaker),No Internal Battery (External Batteries Only),2702,Bypass Fuses  
332,9355-30,9355-30kVA UPS

220V,220V,220V,216,50,3,27000,100,79,136,0.663,1684,761,494,7.768,Other,Industrial Relay Card,R/T (no output breaker),3X Battery Shelves9Ah (108 Batteries),2702,Bypass Fuses  
333,9355-30,9355-30kVA UPS

220V,220V,220V,216,50,3,27000,100,79,136,0.663,1684,761,494,3.041,Other,Industrial Relay Card,Parallel (no output breaker),No Internal Battery (External Batteries Only),2702,Bypass Fuses  
334,9355-30,9355-30kVA UPS

220V,220V,220V,216,50,3,27000,100,79,136,0.663,1684,761,494,7.768,Other,Industrial Relay Card,Parallel (no output breaker),3X Battery Shelves9Ah (108 Batteries),2702,Bypass Fuses  
335,9355-30,9355-30kVA UPS

220V,220V,220V,216,50,3,27000,100,79,136,0.663,1684,761,494,3.041,Other,Industrial Relay Card,R/T with output breaker,No Internal Battery (External Batteries Only),2702,Bypass Fuses  
336,9355-30,9355-30kVA UPS

220V,220V,220V,216,50,3,27000,100,79,136,0.663,1684,761,494,7.768,Other,Industrial Relay Card,R/T with output breaker,3X Battery Shelves9Ah (108 Batteries),2702,Bypass Fuses  
337,9355-30,9355-30kVA UPS

220V,220V,220V,216,50,3,27000,100,79,136,0.663,1684,761,494,3.041,Other,Industrial Relay Card,Parallel with output breaker,No Internal Battery (External Batteries Only),2702,Bypass Fuses  
338,9355-30,9355-30kVA UPS

220V,220V,220V,216,50,3,27000,100,79,136,0.663,1684,761,494,7.768,Other,Industrial Relay Card,Parallel with output breaker,3X Battery Shelves9Ah (108 Batteries),2702,Bypass Fuses  
339,9355-30,9355-30kVA UPS

220V,220V,220V,216,50,3,27000,100,79,136,0.663,1684,761,494,3.041,Other,Industrial Relay Card,R/T - FAA (60 +/- 0.5 Hz) (no output breaker),No Internal Battery (External Batteries Only),2702,Bypass Fuses  
340,9355-30,9355-30kVA UPS

220V,220V,220V,216,50,3,27000,100,79,136,0.663,1684,761,494,7.768,Other,Industrial Relay Card,R/T - FAA (60 +/- 0.5 Hz) (no output breaker),3X Battery Shelves9Ah (108 Batteries),2702,Bypass Fuses  
341,9355-30,9355-30kVA UPS

220V,220V,220V,216,50,3,27000,100,79,136,0.663,1684,761,494,3.041,Other,Modem Card,R/T (no output breaker),No Internal Battery (External Batteries Only),2702,Bypass Fuses  
342,9355-30,9355-30kVA UPS

220V,220V,220V,216,50,3,27000,100,79,136,0.663,1684,761,494,7.768,Other,Modem Card,R/T (no output breaker),3X Battery Shelves9Ah (108 Batteries),2702,Bypass Fuses  
343,9355-30,9355-30kVA UPS

220V,220V,220V,216,50,3,27000,100,79,136,0.663,1684,761,494,3.041,Other,Modem Card,Parallel (no output breaker),No Internal Battery (External Batteries Only),2702,Bypass Fuses

344,9355-30,9355-30kVA UPS  
220V,220V,220V,216,50,3,27000,100,79,136,0.663,1684,761,494,7.768,Other,Modem Card,Parallel (no output breaker),3X Battery Shelves9Ah (108 Batteries),2702,Bypass Fuses

345,9355-30,9355-30kVA UPS  
220V,220V,220V,216,50,3,27000,100,79,136,0.663,1684,761,494,3.041,Other,Modem Card,R/T with output breaker,No Internal Battery (External Batteries Only),2702,Bypass Fuses

346,9355-30,9355-30kVA UPS  
220V,220V,220V,216,50,3,27000,100,79,136,0.663,1684,761,494,7.768,Other,Modem Card,R/T with output breaker,3X Battery Shelves9Ah (108 Batteries),2702,Bypass Fuses

347,9355-30,9355-30kVA UPS  
220V,220V,220V,216,50,3,27000,100,79,136,0.663,1684,761,494,3.041,Other,Modem Card,Parallel with output breaker,No Internal Battery (External Batteries Only),2702,Bypass Fuses

348,9355-30,9355-30kVA UPS  
220V,220V,220V,216,50,3,27000,100,79,136,0.663,1684,761,494,7.768,Other,Modem Card,Parallel with output breaker,3X Battery Shelves9Ah (108 Batteries),2702,Bypass Fuses

349,9355-30,9355-30kVA UPS  
220V,220V,220V,216,50,3,27000,100,79,136,0.663,1684,761,494,3.041,Other,Modem Card,R/T - FAA (60 +/- 0.5 Hz) (no output breaker),No Internal Battery (External Batteries Only),2702,Bypass Fuses

350,9355-30,9355-30kVA UPS  
220V,220V,220V,216,50,3,27000,100,79,136,0.663,1684,761,494,7.768,Other,Modem Card,R/T - FAA (60 +/- 0.5 Hz) (no output breaker),3X Battery Shelves9Ah (108 Batteries),2702,Bypass Fuses

351,9355-30,9355-30kVA UPS  
220V,220V,220V,216,60,3,27000,100,79,136,0.663,1684,761,494,3.041,Other,Power Expert Gateway Card,R/T (no output breaker),No Internal Battery (External Batteries Only),2702,Bypass Fuses

352,9355-30,9355-30kVA UPS  
220V,220V,220V,216,60,3,27000,100,79,136,0.663,1684,761,494,7.768,Other,Power Expert Gateway Card,R/T (no output breaker),3X Battery Shelves9Ah (108 Batteries),2702,Bypass Fuses

353,9355-30,9355-30kVA UPS  
220V,220V,220V,216,60,3,27000,100,79,136,0.663,1684,761,494,3.041,Other,Power Expert Gateway Card,Parallel (no output breaker),No Internal Battery (External Batteries Only),2702,Bypass Fuses

354,9355-30,9355-30kVA UPS  
220V,220V,220V,216,60,3,27000,100,79,136,0.663,1684,761,494,7.768,Other,Power Expert Gateway Card,Parallel (no output breaker),3X Battery Shelves9Ah (108 Batteries),2702,Bypass Fuses

355,9355-30,9355-30kVA UPS  
220V,220V,220V,216,60,3,27000,100,79,136,0.663,1684,761,494,3.041,Other,Power Expert Gateway Card,R/T with output breaker,No Internal Battery (External Batteries Only),2702,Bypass Fuses

356,9355-30,9355-30kVA UPS  
220V,220V,220V,216,60,3,27000,100,79,136,0.663,1684,761,494,7.768,Other,Power Expert Gateway Card,R/T with output breaker,3X Battery Shelves9Ah (108 Batteries),2702,Bypass Fuses

357,9355-30,9355-30kVA UPS  
220V,220V,220V,216,60,3,27000,100,79,136,0.663,1684,761,494,3.041,Other,Power Expert Gateway Card,Parallel with output breaker,No Internal Battery (External Batteries Only),2702,Bypass Fuses

358,9355-30,9355-30kVA UPS  
220V,220V,220V,216,60,3,27000,100,79,136,0.663,1684,761,494,7.768,Other,Power Expert Gateway Card,Parallel with output breaker,3X Battery Shelves9Ah (108 Batteries),2702,Bypass Fuses

359,9355-30,9355-30kVA UPS  
220V,220V,220V,216,60,3,27000,100,79,136,0.663,1684,761,494,3.041,Other,Power Expert Gateway Card,R/T - FAA (60 +/- 0.5 Hz) (no output breaker),No Internal Battery (External Batteries Only),2702,Bypass Fuses

360,9355-30,9355-30kVA UPS  
220V,220V,220V,216,60,3,27000,100,79,136,0.663,1684,761,494,7.768,Other,Power Expert Gateway Card,R/T - FAA (60 +/- 0.5 Hz) (no output breaker),3X Battery Shelves9Ah (108 Batteries),2702,Bypass Fuses

361,9355-30,9355-30kVA UPS  
 220V,220V,220V,216,60,3,27000,100,79,136,0.663,1684,761,494,3.041,Other,Modbus Card,R/T  
 (no output breaker),No Internal Battery (External Batteries Only),2702,Bypass Fuses

362,9355-30,9355-30kVA UPS  
 220V,220V,220V,216,60,3,27000,100,79,136,0.663,1684,761,494,7.768,Other,Modbus Card,R/T  
 (no output breaker),3X Battery Shelves9Ah (108 Batteries),2702,Bypass Fuses

363,9355-30,9355-30kVA UPS  
 220V,220V,220V,216,60,3,27000,100,79,136,0.663,1684,761,494,3.041,Other,Modbus  
 Card,Parallel (no output breaker),No Internal Battery (External Batteries  
 Only),2702,Bypass Fuses

364,9355-30,9355-30kVA UPS  
 220V,220V,220V,216,60,3,27000,100,79,136,0.663,1684,761,494,7.768,Other,Modbus  
 Card,Parallel (no output breaker),3X Battery Shelves9Ah (108 Batteries),2702,Bypass  
 Fuses

365,9355-30,9355-30kVA UPS  
 220V,220V,220V,216,60,3,27000,100,79,136,0.663,1684,761,494,3.041,Other,Modbus Card,R/T  
 with output breaker,No Internal Battery (External Batteries Only),2702,Bypass Fuses

366,9355-30,9355-30kVA UPS  
 220V,220V,220V,216,60,3,27000,100,79,136,0.663,1684,761,494,7.768,Other,Modbus Card,R/T  
 with output breaker,3X Battery Shelves9Ah (108 Batteries),2702,Bypass Fuses

367,9355-30,9355-30kVA UPS  
 220V,220V,220V,216,60,3,27000,100,79,136,0.663,1684,761,494,3.041,Other,Modbus  
 Card,Parallel with output breaker,No Internal Battery (External Batteries  
 Only),2702,Bypass Fuses

368,9355-30,9355-30kVA UPS  
 220V,220V,220V,216,60,3,27000,100,79,136,0.663,1684,761,494,7.768,Other,Modbus  
 Card,Parallel with output breaker,3X Battery Shelves9Ah (108 Batteries),2702,Bypass  
 Fuses

369,9355-30,9355-30kVA UPS  
 220V,220V,220V,216,60,3,27000,100,79,136,0.663,1684,761,494,3.041,Other,Modbus Card,R/T -  
 FAA (60 +/- 0.5 Hz) (no output breaker),No Internal Battery (External Batteries  
 Only),2702,Bypass Fuses

370,9355-30,9355-30kVA UPS  
 220V,220V,220V,216,60,3,27000,100,79,136,0.663,1684,761,494,7.768,Other,Modbus Card,R/T -  
 FAA (60 +/- 0.5 Hz) (no output breaker),3X Battery Shelves9Ah (108 Batteries),2702,Bypass  
 Fuses

371,9355-30,9355-30kVA UPS  
 220V,220V,220V,216,60,3,27000,100,79,136,0.663,1684,761,494,3.041,Other,Relay Card,R/T  
 (no output breaker),No Internal Battery (External Batteries Only),2702,Bypass Fuses

372,9355-30,9355-30kVA UPS  
 220V,220V,220V,216,60,3,27000,100,79,136,0.663,1684,761,494,7.768,Other,Relay Card,R/T  
 (no output breaker),3X Battery Shelves9Ah (108 Batteries),2702,Bypass Fuses

373,9355-30,9355-30kVA UPS  
 220V,220V,220V,216,60,3,27000,100,79,136,0.663,1684,761,494,3.041,Other,Relay  
 Card,Parallel (no output breaker),No Internal Battery (External Batteries  
 Only),2702,Bypass Fuses

374,9355-30,9355-30kVA UPS  
 220V,220V,220V,216,60,3,27000,100,79,136,0.663,1684,761,494,7.768,Other,Relay  
 Card,Parallel (no output breaker),3X Battery Shelves9Ah (108 Batteries),2702,Bypass  
 Fuses

375,9355-30,9355-30kVA UPS  
 220V,220V,220V,216,60,3,27000,100,79,136,0.663,1684,761,494,3.041,Other,Relay Card,R/T  
 with output breaker,No Internal Battery (External Batteries Only),2702,Bypass Fuses

376,9355-30,9355-30kVA UPS  
 220V,220V,220V,216,60,3,27000,100,79,136,0.663,1684,761,494,7.768,Other,Relay Card,R/T  
 with output breaker,3X Battery Shelves9Ah (108 Batteries),2702,Bypass Fuses

377,9355-30,9355-30kVA UPS  
 220V,220V,220V,216,60,3,27000,100,79,136,0.663,1684,761,494,3.041,Other,Relay  
 Card,Parallel with output breaker,No Internal Battery (External Batteries  
 Only),2702,Bypass Fuses

378,9355-30,9355-30kVA UPS  
 220V,220V,220V,216,60,3,27000,100,79,136,0.663,1684,761,494,7.768,Other,Relay  
 Card,Parallel with output breaker,3X Battery Shelves9Ah (108 Batteries),2702,Bypass  
 Fuses

379,9355-30,9355-30kVA UPS  
 220V,220V,220V,216,60,3,27000,100,79,136,0.663,1684,761,494,3.041,Other,Relay Card,R/T -

FAA (60 +/- 0.5 Hz) (no output breaker),No Internal Battery (External Batteries Only),2702,Bypass Fuses  
 380,9355-30,9355-30kVA UPS  
 220V,220V,220V,216,60,3,27000,100,79,136,0.663,1684,761,494,7.768,Other,Relay Card,R/T - FAA (60 +/- 0.5 Hz) (no output breaker),3X Battery Shelves9Ah (108 Batteries),2702,Bypass Fuses  
 381,9355-30,9355-30kVA UPS  
 220V,220V,220V,216,60,3,27000,100,79,136,0.663,1684,761,494,3.041,Other,Industrial Relay Card,R/T (no output breaker),No Internal Battery (External Batteries Only),2702,Bypass Fuses  
 382,9355-30,9355-30kVA UPS  
 220V,220V,220V,216,60,3,27000,100,79,136,0.663,1684,761,494,7.768,Other,Industrial Relay Card,R/T (no output breaker),3X Battery Shelves9Ah (108 Batteries),2702,Bypass Fuses  
 383,9355-30,9355-30kVA UPS  
 220V,220V,220V,216,60,3,27000,100,79,136,0.663,1684,761,494,3.041,Other,Industrial Relay Card,Parallel (no output breaker),No Internal Battery (External Batteries Only),2702,Bypass Fuses  
 384,9355-30,9355-30kVA UPS  
 220V,220V,220V,216,60,3,27000,100,79,136,0.663,1684,761,494,7.768,Other,Industrial Relay Card,Parallel (no output breaker),3X Battery Shelves9Ah (108 Batteries),2702,Bypass Fuses  
 385,9355-30,9355-30kVA UPS  
 220V,220V,220V,216,60,3,27000,100,79,136,0.663,1684,761,494,3.041,Other,Industrial Relay Card,R/T with output breaker,No Internal Battery (External Batteries Only),2702,Bypass Fuses  
 386,9355-30,9355-30kVA UPS  
 220V,220V,220V,216,60,3,27000,100,79,136,0.663,1684,761,494,7.768,Other,Industrial Relay Card,R/T with output breaker,3X Battery Shelves9Ah (108 Batteries),2702,Bypass Fuses  
 387,9355-30,9355-30kVA UPS  
 220V,220V,220V,216,60,3,27000,100,79,136,0.663,1684,761,494,3.041,Other,Industrial Relay Card,Parallel with output breaker,No Internal Battery (External Batteries Only),2702,Bypass Fuses  
 388,9355-30,9355-30kVA UPS  
 220V,220V,220V,216,60,3,27000,100,79,136,0.663,1684,761,494,7.768,Other,Industrial Relay Card,Parallel with output breaker,3X Battery Shelves9Ah (108 Batteries),2702,Bypass Fuses  
 389,9355-30,9355-30kVA UPS  
 220V,220V,220V,216,60,3,27000,100,79,136,0.663,1684,761,494,3.041,Other,Industrial Relay Card,R/T - FAA (60 +/- 0.5 Hz) (no output breaker),No Internal Battery (External Batteries Only),2702,Bypass Fuses  
 390,9355-30,9355-30kVA UPS  
 220V,220V,220V,216,60,3,27000,100,79,136,0.663,1684,761,494,7.768,Other,Industrial Relay Card,R/T - FAA (60 +/- 0.5 Hz) (no output breaker),3X Battery Shelves9Ah (108 Batteries),2702,Bypass Fuses  
 391,9355-30,9355-30kVA UPS  
 220V,220V,220V,216,60,3,27000,100,79,136,0.663,1684,761,494,3.041,Other,Modem Card,R/T (no output breaker),No Internal Battery (External Batteries Only),2702,Bypass Fuses  
 392,9355-30,9355-30kVA UPS  
 220V,220V,220V,216,60,3,27000,100,79,136,0.663,1684,761,494,7.768,Other,Modem Card,R/T (no output breaker),3X Battery Shelves9Ah (108 Batteries),2702,Bypass Fuses  
 393,9355-30,9355-30kVA UPS  
 220V,220V,220V,216,60,3,27000,100,79,136,0.663,1684,761,494,3.041,Other,Modem Card,Parallel (no output breaker),No Internal Battery (External Batteries Only),2702,Bypass Fuses  
 394,9355-30,9355-30kVA UPS  
 220V,220V,220V,216,60,3,27000,100,79,136,0.663,1684,761,494,7.768,Other,Modem Card,Parallel (no output breaker),3X Battery Shelves9Ah (108 Batteries),2702,Bypass Fuses  
 395,9355-30,9355-30kVA UPS  
 220V,220V,220V,216,60,3,27000,100,79,136,0.663,1684,761,494,3.041,Other,Modem Card,R/T with output breaker,No Internal Battery (External Batteries Only),2702,Bypass Fuses  
 396,9355-30,9355-30kVA UPS  
 220V,220V,220V,216,60,3,27000,100,79,136,0.663,1684,761,494,7.768,Other,Modem Card,R/T with output breaker,3X Battery Shelves9Ah (108 Batteries),2702,Bypass Fuses  
 397,9355-30,9355-30kVA UPS  
 220V,220V,220V,216,60,3,27000,100,79,136,0.663,1684,761,494,3.041,Other,Modem

Card,Parallel with output breaker,No Internal Battery (External Batteries Only),2702,Bypass Fuses  
 398,9355-30,9355-30kVA UPS  
 220V,220V,220V,216,60,3,27000,100,79,136,0.663,1684,761,494,7.768,Other,Modem  
 Card,Parallel with output breaker,3X Battery Shelves9Ah (108 Batteries),2702,Bypass Fuses  
 399,9355-30,9355-30kVA UPS  
 220V,220V,220V,216,60,3,27000,100,79,136,0.663,1684,761,494,3.041,Other,Modem Card,R/T - FAA (60 +/- 0.5 Hz) (no output breaker),No Internal Battery (External Batteries Only),2702,Bypass Fuses  
 400,9355-30,9355-30kVA UPS  
 220V,220V,220V,216,60,3,27000,100,79,136,0.663,1684,761,494,7.768,Other,Modem Card,R/T - FAA (60 +/- 0.5 Hz) (no output breaker),3X Battery Shelves9Ah (108 Batteries),2702,Bypass Fuses  
 401,BH20KEL2083P100,9355-18kVA UL 924  
 UPS,208V,208V,216,60,3,18000,100,50,91,0.663,1684,761,494,3.041,Yes,Power Expert Gateway Card,R/T (no output breaker),No Internal Battery (External Batteries Only),1981,Bypass Fuses  
 402,BH20KEL2083P100,9355-18kVA UL 924  
 UPS,208V,208V,216,60,3,18000,100,50,91,0.663,1684,761,494,7.768,Yes,Power Expert Gateway Card,R/T (no output breaker),3X Battery Shelves9Ah (108 Batteries),1981,Bypass Fuses  
 403,BH20KEL2083P100,9355-18kVA UL 924  
 UPS,208V,208V,216,60,3,18000,100,50,91,0.663,1684,761,494,3.041,Yes,Power Expert Gateway Card,Parallel (no output breaker),No Internal Battery (External Batteries Only),1981,Bypass Fuses  
 404,BH20KEL2083P100,9355-18kVA UL 924  
 UPS,208V,208V,216,60,3,18000,100,50,91,0.663,1684,761,494,7.768,Yes,Power Expert Gateway Card,Parallel (no output breaker),3X Battery Shelves9Ah (108 Batteries),1981,Bypass Fuses  
 405,BH20KEL2083P100,9355-18kVA UL 924  
 UPS,208V,208V,216,60,3,18000,100,50,91,0.663,1684,761,494,3.041,Yes,Power Expert Gateway Card,R/T with output breaker,No Internal Battery (External Batteries Only),1981,Bypass Fuses  
 406,BH20KEL2083P100,9355-18kVA UL 924  
 UPS,208V,208V,216,60,3,18000,100,50,91,0.663,1684,761,494,7.768,Yes,Power Expert Gateway Card,R/T with output breaker,3X Battery Shelves9Ah (108 Batteries),1981,Bypass Fuses  
 407,BH20KEL2083P100,9355-18kVA UL 924  
 UPS,208V,208V,216,60,3,18000,100,50,91,0.663,1684,761,494,3.041,Yes,Power Expert Gateway Card,Parallel with output breaker,No Internal Battery (External Batteries Only),1981,Bypass Fuses  
 408,BH20KEL2083P100,9355-18kVA UL 924  
 UPS,208V,208V,216,60,3,18000,100,50,91,0.663,1684,761,494,7.768,Yes,Power Expert Gateway Card,Parallel with output breaker,3X Battery Shelves9Ah (108 Batteries),1981,Bypass Fuses  
 409,BH20KEL2083P100,9355-18kVA UL 924  
 UPS,208V,208V,216,60,3,18000,100,50,91,0.663,1684,761,494,3.041,Yes,Power Expert Gateway Card,R/T - FAA (60 +/- 0.5 Hz) (no output breaker),No Internal Battery (External Batteries Only),1981,Bypass Fuses  
 410,BH20KEL2083P100,9355-18kVA UL 924  
 UPS,208V,208V,216,60,3,18000,100,50,91,0.663,1684,761,494,7.768,Yes,Power Expert Gateway Card,R/T - FAA (60 +/- 0.5 Hz) (no output breaker),3X Battery Shelves9Ah (108 Batteries),1981,Bypass Fuses  
 411,BH20KEL2083P100,9355-18kVA UL 924  
 UPS,208V,208V,216,60,3,18000,100,50,91,0.663,1684,761,494,3.041,Yes,Modbus Card,R/T (no output breaker),No Internal Battery (External Batteries Only),1981,Bypass Fuses  
 412,BH20KEL2083P100,9355-18kVA UL 924  
 UPS,208V,208V,216,60,3,18000,100,50,91,0.663,1684,761,494,7.768,Yes,Modbus Card,R/T (no output breaker),3X Battery Shelves9Ah (108 Batteries),1981,Bypass Fuses  
 413,BH20KEL2083P100,9355-18kVA UL 924  
 UPS,208V,208V,216,60,3,18000,100,50,91,0.663,1684,761,494,3.041,Yes,Modbus Card,Parallel (no output breaker),No Internal Battery (External Batteries Only),1981,Bypass Fuses  
 414,BH20KEL2083P100,9355-18kVA UL 924  
 UPS,208V,208V,216,60,3,18000,100,50,91,0.663,1684,761,494,7.768,Yes,Modbus Card,Parallel (no output breaker),3X Battery Shelves9Ah (108 Batteries),1981,Bypass Fuses  
 415,BH20KEL2083P100,9355-18kVA UL 924  
 UPS,208V,208V,216,60,3,18000,100,50,91,0.663,1684,761,494,3.041,Yes,Modbus Card,R/T with

output breaker, No Internal Battery (External Batteries Only), 1981, Bypass Fuses  
 416, BH20KEL2083P100, 9355-18kVA UL 924  
 UPS, 208V, 208V, 216, 60, 3, 18000, 100, 50, 91, 0.663, 1684, 761, 494, 7.768, Yes, Modbus Card, R/T with  
 output breaker, 3X Battery Shelves 9Ah (108 Batteries), 1981, Bypass Fuses  
 417, BH20KEL2083P100, 9355-18kVA UL 924  
 UPS, 208V, 208V, 216, 60, 3, 18000, 100, 50, 91, 0.663, 1684, 761, 494, 3.041, Yes, Modbus Card, Parallel  
 with output breaker, No Internal Battery (External Batteries Only), 1981, Bypass Fuses  
 418, BH20KEL2083P100, 9355-18kVA UL 924  
 UPS, 208V, 208V, 216, 60, 3, 18000, 100, 50, 91, 0.663, 1684, 761, 494, 7.768, Yes, Modbus Card, Parallel  
 with output breaker, 3X Battery Shelves 9Ah (108 Batteries), 1981, Bypass Fuses  
 419, BH20KEL2083P100, 9355-18kVA UL 924  
 UPS, 208V, 208V, 216, 60, 3, 18000, 100, 50, 91, 0.663, 1684, 761, 494, 3.041, Yes, Modbus Card, R/T - FAA  
 (60 +/- 0.5 Hz) (no output breaker), No Internal Battery (External Batteries  
 Only), 1981, Bypass Fuses  
 420, BH20KEL2083P100, 9355-18kVA UL 924  
 UPS, 208V, 208V, 216, 60, 3, 18000, 100, 50, 91, 0.663, 1684, 761, 494, 7.768, Yes, Modbus Card, R/T - FAA  
 (60 +/- 0.5 Hz) (no output breaker), 3X Battery Shelves 9Ah (108 Batteries), 1981, Bypass  
 Fuses  
 421, BH20KEL2083P100, 9355-18kVA UL 924  
 UPS, 208V, 208V, 216, 60, 3, 18000, 100, 50, 91, 0.663, 1684, 761, 494, 3.041, Yes, Relay Card, R/T (no  
 output breaker), No Internal Battery (External Batteries Only), 1981, Bypass Fuses  
 422, BH20KEL2083P100, 9355-18kVA UL 924  
 UPS, 208V, 208V, 216, 60, 3, 18000, 100, 50, 91, 0.663, 1684, 761, 494, 7.768, Yes, Relay Card, R/T (no  
 output breaker), 3X Battery Shelves 9Ah (108 Batteries), 1981, Bypass Fuses  
 423, BH20KEL2083P100, 9355-18kVA UL 924  
 UPS, 208V, 208V, 216, 60, 3, 18000, 100, 50, 91, 0.663, 1684, 761, 494, 3.041, Yes, Relay Card, Parallel  
 (no output breaker), No Internal Battery (External Batteries Only), 1981, Bypass Fuses  
 424, BH20KEL2083P100, 9355-18kVA UL 924  
 UPS, 208V, 208V, 216, 60, 3, 18000, 100, 50, 91, 0.663, 1684, 761, 494, 7.768, Yes, Relay Card, Parallel  
 (no output breaker), 3X Battery Shelves 9Ah (108 Batteries), 1981, Bypass Fuses  
 425, BH20KEL2083P100, 9355-18kVA UL 924  
 UPS, 208V, 208V, 216, 60, 3, 18000, 100, 50, 91, 0.663, 1684, 761, 494, 3.041, Yes, Relay Card, R/T with  
 output breaker, No Internal Battery (External Batteries Only), 1981, Bypass Fuses  
 426, BH20KEL2083P100, 9355-18kVA UL 924  
 UPS, 208V, 208V, 216, 60, 3, 18000, 100, 50, 91, 0.663, 1684, 761, 494, 7.768, Yes, Relay Card, R/T with  
 output breaker, 3X Battery Shelves 9Ah (108 Batteries), 1981, Bypass Fuses  
 427, BH20KEL2083P100, 9355-18kVA UL 924  
 UPS, 208V, 208V, 216, 60, 3, 18000, 100, 50, 91, 0.663, 1684, 761, 494, 3.041, Yes, Relay Card, Parallel  
 with output breaker, No Internal Battery (External Batteries Only), 1981, Bypass Fuses  
 428, BH20KEL2083P100, 9355-18kVA UL 924  
 UPS, 208V, 208V, 216, 60, 3, 18000, 100, 50, 91, 0.663, 1684, 761, 494, 7.768, Yes, Relay Card, Parallel  
 with output breaker, 3X Battery Shelves 9Ah (108 Batteries), 1981, Bypass Fuses  
 429, BH20KEL2083P100, 9355-18kVA UL 924  
 UPS, 208V, 208V, 216, 60, 3, 18000, 100, 50, 91, 0.663, 1684, 761, 494, 3.041, Yes, Relay Card, R/T - FAA  
 (60 +/- 0.5 Hz) (no output breaker), No Internal Battery (External Batteries  
 Only), 1981, Bypass Fuses  
 430, BH20KEL2083P100, 9355-18kVA UL 924  
 UPS, 208V, 208V, 216, 60, 3, 18000, 100, 50, 91, 0.663, 1684, 761, 494, 7.768, Yes, Relay Card, R/T - FAA  
 (60 +/- 0.5 Hz) (no output breaker), 3X Battery Shelves 9Ah (108 Batteries), 1981, Bypass  
 Fuses  
 431, BH20KEL2083P100, 9355-18kVA UL 924  
 UPS, 208V, 208V, 216, 60, 3, 18000, 100, 50, 91, 0.663, 1684, 761, 494, 3.041, Yes, Industrial Relay  
 Card, R/T (no output breaker), No Internal Battery (External Batteries Only), 1981, Bypass  
 Fuses  
 432, BH20KEL2083P100, 9355-18kVA UL 924  
 UPS, 208V, 208V, 216, 60, 3, 18000, 100, 50, 91, 0.663, 1684, 761, 494, 7.768, Yes, Industrial Relay  
 Card, R/T (no output breaker), 3X Battery Shelves 9Ah (108 Batteries), 1981, Bypass Fuses  
 433, BH20KEL2083P100, 9355-18kVA UL 924  
 UPS, 208V, 208V, 216, 60, 3, 18000, 100, 50, 91, 0.663, 1684, 761, 494, 3.041, Yes, Industrial Relay  
 Card, Parallel (no output breaker), No Internal Battery (External Batteries  
 Only), 1981, Bypass Fuses  
 434, BH20KEL2083P100, 9355-18kVA UL 924  
 UPS, 208V, 208V, 216, 60, 3, 18000, 100, 50, 91, 0.663, 1684, 761, 494, 7.768, Yes, Industrial Relay  
 Card, Parallel (no output breaker), 3X Battery Shelves 9Ah (108 Batteries), 1981, Bypass  
 Fuses  
 435, BH20KEL2083P100, 9355-18kVA UL 924



UPS,208V,208V,216,60,3,18000,100,50,91,0.663,1684,761,494,3.041,Yes,Industrial Relay Card,R/T with output breaker,No Internal Battery (External Batteries Only),1981,Bypass Fuses  
436,BH20KEL2083P100,9355-18kVA UL 924  
UPS,208V,208V,216,60,3,18000,100,50,91,0.663,1684,761,494,7.768,Yes,Industrial Relay Card,R/T with output breaker,3X Battery Shelves9Ah (108 Batteries),1981,Bypass Fuses  
437,BH20KEL2083P100,9355-18kVA UL 924  
UPS,208V,208V,216,60,3,18000,100,50,91,0.663,1684,761,494,3.041,Yes,Industrial Relay Card,Parallel with output breaker,No Internal Battery (External Batteries Only),1981,Bypass Fuses  
438,BH20KEL2083P100,9355-18kVA UL 924  
UPS,208V,208V,216,60,3,18000,100,50,91,0.663,1684,761,494,7.768,Yes,Industrial Relay Card,Parallel with output breaker,3X Battery Shelves9Ah (108 Batteries),1981,Bypass Fuses  
439,BH20KEL2083P100,9355-18kVA UL 924  
UPS,208V,208V,216,60,3,18000,100,50,91,0.663,1684,761,494,3.041,Yes,Industrial Relay Card,R/T - FAA (60 +/- 0.5 Hz) (no output breaker),No Internal Battery (External Batteries Only),1981,Bypass Fuses  
440,BH20KEL2083P100,9355-18kVA UL 924  
UPS,208V,208V,216,60,3,18000,100,50,91,0.663,1684,761,494,7.768,Yes,Industrial Relay Card,R/T - FAA (60 +/- 0.5 Hz) (no output breaker),3X Battery Shelves9Ah (108 Batteries),1981,Bypass Fuses  
441,BH20KEL2083P100,9355-18kVA UL 924  
UPS,208V,208V,216,60,3,18000,100,50,91,0.663,1684,761,494,3.041,Yes,Modem Card,R/T (no output breaker),No Internal Battery (External Batteries Only),1981,Bypass Fuses  
442,BH20KEL2083P100,9355-18kVA UL 924  
UPS,208V,208V,216,60,3,18000,100,50,91,0.663,1684,761,494,7.768,Yes,Modem Card,R/T (no output breaker),3X Battery Shelves9Ah (108 Batteries),1981,Bypass Fuses  
443,BH20KEL2083P100,9355-18kVA UL 924  
UPS,208V,208V,216,60,3,18000,100,50,91,0.663,1684,761,494,3.041,Yes,Modem Card,Parallel (no output breaker),No Internal Battery (External Batteries Only),1981,Bypass Fuses  
444,BH20KEL2083P100,9355-18kVA UL 924  
UPS,208V,208V,216,60,3,18000,100,50,91,0.663,1684,761,494,7.768,Yes,Modem Card,Parallel (no output breaker),3X Battery Shelves9Ah (108 Batteries),1981,Bypass Fuses  
445,BH20KEL2083P100,9355-18kVA UL 924  
UPS,208V,208V,216,60,3,18000,100,50,91,0.663,1684,761,494,3.041,Yes,Modem Card,R/T with output breaker,No Internal Battery (External Batteries Only),1981,Bypass Fuses  
446,BH20KEL2083P100,9355-18kVA UL 924  
UPS,208V,208V,216,60,3,18000,100,50,91,0.663,1684,761,494,7.768,Yes,Modem Card,R/T with output breaker,3X Battery Shelves9Ah (108 Batteries),1981,Bypass Fuses  
447,BH20KEL2083P100,9355-18kVA UL 924  
UPS,208V,208V,216,60,3,18000,100,50,91,0.663,1684,761,494,3.041,Yes,Modem Card,Parallel with output breaker,No Internal Battery (External Batteries Only),1981,Bypass Fuses  
448,BH20KEL2083P100,9355-18kVA UL 924  
UPS,208V,208V,216,60,3,18000,100,50,91,0.663,1684,761,494,7.768,Yes,Modem Card,Parallel with output breaker,3X Battery Shelves9Ah (108 Batteries),1981,Bypass Fuses  
449,BH20KEL2083P100,9355-18kVA UL 924  
UPS,208V,208V,216,60,3,18000,100,50,91,0.663,1684,761,494,3.041,Yes,Modem Card,R/T - FAA (60 +/- 0.5 Hz) (no output breaker),No Internal Battery (External Batteries Only),1981,Bypass Fuses  
450,BH20KEL2083P100,9355-18kVA UL 924  
UPS,208V,208V,216,60,3,18000,100,50,91,0.663,1684,761,494,7.768,Yes,Modem Card,R/T - FAA (60 +/- 0.5 Hz) (no output breaker),3X Battery Shelves9Ah (108 Batteries),1981,Bypass Fuses  
451,BH30KEL208SF100,9355-24kVA UL 924  
UPS,208V,208V,216,60,3,24000,100,70,91,0.663,1684,761,494,3.041,Yes,Power Expert Gateway Card,R/T (no output breaker),No Internal Battery (External Batteries Only),2702,Bypass Fuses  
452,BH30KEL208SF100,9355-24kVA UL 924  
UPS,208V,208V,216,60,3,24000,100,70,91,0.663,1684,761,494,7.768,Yes,Power Expert Gateway Card,R/T (no output breaker),3X Battery Shelves9Ah (108 Batteries),2702,Bypass Fuses  
453,BH30KEL208SF100,9355-24kVA UL 924  
UPS,208V,208V,216,60,3,24000,100,70,91,0.663,1684,761,494,3.041,Yes,Power Expert Gateway Card,Parallel (no output breaker),No Internal Battery (External Batteries Only),2702,Bypass Fuses  
454,BH30KEL208SF100,9355-24kVA UL 924

UPS,208V,208V,216,60,3,24000,100,70,91,0.663,1684,761,494,7.768,Yes,Power Expert Gateway Card,Parallel (no output breaker),3X Battery Shelves9Ah (108 Batteries),2702,Bypass Fuses  
455,BH30KEL208SF100,9355-24kVA UL 924  
UPS,208V,208V,216,60,3,24000,100,70,91,0.663,1684,761,494,3.041,Yes,Power Expert Gateway Card,R/T with output breaker,No Internal Battery (External Batteries Only),2702,Bypass Fuses  
456,BH30KEL208SF100,9355-24kVA UL 924  
UPS,208V,208V,216,60,3,24000,100,70,91,0.663,1684,761,494,7.768,Yes,Power Expert Gateway Card,R/T with output breaker,3X Battery Shelves9Ah (108 Batteries),2702,Bypass Fuses  
457,BH30KEL208SF100,9355-24kVA UL 924  
UPS,208V,208V,216,60,3,24000,100,70,91,0.663,1684,761,494,3.041,Yes,Power Expert Gateway Card,Parallel with output breaker,No Internal Battery (External Batteries Only),2702,Bypass Fuses  
458,BH30KEL208SF100,9355-24kVA UL 924  
UPS,208V,208V,216,60,3,24000,100,70,91,0.663,1684,761,494,7.768,Yes,Power Expert Gateway Card,Parallel with output breaker,3X Battery Shelves9Ah (108 Batteries),2702,Bypass Fuses  
459,BH30KEL208SF100,9355-24kVA UL 924  
UPS,208V,208V,216,60,3,24000,100,70,91,0.663,1684,761,494,3.041,Yes,Power Expert Gateway Card,R/T - FAA (60 +/- 0.5 Hz) (no output breaker),No Internal Battery (External Batteries Only),2702,Bypass Fuses  
460,BH30KEL208SF100,9355-24kVA UL 924  
UPS,208V,208V,216,60,3,24000,100,70,91,0.663,1684,761,494,7.768,Yes,Power Expert Gateway Card,R/T - FAA (60 +/- 0.5 Hz) (no output breaker),3X Battery Shelves9Ah (108 Batteries),2702,Bypass Fuses  
461,BH30KEL208SF100,9355-24kVA UL 924  
UPS,208V,208V,216,60,3,24000,100,70,91,0.663,1684,761,494,3.041,Yes,Modbus Card,R/T (no output breaker),No Internal Battery (External Batteries Only),2702,Bypass Fuses  
462,BH30KEL208SF100,9355-24kVA UL 924  
UPS,208V,208V,216,60,3,24000,100,70,91,0.663,1684,761,494,7.768,Yes,Modbus Card,R/T (no output breaker),3X Battery Shelves9Ah (108 Batteries),2702,Bypass Fuses  
463,BH30KEL208SF100,9355-24kVA UL 924  
UPS,208V,208V,216,60,3,24000,100,70,91,0.663,1684,761,494,3.041,Yes,Modbus Card,Parallel (no output breaker),No Internal Battery (External Batteries Only),2702,Bypass Fuses  
464,BH30KEL208SF100,9355-24kVA UL 924  
UPS,208V,208V,216,60,3,24000,100,70,91,0.663,1684,761,494,7.768,Yes,Modbus Card,Parallel (no output breaker),3X Battery Shelves9Ah (108 Batteries),2702,Bypass Fuses  
465,BH30KEL208SF100,9355-24kVA UL 924  
UPS,208V,208V,216,60,3,24000,100,70,91,0.663,1684,761,494,3.041,Yes,Modbus Card,R/T with output breaker,No Internal Battery (External Batteries Only),2702,Bypass Fuses  
466,BH30KEL208SF100,9355-24kVA UL 924  
UPS,208V,208V,216,60,3,24000,100,70,91,0.663,1684,761,494,7.768,Yes,Modbus Card,R/T with output breaker,3X Battery Shelves9Ah (108 Batteries),2702,Bypass Fuses  
467,BH30KEL208SF100,9355-24kVA UL 924  
UPS,208V,208V,216,60,3,24000,100,70,91,0.663,1684,761,494,3.041,Yes,Modbus Card,Parallel with output breaker,No Internal Battery (External Batteries Only),2702,Bypass Fuses  
468,BH30KEL208SF100,9355-24kVA UL 924  
UPS,208V,208V,216,60,3,24000,100,70,91,0.663,1684,761,494,7.768,Yes,Modbus Card,Parallel with output breaker,3X Battery Shelves9Ah (108 Batteries),2702,Bypass Fuses  
469,BH30KEL208SF100,9355-24kVA UL 924  
UPS,208V,208V,216,60,3,24000,100,70,91,0.663,1684,761,494,3.041,Yes,Modbus Card,R/T - FAA (60 +/- 0.5 Hz) (no output breaker),No Internal Battery (External Batteries Only),2702,Bypass Fuses  
470,BH30KEL208SF100,9355-24kVA UL 924  
UPS,208V,208V,216,60,3,24000,100,70,91,0.663,1684,761,494,7.768,Yes,Modbus Card,R/T - FAA (60 +/- 0.5 Hz) (no output breaker),3X Battery Shelves9Ah (108 Batteries),2702,Bypass Fuses  
471,BH30KEL208SF100,9355-24kVA UL 924  
UPS,208V,208V,216,60,3,24000,100,70,91,0.663,1684,761,494,3.041,Yes,Relay Card,R/T (no output breaker),No Internal Battery (External Batteries Only),2702,Bypass Fuses  
472,BH30KEL208SF100,9355-24kVA UL 924  
UPS,208V,208V,216,60,3,24000,100,70,91,0.663,1684,761,494,7.768,Yes,Relay Card,R/T (no output breaker),3X Battery Shelves9Ah (108 Batteries),2702,Bypass Fuses  
473,BH30KEL208SF100,9355-24kVA UL 924  
UPS,208V,208V,216,60,3,24000,100,70,91,0.663,1684,761,494,3.041,Yes,Relay Card,Parallel

(no output breaker),No Internal Battery (External Batteries Only),2702,Bypass Fuses  
474,BH30KEL208SF100,9355-24kVA UL 924  
UPS,208V,208V,216,60,3,24000,100,70,91,0.663,1684,761,494,7.768,Yes,Relay Card,Parallel  
(no output breaker),3X Battery Shelves9Ah (108 Batteries),2702,Bypass Fuses  
475,BH30KEL208SF100,9355-24kVA UL 924  
UPS,208V,208V,216,60,3,24000,100,70,91,0.663,1684,761,494,3.041,Yes,Relay Card,R/T with  
output breaker,No Internal Battery (External Batteries Only),2702,Bypass Fuses  
476,BH30KEL208SF100,9355-24kVA UL 924  
UPS,208V,208V,216,60,3,24000,100,70,91,0.663,1684,761,494,7.768,Yes,Relay Card,R/T with  
output breaker,3X Battery Shelves9Ah (108 Batteries),2702,Bypass Fuses  
477,BH30KEL208SF100,9355-24kVA UL 924  
UPS,208V,208V,216,60,3,24000,100,70,91,0.663,1684,761,494,3.041,Yes,Relay Card,Parallel  
with output breaker,No Internal Battery (External Batteries Only),2702,Bypass Fuses  
478,BH30KEL208SF100,9355-24kVA UL 924  
UPS,208V,208V,216,60,3,24000,100,70,91,0.663,1684,761,494,7.768,Yes,Relay Card,Parallel  
with output breaker,3X Battery Shelves9Ah (108 Batteries),2702,Bypass Fuses  
479,BH30KEL208SF100,9355-24kVA UL 924  
UPS,208V,208V,216,60,3,24000,100,70,91,0.663,1684,761,494,3.041,Yes,Relay Card,R/T - FAA  
(60 +/- 0.5 Hz) (no output breaker),No Internal Battery (External Batteries  
Only),2702,Bypass Fuses  
480,BH30KEL208SF100,9355-24kVA UL 924  
UPS,208V,208V,216,60,3,24000,100,70,91,0.663,1684,761,494,7.768,Yes,Relay Card,R/T - FAA  
(60 +/- 0.5 Hz) (no output breaker),3X Battery Shelves9Ah (108 Batteries),2702,Bypass  
Fuses  
481,BH30KEL208SF100,9355-24kVA UL 924  
UPS,208V,208V,216,60,3,24000,100,70,91,0.663,1684,761,494,3.041,Yes,Industrial Relay  
Card,R/T (no output breaker),No Internal Battery (External Batteries Only),2702,Bypass  
Fuses  
482,BH30KEL208SF100,9355-24kVA UL 924  
UPS,208V,208V,216,60,3,24000,100,70,91,0.663,1684,761,494,7.768,Yes,Industrial Relay  
Card,R/T (no output breaker),3X Battery Shelves9Ah (108 Batteries),2702,Bypass Fuses  
483,BH30KEL208SF100,9355-24kVA UL 924  
UPS,208V,208V,216,60,3,24000,100,70,91,0.663,1684,761,494,3.041,Yes,Industrial Relay  
Card,Parallel (no output breaker),No Internal Battery (External Batteries  
Only),2702,Bypass Fuses  
484,BH30KEL208SF100,9355-24kVA UL 924  
UPS,208V,208V,216,60,3,24000,100,70,91,0.663,1684,761,494,7.768,Yes,Industrial Relay  
Card,Parallel (no output breaker),3X Battery Shelves9Ah (108 Batteries),2702,Bypass  
Fuses  
485,BH30KEL208SF100,9355-24kVA UL 924  
UPS,208V,208V,216,60,3,24000,100,70,91,0.663,1684,761,494,3.041,Yes,Industrial Relay  
Card,R/T with output breaker,No Internal Battery (External Batteries Only),2702,Bypass  
Fuses  
486,BH30KEL208SF100,9355-24kVA UL 924  
UPS,208V,208V,216,60,3,24000,100,70,91,0.663,1684,761,494,7.768,Yes,Industrial Relay  
Card,R/T with output breaker,3X Battery Shelves9Ah (108 Batteries),2702,Bypass Fuses  
487,BH30KEL208SF100,9355-24kVA UL 924  
UPS,208V,208V,216,60,3,24000,100,70,91,0.663,1684,761,494,3.041,Yes,Industrial Relay  
Card,Parallel with output breaker,No Internal Battery (External Batteries  
Only),2702,Bypass Fuses  
488,BH30KEL208SF100,9355-24kVA UL 924  
UPS,208V,208V,216,60,3,24000,100,70,91,0.663,1684,761,494,7.768,Yes,Industrial Relay  
Card,Parallel with output breaker,3X Battery Shelves9Ah (108 Batteries),2702,Bypass  
Fuses  
489,BH30KEL208SF100,9355-24kVA UL 924  
UPS,208V,208V,216,60,3,24000,100,70,91,0.663,1684,761,494,3.041,Yes,Industrial Relay  
Card,R/T - FAA (60 +/- 0.5 Hz) (no output breaker),No Internal Battery (External  
Batteries Only),2702,Bypass Fuses  
490,BH30KEL208SF100,9355-24kVA UL 924  
UPS,208V,208V,216,60,3,24000,100,70,91,0.663,1684,761,494,7.768,Yes,Industrial Relay  
Card,R/T - FAA (60 +/- 0.5 Hz) (no output breaker),3X Battery Shelves9Ah (108  
Batteries),2702,Bypass Fuses  
491,BH30KEL208SF100,9355-24kVA UL 924  
UPS,208V,208V,216,60,3,24000,100,70,91,0.663,1684,761,494,3.041,Yes,Modem Card,R/T (no  
output breaker),No Internal Battery (External Batteries Only),2702,Bypass Fuses  
492,BH30KEL208SF100,9355-24kVA UL 924

UPS,208V,208V,216,60,3,24000,100,70,91,0.663,1684,761,494,7.768,Yes,Modem Card,R/T (no output breaker),3X Battery Shelves9Ah (108 Batteries),2702,Bypass Fuses  
493,BH30KEL208SF100,9355-24kVA UL 924

UPS,208V,208V,216,60,3,24000,100,70,91,0.663,1684,761,494,3.041,Yes,Modem Card,Parallel (no output breaker),No Internal Battery (External Batteries Only),2702,Bypass Fuses  
494,BH30KEL208SF100,9355-24kVA UL 924

UPS,208V,208V,216,60,3,24000,100,70,91,0.663,1684,761,494,7.768,Yes,Modem Card,Parallel (no output breaker),3X Battery Shelves9Ah (108 Batteries),2702,Bypass Fuses  
495,BH30KEL208SF100,9355-24kVA UL 924

UPS,208V,208V,216,60,3,24000,100,70,91,0.663,1684,761,494,3.041,Yes,Modem Card,R/T with output breaker,No Internal Battery (External Batteries Only),2702,Bypass Fuses  
496,BH30KEL208SF100,9355-24kVA UL 924

UPS,208V,208V,216,60,3,24000,100,70,91,0.663,1684,761,494,7.768,Yes,Modem Card,R/T with output breaker,3X Battery Shelves9Ah (108 Batteries),2702,Bypass Fuses  
497,BH30KEL208SF100,9355-24kVA UL 924

UPS,208V,208V,216,60,3,24000,100,70,91,0.663,1684,761,494,3.041,Yes,Modem Card,Parallel with output breaker,No Internal Battery (External Batteries Only),2702,Bypass Fuses  
498,BH30KEL208SF100,9355-24kVA UL 924

UPS,208V,208V,216,60,3,24000,100,70,91,0.663,1684,761,494,7.768,Yes,Modem Card,Parallel with output breaker,3X Battery Shelves9Ah (108 Batteries),2702,Bypass Fuses  
499,BH30KEL208SF100,9355-24kVA UL 924

UPS,208V,208V,216,60,3,24000,100,70,91,0.663,1684,761,494,3.041,Yes,Modem Card,R/T - FAA (60 +/- 0.5 Hz) (no output breaker),No Internal Battery (External Batteries Only),2702,Bypass Fuses  
500,BH30KEL208SF100,9355-24kVA UL 924

UPS,208V,208V,216,60,3,24000,100,70,91,0.663,1684,761,494,7.768,Yes,Modem Card,R/T - FAA (60 +/- 0.5 Hz) (no output breaker),3X Battery Shelves9Ah (108 Batteries),2702,Bypass Fuses  
501,BH30KEL2083P100,9355-30kVA UL 930

UPS,208V,208V,216,60,3,27000,100,75,136,0.663,1684,761,494,3.041,Yes,Power Expert Gateway Card,R/T (no output breaker),No Internal Battery (External Batteries Only),2702,Bypass Fuses  
502,BH30KEL2083P100,9355-30kVA UL 930

UPS,208V,208V,216,60,3,27000,100,75,136,0.663,1684,761,494,7.768,Yes,Power Expert Gateway Card,R/T (no output breaker),3X Battery Shelves9Ah (108 Batteries),2702,Bypass Fuses  
503,BH30KEL2083P100,9355-30kVA UL 930

UPS,208V,208V,216,60,3,27000,100,75,136,0.663,1684,761,494,3.041,Yes,Power Expert Gateway Card,Parallel (no output breaker),No Internal Battery (External Batteries Only),2702,Bypass Fuses  
504,BH30KEL2083P100,9355-30kVA UL 930

UPS,208V,208V,216,60,3,27000,100,75,136,0.663,1684,761,494,7.768,Yes,Power Expert Gateway Card,Parallel (no output breaker),3X Battery Shelves9Ah (108 Batteries),2702,Bypass Fuses  
505,BH30KEL2083P100,9355-30kVA UL 930

UPS,208V,208V,216,60,3,27000,100,75,136,0.663,1684,761,494,3.041,Yes,Power Expert Gateway Card,R/T with output breaker,No Internal Battery (External Batteries Only),2702,Bypass Fuses  
506,BH30KEL2083P100,9355-30kVA UL 930

UPS,208V,208V,216,60,3,27000,100,75,136,0.663,1684,761,494,7.768,Yes,Power Expert Gateway Card,R/T with output breaker,3X Battery Shelves9Ah (108 Batteries),2702,Bypass Fuses  
507,BH30KEL2083P100,9355-30kVA UL 930

UPS,208V,208V,216,60,3,27000,100,75,136,0.663,1684,761,494,3.041,Yes,Power Expert Gateway Card,Parallel with output breaker,No Internal Battery (External Batteries Only),2702,Bypass Fuses  
508,BH30KEL2083P100,9355-30kVA UL 930

UPS,208V,208V,216,60,3,27000,100,75,136,0.663,1684,761,494,7.768,Yes,Power Expert Gateway Card,Parallel with output breaker,3X Battery Shelves9Ah (108 Batteries),2702,Bypass Fuses  
509,BH30KEL2083P100,9355-30kVA UL 930

UPS,208V,208V,216,60,3,27000,100,75,136,0.663,1684,761,494,3.041,Yes,Power Expert Gateway Card,R/T - FAA (60 +/- 0.5 Hz) (no output breaker),No Internal Battery (External Batteries Only),2702,Bypass Fuses  
510,BH30KEL2083P100,9355-30kVA UL 930

UPS,208V,208V,216,60,3,27000,100,75,136,0.663,1684,761,494,7.768,Yes,Power Expert Gateway Card,R/T - FAA (60 +/- 0.5 Hz) (no output breaker),3X Battery Shelves9Ah (108 Batteries),2702,Bypass Fuses

511,BH30KEL2083P100,9355-30kVA UL 930  
 UPS,208V,208V,216,60,3,27000,100,75,136,0.663,1684,761,494,3.041,Yes,Modbus Card,R/T (no output breaker),No Internal Battery (External Batteries Only),2702,Bypass Fuses  
 512,BH30KEL2083P100,9355-30kVA UL 930  
 UPS,208V,208V,216,60,3,27000,100,75,136,0.663,1684,761,494,7.768,Yes,Modbus Card,R/T (no output breaker),3X Battery Shelves9Ah (108 Batteries),2702,Bypass Fuses  
 513,BH30KEL2083P100,9355-30kVA UL 930  
 UPS,208V,208V,216,60,3,27000,100,75,136,0.663,1684,761,494,3.041,Yes,Modbus Card,Parallel (no output breaker),No Internal Battery (External Batteries Only),2702,Bypass Fuses  
 514,BH30KEL2083P100,9355-30kVA UL 930  
 UPS,208V,208V,216,60,3,27000,100,75,136,0.663,1684,761,494,7.768,Yes,Modbus Card,Parallel (no output breaker),3X Battery Shelves9Ah (108 Batteries),2702,Bypass Fuses  
 515,BH30KEL2083P100,9355-30kVA UL 930  
 UPS,208V,208V,216,60,3,27000,100,75,136,0.663,1684,761,494,3.041,Yes,Modbus Card,R/T with output breaker,No Internal Battery (External Batteries Only),2702,Bypass Fuses  
 516,BH30KEL2083P100,9355-30kVA UL 930  
 UPS,208V,208V,216,60,3,27000,100,75,136,0.663,1684,761,494,7.768,Yes,Modbus Card,R/T with output breaker,3X Battery Shelves9Ah (108 Batteries),2702,Bypass Fuses  
 517,BH30KEL2083P100,9355-30kVA UL 930  
 UPS,208V,208V,216,60,3,27000,100,75,136,0.663,1684,761,494,3.041,Yes,Modbus Card,Parallel with output breaker,No Internal Battery (External Batteries Only),2702,Bypass Fuses  
 518,BH30KEL2083P100,9355-30kVA UL 930  
 UPS,208V,208V,216,60,3,27000,100,75,136,0.663,1684,761,494,7.768,Yes,Modbus Card,Parallel with output breaker,3X Battery Shelves9Ah (108 Batteries),2702,Bypass Fuses  
 519,BH30KEL2083P100,9355-30kVA UL 930  
 UPS,208V,208V,216,60,3,27000,100,75,136,0.663,1684,761,494,3.041,Yes,Modbus Card,R/T - FAA (60 +/- 0.5 Hz) (no output breaker),No Internal Battery (External Batteries Only),2702,Bypass Fuses  
 520,BH30KEL2083P100,9355-30kVA UL 930  
 UPS,208V,208V,216,60,3,27000,100,75,136,0.663,1684,761,494,7.768,Yes,Modbus Card,R/T - FAA (60 +/- 0.5 Hz) (no output breaker),3X Battery Shelves9Ah (108 Batteries),2702,Bypass Fuses  
 521,BH30KEL2083P100,9355-30kVA UL 930  
 UPS,208V,208V,216,60,3,27000,100,75,136,0.663,1684,761,494,3.041,Yes,Relay Card,R/T (no output breaker),No Internal Battery (External Batteries Only),2702,Bypass Fuses  
 522,BH30KEL2083P100,9355-30kVA UL 930  
 UPS,208V,208V,216,60,3,27000,100,75,136,0.663,1684,761,494,7.768,Yes,Relay Card,R/T (no output breaker),3X Battery Shelves9Ah (108 Batteries),2702,Bypass Fuses  
 523,BH30KEL2083P100,9355-30kVA UL 930  
 UPS,208V,208V,216,60,3,27000,100,75,136,0.663,1684,761,494,3.041,Yes,Relay Card,Parallel (no output breaker),No Internal Battery (External Batteries Only),2702,Bypass Fuses  
 524,BH30KEL2083P100,9355-30kVA UL 930  
 UPS,208V,208V,216,60,3,27000,100,75,136,0.663,1684,761,494,7.768,Yes,Relay Card,Parallel (no output breaker),3X Battery Shelves9Ah (108 Batteries),2702,Bypass Fuses  
 525,BH30KEL2083P100,9355-30kVA UL 930  
 UPS,208V,208V,216,60,3,27000,100,75,136,0.663,1684,761,494,3.041,Yes,Relay Card,R/T with output breaker,No Internal Battery (External Batteries Only),2702,Bypass Fuses  
 526,BH30KEL2083P100,9355-30kVA UL 930  
 UPS,208V,208V,216,60,3,27000,100,75,136,0.663,1684,761,494,7.768,Yes,Relay Card,R/T with output breaker,3X Battery Shelves9Ah (108 Batteries),2702,Bypass Fuses  
 527,BH30KEL2083P100,9355-30kVA UL 930  
 UPS,208V,208V,216,60,3,27000,100,75,136,0.663,1684,761,494,3.041,Yes,Relay Card,Parallel with output breaker,No Internal Battery (External Batteries Only),2702,Bypass Fuses  
 528,BH30KEL2083P100,9355-30kVA UL 930  
 UPS,208V,208V,216,60,3,27000,100,75,136,0.663,1684,761,494,7.768,Yes,Relay Card,Parallel with output breaker,3X Battery Shelves9Ah (108 Batteries),2702,Bypass Fuses  
 529,BH30KEL2083P100,9355-30kVA UL 930  
 UPS,208V,208V,216,60,3,27000,100,75,136,0.663,1684,761,494,3.041,Yes,Relay Card,R/T - FAA (60 +/- 0.5 Hz) (no output breaker),No Internal Battery (External Batteries Only),2702,Bypass Fuses  
 530,BH30KEL2083P100,9355-30kVA UL 930  
 UPS,208V,208V,216,60,3,27000,100,75,136,0.663,1684,761,494,7.768,Yes,Relay Card,R/T - FAA (60 +/- 0.5 Hz) (no output breaker),3X Battery Shelves9Ah (108 Batteries),2702,Bypass Fuses  
 531,BH30KEL2083P100,9355-30kVA UL 930  
 UPS,208V,208V,216,60,3,27000,100,75,136,0.663,1684,761,494,3.041,Yes,Industrial Relay

Card,R/T (no output breaker),No Internal Battery (External Batteries Only),2702,Bypass Fuses

532,BH30KEL2083P100,9355-30kVA UL 930

UPS,208V,208V,216,60,3,27000,100,75,136,0.663,1684,761,494,7.768,Yes,Industrial Relay Card,R/T (no output breaker),3X Battery Shelves9Ah (108 Batteries),2702,Bypass Fuses

533,BH30KEL2083P100,9355-30kVA UL 930

UPS,208V,208V,216,60,3,27000,100,75,136,0.663,1684,761,494,3.041,Yes,Industrial Relay Card,Parallel (no output breaker),No Internal Battery (External Batteries Only),2702,Bypass Fuses

534,BH30KEL2083P100,9355-30kVA UL 930

UPS,208V,208V,216,60,3,27000,100,75,136,0.663,1684,761,494,7.768,Yes,Industrial Relay Card,Parallel (no output breaker),3X Battery Shelves9Ah (108 Batteries),2702,Bypass Fuses

535,BH30KEL2083P100,9355-30kVA UL 930

UPS,208V,208V,216,60,3,27000,100,75,136,0.663,1684,761,494,3.041,Yes,Industrial Relay Card,R/T with output breaker,No Internal Battery (External Batteries Only),2702,Bypass Fuses

536,BH30KEL2083P100,9355-30kVA UL 930

UPS,208V,208V,216,60,3,27000,100,75,136,0.663,1684,761,494,7.768,Yes,Industrial Relay Card,R/T with output breaker,3X Battery Shelves9Ah (108 Batteries),2702,Bypass Fuses

537,BH30KEL2083P100,9355-30kVA UL 930

UPS,208V,208V,216,60,3,27000,100,75,136,0.663,1684,761,494,3.041,Yes,Industrial Relay Card,Parallel with output breaker,No Internal Battery (External Batteries Only),2702,Bypass Fuses

538,BH30KEL2083P100,9355-30kVA UL 930

UPS,208V,208V,216,60,3,27000,100,75,136,0.663,1684,761,494,7.768,Yes,Industrial Relay Card,Parallel with output breaker,3X Battery Shelves9Ah (108 Batteries),2702,Bypass Fuses

539,BH30KEL2083P100,9355-30kVA UL 930

UPS,208V,208V,216,60,3,27000,100,75,136,0.663,1684,761,494,3.041,Yes,Industrial Relay Card,R/T - FAA (60 +/- 0.5 Hz) (no output breaker),No Internal Battery (External Batteries Only),2702,Bypass Fuses

540,BH30KEL2083P100,9355-30kVA UL 930

UPS,208V,208V,216,60,3,27000,100,75,136,0.663,1684,761,494,7.768,Yes,Industrial Relay Card,R/T - FAA (60 +/- 0.5 Hz) (no output breaker),3X Battery Shelves9Ah (108 Batteries),2702,Bypass Fuses

541,BH30KEL2083P100,9355-30kVA UL 930

UPS,208V,208V,216,60,3,27000,100,75,136,0.663,1684,761,494,3.041,Yes,Modem Card,R/T (no output breaker),No Internal Battery (External Batteries Only),2702,Bypass Fuses

542,BH30KEL2083P100,9355-30kVA UL 930

UPS,208V,208V,216,60,3,27000,100,75,136,0.663,1684,761,494,7.768,Yes,Modem Card,R/T (no output breaker),3X Battery Shelves9Ah (108 Batteries),2702,Bypass Fuses

543,BH30KEL2083P100,9355-30kVA UL 930

UPS,208V,208V,216,60,3,27000,100,75,136,0.663,1684,761,494,3.041,Yes,Modem Card,Parallel (no output breaker),No Internal Battery (External Batteries Only),2702,Bypass Fuses

544,BH30KEL2083P100,9355-30kVA UL 930

UPS,208V,208V,216,60,3,27000,100,75,136,0.663,1684,761,494,7.768,Yes,Modem Card,Parallel (no output breaker),3X Battery Shelves9Ah (108 Batteries),2702,Bypass Fuses

545,BH30KEL2083P100,9355-30kVA UL 930

UPS,208V,208V,216,60,3,27000,100,75,136,0.663,1684,761,494,3.041,Yes,Modem Card,R/T with output breaker,No Internal Battery (External Batteries Only),2702,Bypass Fuses

546,BH30KEL2083P100,9355-30kVA UL 930

UPS,208V,208V,216,60,3,27000,100,75,136,0.663,1684,761,494,7.768,Yes,Modem Card,R/T with output breaker,3X Battery Shelves9Ah (108 Batteries),2702,Bypass Fuses

547,BH30KEL2083P100,9355-30kVA UL 930

UPS,208V,208V,216,60,3,27000,100,75,136,0.663,1684,761,494,3.041,Yes,Modem Card,Parallel with output breaker,No Internal Battery (External Batteries Only),2702,Bypass Fuses

548,BH30KEL2083P100,9355-30kVA UL 930

UPS,208V,208V,216,60,3,27000,100,75,136,0.663,1684,761,494,7.768,Yes,Modem Card,Parallel with output breaker,3X Battery Shelves9Ah (108 Batteries),2702,Bypass Fuses

549,BH30KEL2083P100,9355-30kVA UL 930

UPS,208V,208V,216,60,3,27000,100,75,136,0.663,1684,761,494,3.041,Yes,Modem Card,R/T - FAA (60 +/- 0.5 Hz) (no output breaker),No Internal Battery (External Batteries Only),2702,Bypass Fuses

550,BH30KEL2083P100,9355-30kVA UL 930

UPS,208V,208V,216,60,3,27000,100,75,136,0.663,1684,761,494,7.768,Yes,Modem Card,R/T - FAA

(60 +/- 0.5 Hz) (no output breaker),3X Battery Shelves9Ah (108 Batteries),2702,Bypass  
Fuses