

,EqptModel##other##,EqptDescription##other##,InputVoltage##electrical_potential##volts,OutputVoltage##electrical_potential##volts,InputCurrent##electrical_curren
ent##amperes,OutputCurrent##electrical_current##amperes,NominalFrequencyRange##electrical_frequency##hertz,Volume##volume##cubic_meters,NominalHeight##length##
millimeters,NominalDepth##length##millimeters,NominalWidth##length##millimeters,UnitWeight##unit_weight##kilonewtons_per_cubic_meter,UL##other##,MBS##other##,B
ypass transformer##other##,Input Transformer##other##,Output transformer##other##
1,KBT000000000010,9355_30 options Cabinet,208,208,100,100,50,0.63224096,1684,760,494,0.147095816,yes,yes,no,no,no
2,KBT000000000010,9355_30 options Cabinet,208,208,100,100,60,0.63224096,1684,760,494,0.147095816,yes,yes,no,no,no
3,KBT001100000010,9355_30 options Cabinet,208,208,100,100,60,0.63224096,1684,760,494,0.384347132,yes,yes,yes,no,no
4,KBT001200000010,9355_30 options Cabinet,480,208,48,100,60,0.63224096,1684,760,494,0.384347132,yes,yes,yes,no,no
5,KBT001300000010,9355_30 options Cabinet,600,208,32,100,60,0.63224096,1684,760,494,0.384347132,yes,yes,yes,no,no
6,KBT002100000010,9355_30 options Cabinet,208,208,100,100,60,0.63224096,1684,760,494,0.384347132,yes,no,no,yes,no
7,KBT002200000010,9355_30 options Cabinet,480,208,48,100,60,0.63224096,1684,760,494,0.384347132,yes,no,no,yes,no
8,KBT002300000010,9355_30 options Cabinet,600,208,32,100,60,0.63224096,1684,760,494,0.384347132,yes,no,no,yes,no

9,KB003200000010,9355_30 options Cabinet,208,480,84,37,60,0.63224096,1684,760,494,0.384347132,yes,no,no,no,yes
10,KB004200000010,9355_30 options Cabinet,480,480,48,37,60,0.63224096,1684,760,494,0.569403159,yes,yes,yes,no,yes
11,KB004200000010 Use Alternate Label: Field 12: BHKBT004200,9355_30 options Cabinet,480,480,48,37,60,0.63224096,1684,760,494,0.569403159,yes,yes,yes,no,yes