

Eaton® batteries

Physical properties

Type	PWHR1234W2FR	PWHR12120W3FR	PWHR12200W4FR	PWHR12280W4FR	PWHR12330W4FR	PWHR12390W4FR	PWHR12540W
Electrolyte (gal / battery)	0.095	0.368	0.696	0.907	1.054	1.205	1.704
Battery weight (kg)	2.7	10.2	17.3	25.8	29.6	33.0	43.9
Connection	0.250 inch (6.35 mm) tab	M5	M6	M6	M6	M6	M6
Tightening torque (max)	N/A	51 lb in	91 lb in	91 lb in	91 lb in	91 lb in	91 lb in
20hr-rate (Ah)	8.5	30.0	50.0	70.0	82.5	97.5	135.0
"Gassing Rate (ft ³ /hour) 2.3 V/cell, 99% recombination efficiency	0.0000804	0.0002923	0.0004871	0.0006820	0.0008038	0.0009499	0.0013153

For additional information on Eaton's private-labeled batteries, contact Battery Service Sales Support at: **800.843.9433** or **Eaton.com/UPSbatteries**



Powering Business Worldwide

Eaton
1000 Eaton Boulevard
Cleveland, OH 44122
United States
Eaton.com

© 2015 Eaton
All Rights Reserved
Printed in USA
TD162003EN / GG
March 2015

Eaton is a registered trademark.
All other trademarks are property
of their respective owners.