





EBA309-10
G3 BASIC

FUNCTIONALITY	INPUT	OUTPUT	OPERATING TEMPERATURE
POWER DISTRIBUTION	NEMA L21-20P 10FT 12AWG / 5C POWERCORD	(39) NEMA 5-20R	32° TO 140° F 0° TO 60° C
MECHANICAL	INPUT RATING	OUTPUT RATING	CERTIFICATIONS
66.50" (1689mm) LENGTH 2.05" (52mm) WIDTH 2.09" (53mm) DEPTH ALUMINUM CHASSIS, BLACK	120/208V~ WYE 3W+N+PE 16A 50/60HZ	120V~ 16A PER OUTLET 16A MAX PER SECTION 16A MAX PER PHASE	
CIRCUIT BREAKERS	FILTER AND SPIKE/SURGE	ACCESSORIES	CONFIGURATION
NONE	NONE	INCLUDED SPK012 - INSTALLATION	EBA3PB15AMG78AC



TITLE	ePDU G3 SPECIFICATION EBA309-10	DRAW	SPOCK LIU 2013-11-20
DWG NO.	B9001-221170-01P	DESIGN	
MATERIAL		CHECKED	ELON GUO 2013-11-20
COATING		SAFETY	
UNITS	in[mm]	APPROVED	VICKY SHEN 2013-11-20
SHEET	1/1	SCALE	1:5

**EAT•N**
ELECTRICAL SECTOR