



EBA308-10
G3 BASIC

FUNCTIONALITY	INPUT	OUTPUT	OPERATING TEMPERATURE
POWER DISTRIBUTION	NEMA L21-20P 10FT 12AWG / 5C POWERCORD	(21) NEMA 5-20R (6) NEMA L6-20R	32° TO 140° F 0° TO 60° C
MECHANICAL	INPUT RATING	OUTPUT RATING	CERTIFICATIONS
66.50" (1689mm) LENGTH 2.05" (52mm) WIDTH 2.09" (53mm) DEPTH ALUMINUM CHASSIS, BLACK	120/208V~ WYE 3W+N+PE 16A 50/60HZ	120V~; 16A PER 5-20 200-240V~; 16A PER L6-20 16A MAX PER SECTION 16A MAX PER PHASE	
CIRCUIT BREAKERS	FILTER AND SPIKE/SURGE	ACCESSORIES	CONFIGURATION
NONE	NONE	INCLUDED SPK012 - INSTALLATION	EBA3PB15AFE78AC

TITLE	ePDU G3 SPECIFICATION EBA308-10	DRAW	SPOCK LIU 2013-11-20
DWG NO.	B9001-221160-01P	CHECKED	ELON GUO 2013-11-20
MATERIAL		SAFETY	
COATING		APPROVED	VICKY SHEN 2013-11-20
UNITS	in[mm]	SCALE	A3 1:5
SHEET	1/1		

