





EMI301-10
G3 METERED INPUT

FUNCTIONALITY	INPUT	OUTPUT	OPERATING TEMPERATURE
CURRENT, POWER, AND ENERGY METERING FOR INPUT AND BRANCH	NEMA L15-20P 10FT 12AWG / 4C POWERCORD	(30) IEC 60320 C13 GRIP (6) IEC 60320 C19 GRIP	32° TO 140° F 0° TO 60° C
MECHANICAL	INPUT RATING	OUTPUT RATING	CERTIFICATIONS
66.50" (1689mm) LENGTH 2.05" (52mm) WIDTH 2.09" (53mm) DEPTH ALUMINUM CHASSIS, BLACK	200-240V~ DELTA 3W+PE 16A 50/60HZ	200-240V~ 15A PER C13 16A PER C19 16A MAX PER SECTION 16A MAX PER PHASE	
CIRCUIT BREAKERS	FILTER AND SPIKE/SURGE	ACCESSORIES	CONFIGURATION
(3) 20A 2-POLE LISTED	NONE	INCLUDED SPK012 - INSTALLATION INCLUDED SPK013 - NETWORK OPTIONAL EMP001 - ENVIRONMENTAL PROBE	EMI3PA15JGJ78A1



TITLE	ePDU G3 SPECIFICATION EMI301-10	DRAW	J. SMITH	2014-01-07
DWG NO.	EMI3PA15JGJ78A1_SP REV 001	DESIGN		
MATERIAL		CHECKED		
COATING		SAFETY		
UNITS	in[mm]	APPROVED		
SHEET	1/1			

A3

SCALE

1:5


ELECTRICAL SECTOR