



EMIT02-10 G3 METERED INPUT			
FUNCTIONALITY	INPUT	OUTPUT	ENVIRONMENTAL
CURRENT, POWER AND ENERGY METERING FOR INPUT	NEMA L5-20 PLUG 10FT 12AWG / 3C POWERCORD	(12) NEMA 5-20	32° TO 140° F 0° TO 60° C
MECHANICAL	INPUT RATING	OUTPUT RATING	CERTIFICATIONS
19.00" (482.6mm) WIDTH 1.69" (42.9mm) HEIGHT 8.00" (203.2mm) DEPTH BLACK CHASSIS	100-127V ~ W + N + PE 16A 50/60HZ	100-127V ~ 16A PER OUTLET 16A MAX TOTAL	
CIRCUIT BREAKERS	FILTER AND SPIKE/SURGE	ACCESSORIES	CONFIGURATION
NONE	NONE	INCLUDED SPK021 - INSTALLATION INCLUDED SPK013 - NETWORK OPTIONAL EMP001 - ENVIRONMENTAL PROBE	EMI3MDB5ALE13A1 SERIAL NUMBER B682 _____

8

7

6

5

4

3

2

1

DESCRIPTION

MODIFIED BY

DATE

STATE

ECO

PRO-ENGINEER GENERATED

PART NAME

REVISION

SHEET

THIRD ANGLE PROJECTION

091701

26 OCT 15

RELEASE

002

EMI3MDB5ALE13A1

002

1 of 1

SCALE

DO NOT SCALE

DRAWING OR

CHANGE MANUALLY

SCALE: 0.500

DO NOT SCALE

DRAWING OR

CHANGE MANUALLY

EATON CORPORATION - CONFIDENTIAL AND PROPRIETARY NOTICE TO PERSONS RECEIVING THIS DOCUMENT AND/OR TECHNICAL INFORMATION THIS DOCUMENT, INCLUDING THE DRAWING AND INFORMATION CONTAINED THEREON, IS CONFIDENTIAL AND IS THE EXCLUSIVE PROPERTY OF EATON CORPORATION, AND IS HEREBY ON LOAN AND SUBJECT TO RECALL BY EATON AT ANY TIME. BY TAKING POSSESSION OF THIS DOCUMENT, THE RECIPIENT ACKNOWLEDGES AND AGREES THAT THIS DOCUMENT CANNOT BE USED IN ANY MANNER ADVERSE TO THE INTERESTS OF EATON, AND THAT NO PORTION OF THIS DOCUMENT MAY BE COPIED OR OTHERWISE REPRODUCED WITHOUT THE PRIOR WRITTEN CONSENT OF EATON. IN THE CASE OF CONFLICTING CONTRACTUAL PROVISIONS, THIS NOTICE SHALL GOVERN THE STATUS OF THIS DOCUMENT. © 2008 Eaton Corporation - All Rights Reserved.

