




| LTR | ECD No. | REVISION | DR | CK | AP | AP | DATE |
|-----|---------|---------------------|----|----|----|----|-----------|
| A | NONE | ENGINEERING RELEASE | JK | | | | 12/13/04 |
| B | 8735 | UPDATE SILKSCREEN | LS | | DK | | 27 OCT 09 |
| C | 11702 | UPDATE EATON LOGOS | GS | | | | 20 MAY 10 |
| 002 | 064790 | ADD ROHS NOTES | HN | | | | 02 MAY 14 |



- NOTES
1. RACK MOUNTED STEEL CHASSIS, BLACK MED. TEXTURE
19.00" WIDE STD. RACK MOUNTING WITH ADJUSTABLE BRACKETS
1.72" HIGH
7.00" DEEP
UNIT REQUIRES CHASSIS SUPPORT BRACKETS
 2. DUAL INPUT:
PRIMARY: 120 VAC, SINGLE PHASE, 50/60HZ
CABLE: 12/3 SOOW, 9 FOOT, L5-20 PLUG
SECONDARY: 120 VAC, SINGLE PHASE, 50/60HZ
CABLE: 12/3 SOOW, 9 FOOT, L5-20 PLUG
 3. OUTPUT: 120 VAC 16 AMPS AT EIGHT NEMA 5-20 RECEPTACLES
 4. FILTER: 20 AMP EMI/RFI FILTER
COMMON MODE, LINE TO GROUND, NEUTRAL TO GROUND
DIFFERENTIAL MODE, LINE TO NEUTRAL
 5. SPIKE SURGE PROTECTION: LINE TO NEUTRAL
 6. CIRCUIT BREAKER: 1 POLE 20 AMP UL RECOGNIZED
 7. INDICATOR LIGHTS: FIVE
1 BLUE, ON WHEN THERE IS POWER TO OUTLETS
4 GREEN, DISPLAYS POWER AVAILABLE FROM DUAL SOURCE,
AND IDENTIFIES THE SOURCE IN USE.
 8. PRIMARY AND SECONDARY SOURCES DO NOT NEED TO BE
PHASE SYNCHRONIZED. UNIT TESTED TO AN OUTPUT
POWER FACTOR OF .85 (LEADING AND LAGGING)
 9. AUTOSWITCH BETWEEN PRIMARY AND SECONDARY POWER SOURCE

| | | |
|---------------|----------|---------|
| INPUT VOLTAGE | DROP-OUT | PULL-IN |
| 120 VAC | 90 | 103 |
 10. UL/CUL LISTED PRODUCT.
 11. ROHS COMPLIANT PER DIRECTIVE 2011/65/EU WITH APPLICABLE EXEMPTIONS.
 12. ALL MATERIALS AND SUB-MATERIALS COMPLY WITH EATON SPECIFICATION 164080496.
DOCUMENTATION CERTIFYING COMPLIANCE TO EATON SPECIFICATION 164080496 IS
AVAILABLE UPON REQUEST.



EATON APPROVAL _____ DATE _____

| | | | | | | | |
|--|--|---|--|--|--|--|--|
| THE INFORMATION AND DESIGN DISCLOSED HEREIN WAS ORIGINATED BY AND IS THE PROPERTY OF EATON CORPORATION. EATON CORPORATION RESERVES ALL PATENT, PROPRIETARY, DESIGN, MANUFACTURING, REPRODUCTION, USE AND SALE RIGHTS THERE TO, AND TO ANY ARTICLE DISCLOSED THEREIN, EXCEPT TO THE EXTENT RIGHTS ARE EXPRESSLY GRANTED TO OTHERS. THE FOREGOING DOES NOT APPLY TO VENDOR PROPRIETARY PARTS. COPYRIGHT 2009 EATON CORP. | | EATON DIMENSIONS IN INCHES TOLERANCES: FRACTIONS ANGLES X.000 .0005 X.000 .010 DECIMALS DECIMALS PAGE CODE 31795 | | TITLE ENGINEERING DRAWING FOR T2235-A2-CFB09L ASSY. 3268 DRAWN BY JK CHECKED LS DATE 10/27/09 SHEET 1 OF 1 DWG NO. T_2235_A2_CFB09L_3268_ME REV. 002 | | 9650 Jeronimo Road Irvine, California 92618 Phone (949) 452-0500 www.epdu.com | |
|--|--|---|--|--|--|--|--|