

Fixture hangers

FLEXIBLE FIXTURE HANGERS

Flexible fixture hangers are used in commercial or light industrial applications where HID high bay and low bay lighting fixtures are used. Specific applications include storage facilities, shipping warehouses, retail and DIY facilities.

Features:

- Suitable for use with 1/2" or 3/4" fixture conduit stems, these hangers allow the conduit stem of the fixture (luminaire) to swing in any direction;

Cat. #	Swing angle from vertical
TPSFH12/TPRFH12	26°
TPSC-5075HF/TPSC-5075HFR	20°

- Available in two styles: one for attachment to round or octagonal steel boxes; the other for attachment to 4" square steel boxes
- Both styles are quickly and easily attached by two screws
- Hangers are drilled and tapped for use with 3/4" conduit stem as standard and come supplied with a 3/4" - 1/2" reducer for 1/2" conduit stem applications
- Hinged door on TPSC-5075HF allows for hands-free wiring

Certifications and compliances:

- UL1598
- CSA C22.2 No. 250
- Suitable for damp locations

Standard materials and finishes:

- Material – sheet steel
- Finish – zinc chromate for corrosion resistance



Cat. #	Description	Fixture rated (weight lbs.)
TPSFH12	For use with 4" square boxes	50



TPSC-5075HF	For use with 4" square boxes, hands free	75
-------------	--	----

Rating is based on the rating of the outlet box on which it is mounted to.



Cat. #	Description	Fixture rated (weight lbs.)
TPRFH12	For use with 4" round or octagon boxes	50



TPSC-5075HFR	For use with 4" round or octagon boxes, hands free	69
--------------	--	----

Rating is based on the rating of the outlet box on which it is mounted to.

SWAY ADAPTERS

The sway adapter installs quickly and easily to pendant mounted fixtures and compensates for shocks and motion due to movements, vibration, earthquakes or other sources by allowing for lateral movement up to 45 degrees. The sway adapter can be used independently or in conjunction with the Swiv-L-Drop hanger. The sway adapter is also finished in an aesthetically-pleasing white painted finish and is designed for use with 1/2" conduit stems and has 3/8" male threads.



Certifications and compliances:

- UL1598
- Suitable for dry locations

Standard materials and finishes:

- Material – sheet steel
- Finish – sway adapter, painted white

Cat. #	Description
SA 1W	For use with 1/2" conduit stem (male thread is 3/8")

SWIV-L-DROP™ CANOPY HANGERS

The Swiv-L-Drop canopy hanger utilizes a patented spring design to provide vibration and shock protection for pendant mounted fixtures in both horizontal and vertical directions. Designed to fit 3" or 4" outlet boxes, the Swiv-L-Drop is for use with 1/2" fixture conduit stems. The smooth, canopy provides an aesthetically-pleasing appearance and installs quickly and easily without the use of tools.



Certifications and compliances:

- UL1598
- Suitable for dry locations

Standard materials and finishes:

- Material – sheet steel
- Finish – canopy, painted white

Cat. #	Description	Support wt. (lbs.)
S 1 1/2 UNPAINTED	For use with 3" or 4" outlet boxes for use with 1/2" conduit stems; unpainted	50 ^v
S 1 3/8 UNPAINTED	For use with 3/8" conduit stems; unpainted	50 ^v

^v 65 lbs. rated with a minimum 12 inch stem if fully supported by other than an outlet box.