

# Fixture hangers

## FLEXIBLE FIXTURE HANGERS

TPSFH and TPRFH flexible fixture hangers are used in commercial or light industrial applications where HID high bay and low bay lighting fixtures are used. Specific applications include storage facilities, shipping warehouses, retail and DIY facilities.

### Features:

- Suitable for use with 1/2" or 3/4" fixture conduit stems, these hangers allow the conduit stem of the fixture (luminaire) to swing in any direction; maximum swing angle is 26° from vertical max. slope angles 22 1/2°
- Available in two styles: one for attachment to round or octagonal steel boxes; the other for attachment to 4" square steel boxes
- Both styles are quickly and easily attached by two screws
- Hangers are drilled and tapped for use with 3/4" conduit stem as standard and come supplied with a 3/4" – 1/2" reducer for 1/2" conduit stem applications

### Certifications and compliances:

- UL1598
- CSA C22.2 No. 250
- Suitable for damp locations

### Standard materials and finishes:

- Material – sheet steel
- Finish – zinc chromate for corrosion resistance



Cat. #	Description	Support wt. (lbs.)
TPRFH12	For use with 4" round or octagon boxes	50
TPSFH12	For use with 4" square boxes	50

## SWIV-L-DROP™ CANOPY HANGERS

The Swiv-L-Drop canopy hanger utilizes a patented spring design to provide vibration and shock protection for pendant mounted fixtures in both horizontal and vertical directions. Designed to fit 3" or 4" outlet boxes, the Swiv-L-Drop is for use with 1/2" fixture conduit stems. The smooth, canopy provides an aesthetically-pleasing appearance and installs quickly and easily without the use of tools.



### Certifications and compliances:

- UL1598
- Suitable for dry locations

### Standard materials and finishes:

- Material – sheet steel
- Finish – canopy, painted white

Cat. #	Description	Support wt. (lbs.)
S 1 1/2 UNPAINTED	For use with 3" or 4" outlet boxes for use with 1/2" conduit stems; unpainted	50
S 1 3/8 UNPAINTED	For use with 3/8" conduit stems; unpainted	50

50 lbs. rated with a minimum 12 inch stem if fully supported by other than an outlet box.

## SWAY ADAPTERS

The sway adapter installs quickly and easily to pendant mounted fixtures and compensates for shocks and motion due to movements, vibration, earthquakes or other sources by allowing for lateral movement up to 45 degrees. The sway adapter can be used independently or in conjunction with the Swiv-L-Drop hanger. The sway adapter is also finished in an aesthetically-pleasing white painted finish and is designed for use with 1/2" conduit stems and has 3/8" male threads.



### Certifications and compliances:

- UL1598
- Suitable for dry locations

### Standard materials and finishes:

- Material – sheet steel
- Finish – sway adapter, painted white

Cat. #	Description
SA 1W	For use with 1/2" conduit stem (male thread is 3/8")