

# Weatherproof LED

## Applications:

- LED weatherproof luminaires combine the energy efficiency of LED technology with rugged weatherproof construction to provide a versatile residential or commercial outdoor lighting solution

## Features:

- Durable die cast aluminum construction for long product life
- Tool-free adjustable head lamps
- Powder paint finish for corrosive environments
- 3000K warm white color
- Voltage – 120/277V
- Long life, up to 12 years
- Closure plugs, gasket and hardware included
- Suitable for wet locations

## Certifications and compliances:



- cULus Listed
- UL File Nos. E470512 and E514227

## Standard materials:

- Luminaire housing – die cast aluminum
- Lens – polycarbonate

## Standard finish:

- Painted powder coat



TPLEDSL7G



TPLED12G



TPLEDK24G

### SINGLE LUMINAIRES

Cat. #	Description	Lumens	Color	Size / outlet holes	Unit qty.	Wt. lbs. per 100
TPLED12G	(1) 12W LED lampholder	1,000	Gray	1/2"	4	155.0
TPLED12W	(1) 12W LED lampholder	1,000	White	1/2"	4	155.0
TPLED12B	(1) 12W LED lampholder	1,000	Bronze	1/2"	4	155.0

### KITS

Cat. #	Description	Lumens	Color	Size / outlet holes	Unit qty.	Wt. lbs. per 100
TPLEDK24G	(2) 12W LED lights, 4" round box and cover	2,000	Gray	5 - 1/2"	2	252.9
TPLEDK24W	(2) 12W LED lights, 4" round box and cover	2,000	White	5 - 1/2"	2	252.9
TPLEDK24BR	(2) 12W LED lights, 4" round box and cover	2,000	Bronze	5 - 1/2"	2	252.9
TPLEDK24BK	(2) 12W LED lights, 4" round box and cover	2,000	Black	5 - 1/2"	2	252.9

### SPIKE LIGHTS

Cat. #	Description	Lumens	Color	Size / outlet holes	Unit qty.	Wt. lbs. per 100
TPLEDSL7G	(1) 7W LED spike light	500	Gray	–	6	97.9
TPLEDSL7W	(1) 7W LED spike light	500	White	–	6	97.9
TPLEDSL7B	(1) 7W LED spike light	500	Bronze	–	6	97.9

# Lampholders and accessories

## Applications:

- For use in outdoor lighting applications

## Features:

- Durable die cast construction
- Adjustable lampholders
- For use with Par38 bulb (150W maximum)
- Includes installation hardware, gasket, closure plugs and instructions

## Certifications and compliances:

- UL File No. E195204
- CSA C22.2 No. 250.0-08
- cULus

## Standard material:

- Die cast aluminum



TP7162 - TP7165



TP7166



TP7178



TP7186



TP7188 (aluminum)

Cat. #	Description	Color	Unit qty.	Wt. lbs. per 100
TP7162 <b>A U</b>	Universal par lampholder	Natural	36	30.6
TP7163 <b>A U</b>	Universal par lampholder	Gray	36	30.9
TP7164 <b>A U</b>	Universal par lampholder	White	36	30.9
TP7165 <b>A U</b>	Universal par lampholder	Bronze	36	30.9
TP7166 <b>A U</b>	Universal par lampholder with external gasket	Gray	36	33.6
TP7170	External gasket only	Black	100	4.8
TP7178 <b>B U</b>	Universal par lampholder with reflector	Gray	6	41.8
TP7186 <b>B</b>	Portable par lampholder with 6' cord	Gray	12	73.5
TP7188	2-1/2" outside dia. pole fitter with 1/2" male thread	Gray	24	57.6

**A** UL Listed and CSA certified.

**B** cULus Listed.

**U** Third party certified for use with CFL and LED lamps.

Weatherproof

# Motion sensors

## Applications:

- For use with LED or standard lighting kits in outdoor applications

## Features:

- Motion detection with Passive Infrared Technology (PIR)
- Set for motion detection or dusk to dawn
- 240 degree field of view
- Adjustable sensitivity from 5 to 70 feet
- Selectable ON time (Test, 1, 5 or 20 minutes)



## Certifications and compliances:

- cULus Listed
- UL File No. E-464470



### Sensitivity



### On-Time



### Set Mode



## Standard material:

- Non-metallic

Cat. #	Description	Color	Unit qty.	Wt. lbs. per 100
WPMSG	MOTION SENSOR GRY	Gray	2	33.1
WPMSBR	MOTION SENSOR BZ	Bronze	2	33.1
WPMSW	MOTION SENSOR WHT	White	2	33.1

# Lampholder combinations

## Applications:

- For use in outdoor lighting applications with single-gang rectangular or 4" round weatherproof box

## Features:

- Durable die cast construction
- Adjustable lampholders
- For use with Par38 bulb (150W maximum)
- Certified for use with CFL and LED lamps
- Includes installation hardware, gasket, closure plugs and instructions

## Certifications and compliances:

- cULus
- UL File No. E195204



## Standard material:

- Die cast aluminum



TP7325



TP7334

### RECTANGULAR COVER COMBINATIONS

Cat. #	Description	Outlet holes	Color	Unit qty.	Wt. lbs. per 100
TP7325	(1) par lampholder	1 - 1/2"	Gray	8	42.1
TP7334	(2) par lampholder	3 - 1/2"	Gray	8	76.2
TP7335	(2) par lampholder	3 - 1/2"	White	8	76.2
TP7333	(2) par lampholder	3 - 1/2"	Bronze	8	76.2



TP7328



TP7330 - TP7332

### 4" ROUND COVER COMBINATIONS

Cat. #	Description	Outlet holes	Color	Unit qty.	Wt. lbs. per 100
TP7328	(1) par lampholder	1 - 1/2"	Gray	8	42.6
TP7329	(1) par lampholder	1 - 1/2"	White	8	42.6
TP7327	(1) par lampholder	1 - 1/2"	Bronze	8	42.6
TP7330	(2) par lampholder	3 - 1/2"	Gray	10	81.4
TP7331	(2) par lampholder	3 - 1/2"	White	10	81.4
TP7332	(2) par lampholder	3 - 1/2"	Bronze	10	81.4

Weatherproof

# Lampholder kits

## Applications:

- For use in outdoor lighting applications

## Features:

- Ready to install lighting kit
- Durable die cast construction
- Adjustable lampholders
- For use with Par38 bulb (150W maximum)
- Certified for use with CFL and LED lamps
- Includes installation hardware, gasket, closure plugs and instructions



TP7340



TP7345

Cat. #	Description	Outlet holes	Color	Unit qty.	Wt. lbs. per 100
TP7340	Box, cover, (2) lampholders	2 - 1/2"	Gray	4	129.0
TP7345	Box, cover, photocell, (2) lampholders	2 - 1/2"	Gray	4	163.4
TP7346	Box, cover, photocell, (2) lampholders	2 - 1/2"	White	4	163.4

## Certifications and compliances:

- cULus
- UL File No. E195204



## Standard material:

- Die cast aluminum

Weatherproof