

SG72911



Description

- High-quality miniature circuit breakers for commercial and residential applications
- Contact position indicator red - green
- Guide for secure terminal connection
- 3-position DIN rail clip, permits removal from existing busbar system
- Comprehensive range of accessories can be mounted subsequently
- Rated currents up to 63 A
- Tripping characteristics B, C, D
- Rated breaking capacity 6 kA according to IEC/EN 60898-1

SG28911

Rated current
 I_n (A)Type
Designation

Article No.

Units per
package**6 kA, Characteristic B****1-pole**

Rated current I_n (A)	Type Designation	Article No.	Units per package
1	PLS6-B1	242640	12/120
1.5	PLS6-B1,5	242641	12/120
1.6	PLS6-B1,6	242642	12/120
2	PLS6-B2	242643	12/120
2.5	PLS6-B2,5	242644	12/120
3	PLS6-B3	242645	12/120
3.5	PLS6-B3,5	242646	12/120
4	PLS6-B4	242647	12/120
5	PLS6-B5	242648	12/120
6	PLS6-B6	242649	12/120
8	PLS6-B8	242650	12/120
10	PLS6-B10	242651	12/120
12	PLS6-B12	242652	12/120
13	PLS6-B13	242653	12/120
15	PLS6-B15	242654	12/120
16	PLS6-B16	242655	12/120
20	PLS6-B20	242656	12/120
25	PLS6-B25	242657	12/120
32	PLS6-B32	242658	12/120
40	PLS6-B40	242659	12/120
50	PLS6-B50	242660	12/120
63	PLS6-B63	242661	12/120

SG40111

**1+N-pole 1.5MU**

Rated current I_n (A)	Type Designation	Article No.	Units per package
1	PLS6-B1/1N	242709	8/80
1.5	PLS6-B1,5/1N	242710	8/80
1.6	PLS6-B1,6/1N	242711	8/80
2	PLS6-B2/1N	242712	8/80
2.5	PLS6-B2,5/1N	242713	8/80
3	PLS6-B3/1N	242714	8/80
3.5	PLS6-B3,5/1N	242715	8/80
4	PLS6-B4/1N	242716	8/80
5	PLS6-B5/1N	242717	8/80
6	PLS6-B6/1N	242718	8/80
8	PLS6-B8/1N	242719	8/80
10	PLS6-B10/1N	242720	8/80
12	PLS6-B12/1N	242721	8/80
13	PLS6-B13/1N	242722	8/80
15	PLS6-B15/1N	242723	8/80
16	PLS6-B16/1N	242724	8/80
20	PLS6-B20/1N	242725	8/80
25	PLS6-B25/1N	242726	8/80
32	PLS6-B32/1N	242727	8/80

SG58211



Rated current I_n (A)	Type Designation	Article No.	Units per package
1+N-pole 2MU			
1	PLZ6-B1/1N	242770	1/60
1.5	PLZ6-B1,5/1N	242771	1/60
1.6	PLZ6-B1,6/1N	242772	1/60
2	PLZ6-B2/1N	242773	1/60
2.5	PLZ6-B2,5/1N	242774	1/60
3	PLZ6-B3/1N	242775	1/60
3.5	PLZ6-B3,5/1N	242776	1/60
4	PLZ6-B4/1N	242777	1/60
5	PLZ6-B5/1N	242778	1/60
6	PLZ6-B6/1N	242779	1/60
8	PLZ6-B8/1N	242780	1/60
10	PLZ6-B10/1N	242781	1/60
12	PLZ6-B12/1N	242782	1/60
13	PLZ6-B13/1N	242783	1/60
15	PLZ6-B15/1N	242784	1/60
16	PLZ6-B16/1N	242785	1/60
20	PLZ6-B20/1N	242786	1/60
25	PLZ6-B25/1N	242787	1/60
32	PLZ6-B32/1N	242788	1/60
40	PLZ6-B40/1N	242789	1/60
50	PLZ6-B50/1N	242790	1/60
63	PLZ6-B63/1N	242791	1/60

SG77911



Rated current I_n (A)	Type Designation	Article No.	Units per package
2-pole			
1	PLS6-B1/2	242839	1/60
1.5	PLS6-B1,5/2	242840	1/60
1.6	PLS6-B1,6/2	242841	1/60
2	PLS6-B2/2	242842	1/60
2.5	PLS6-B2,5/2	242843	1/60
3	PLS6-B3/2	242844	1/60
3.5	PLS6-B3,5/2	242845	1/60
4	PLS6-B4/2	242846	1/60
5	PLS6-B5/2	242847	1/60
6	PLS6-B6/2	242848	1/60
8	PLS6-B8/2	242849	1/60
10	PLS6-B10/2	242850	1/60
12	PLS6-B12/2	242851	1/60
13	PLS6-B13/2	242852	1/60
15	PLS6-B15/2	242853	1/60
16	PLS6-B16/2	242854	1/60
20	PLS6-B20/2	242855	1/60
25	PLS6-B25/2	242856	1/60
32	PLS6-B32/2	242857	1/60
40	PLS6-B40/2	242858	1/60
50	PLS6-B50/2	242859	1/60
63	PLS6-B63/2	242860	1/60

SG74311



Rated current I_n (A)	Type Designation	Article No.	Units per package
3-pole			
1	PLS6-B1/3	242908	1/40
1.5	PLS6-B1,5/3	242909	1/40
1.6	PLS6-B1,6/3	242910	1/40
2	PLS6-B2/3	242911	1/40
2.5	PLS6-B2,5/3	242912	1/40
3	PLS6-B3/3	242913	1/40
3.5	PLS6-B3,5/3	242914	1/40
4	PLS6-B4/3	242915	1/40
5	PLS6-B5/3	242916	1/40
6	PLS6-B6/3	242917	1/40
8	PLS6-B8/3	242918	1/40
10	PLS6-B10/3	242919	1/40
12	PLS6-B12/3	242920	1/40
13	PLS6-B13/3	242921	1/40
15	PLS6-B15/3	242922	1/40
16	PLS6-B16/3	242923	1/40
20	PLS6-B20/3	242924	1/40
25	PLS6-B25/3	242925	1/40
32	PLS6-B32/3	242926	1/40
40	PLS6-B40/3	242927	1/40
50	PLS6-B50/3	242928	1/40
63	PLS6-B63/3	242929	1/40

SG73811



Rated current I_n (A)	Type Designation	Article No.	Units per package
3+N-pole			
1	PLS6-B1/3N	242977	1/30
1.5	PLS6-B1,5/3N	242978	1/30
1.6	PLS6-B1,6/3N	242979	1/30
2	PLS6-B2/3N	242980	1/30
2.5	PLS6-B2,5/3N	242981	1/30
3	PLS6-B3/3N	242982	1/30
3.5	PLS6-B3,5/3N	242983	1/30
4	PLS6-B4/3N	242984	1/30
5	PLS6-B5/3N	242985	1/30
6	PLS6-B6/3N	242986	1/30
8	PLS6-B8/3N	242987	1/30
10	PLS6-B10/3N	242988	1/30
12	PLS6-B12/3N	242989	1/30
13	PLS6-B13/3N	242990	1/30
15	PLS6-B15/3N	242991	1/30
16	PLS6-B16/3N	242992	1/30
20	PLS6-B20/3N	242993	1/30
25	PLS6-B25/3N	242994	1/30
32	PLS6-B32/3N	242995	1/30
40	PLS6-B40/3N	242996	1/30
52	PLS6-B50/3N	242997	1/30
63	PLS6-B63/3N	242998	1/30

SG70011



Rated current I_n (A)	Type Designation	Article No.	Units per package
4-pole			
1	PLS6-B1/4	243046	1/30
1.5	PLS6-B1,5/4	243047	1/30
1.6	PLS6-B1,6/4	243048	1/30
2	PLS6-B2/4	243049	1/30
2.5	PLS6-B2,5/4	243050	1/30
3	PLS6-B3/4	243051	1/30
3.5	PLS6-B3,5/4	243052	1/30
4	PLS6-B4/4	243053	1/30
5	PLS6-B5/4	243054	1/30
6	PLS6-B6/4	243055	1/30
8	PLS6-B8/4	243056	1/30
10	PLS6-B10/4	243057	1/30
12	PLS6-B12/4	243058	1/30
13	PLS6-B13/4	243059	1/30
15	PLS6-B15/4	243060	1/30
16	PLS6-B16/4	243061	1/30
20	PLS6-B20/4	243062	1/30
25	PLS6-B25/4	243063	1/30
32	PLS6-B32/4	243064	1/30
40	PLS6-B40/4	243065	1/30
50	PLS6-B50/4	243066	1/30
63	PLS6-B63/4	243067	1/30

SG28911



Rated current I_n (A)	Type Designation	Article No.	Units per package
6 kA, Characteristic C			
1-pole			
0.16	PLS6-C0.16	242662	12/120
0.25	PLS6-C0,25	242663	12/120
0.5	PLS6-C0,5	242665	12/120
0.75	PLS6-C0,75	242664	12/120
1	PLS6-C1	242666	12/120
1.5	PLS6-C1,5	242667	12/120
1.6	PLS6-C1,6	242668	12/120
2	PLS6-C2	242669	12/120
2.5	PLS6-C2,5	242670	12/120
3	PLS6-C3	242671	12/120
3.5	PLS6-C3,5	242672	12/120
4	PLS6-C4	242673	12/120
5	PLS6-C5	242674	12/120
6	PLS6-C6	242675	12/120
8	PLS6-C8	242676	12/120
10	PLS6-C10	242677	12/120
12	PLS6-C12	242678	12/120
13	PLS6-C13	242679	12/120
15	PLS6-C15	242680	12/120
16	PLS6-C16	242681	12/120
20	PLS6-C20	242682	12/120
25	PLS6-C25	242683	12/120
32	PLS6-C32	242684	12/120
40	PLS6-C40	242685	12/120
50	PLS6-C50	242686	12/120
63	PLS6-C63	242687	12/120

SG40111



1+N-pole 1.5MU			
0.16	PLS6-C0.16/1N	242728	8/80
0.25	PLS6-C0,25/1N	242729	8/80
0.5	PLS6-C0,5/1N	242731	8/80
0.75	PLS6-C0,75/1N	242730	8/80
1	PLS6-C1/1N	242732	8/80
1.5	PLS6-C1,5/1N	242733	8/80
1.6	PLS6-C1,6/1N	242734	8/80
2	PLS6-C2/1N	242735	8/80
2.5	PLS6-C2,5/1N	242736	8/80
3	PLS6-C3/1N	242737	8/80
3.5	PLS6-C3,5/1N	242738	8/80
4	PLS6-C4/1N	242739	8/80
5	PLS6-C5/1N	242740	8/80
6	PLS6-C6/1N	242741	8/80
8	PLS6-C8/1N	242742	8/80
10	PLS6-C10/1N	242743	8/80
12	PLS6-C12/1N	242744	8/80
13	PLS6-C13/1N	242745	8/80
15	PLS6-C15/1N	242746	8/80
16	PLS6-C16/1N	242747	8/80
20	PLS6-C20/1N	242748	8/80
25	PLS6-C25/1N	242749	8/80
32	PLS6-C32/1N	242750	8/80

SG58211



Rated current I_n (A)	Type Designation	Article No.	Units per package
1+N-pole 2MU			
0.16	PLZ6-C0.16/1N	242792	1/60
0.25	PLZ6-C0,25/1N	242793	1/60
0.5	PLZ6-C0,5/1N	242795	1/60
0.75	PLZ6-C0,75/1N	242794	1/60
1	PLZ6-C1/1N	242796	1/60
1.5	PLZ6-C1,5/1N	242797	1/60
1.6	PLZ6-C1,6/1N	242798	1/60
2	PLZ6-C2/1N	242799	1/60
2.5	PLZ6-C2,5/1N	242800	1/60
3	PLZ6-C3/1N	242801	1/60
3.5	PLZ6-C3,5/1N	242802	1/60
4	PLZ6-C4/1N	242803	1/60
5	PLZ6-C5/1N	242804	1/60
6	PLZ6-C6/1N	242805	1/60
8	PLZ6-C8/1N	242806	1/60
10	PLZ6-C10/1N	242807	1/60
12	PLZ6-C12/1N	242808	1/60
13	PLZ6-C13/1N	242809	1/60
15	PLZ6-C15/1N	242810	1/60
16	PLZ6-C16/1N	242811	1/60
20	PLZ6-C20/1N	242812	1/60
25	PLZ6-C25/1N	242813	1/60
32	PLZ6-C32/1N	242814	1/60
40	PLZ6-C40/1N	242815	1/60
50	PLZ6-C50/1N	242816	1/60
63	PLZ6-C63/1N	242817	1/60

SG77911



2-pole			
0.16	PLS6-C0.16/2	242861	1/60
0.25	PLS6-C0,25/2	242862	1/60
0.5	PLS6-C0,5/2	242864	1/60
0.75	PLS6-C0,75/2	242863	1/60
1	PLS6-C1/2	242865	1/60
1.5	PLS6-C1,5/2	242866	1/60
1.6	PLS6-C1,6/2	242867	1/60
2	PLS6-C2/2	242868	1/60
2.5	PLS6-C2,5/2	242869	1/60
3	PLS6-C3/2	242870	1/60
3.5	PLS6-C3,5/2	242871	1/60
4	PLS6-C4/2	242872	1/60
5	PLS6-C5/2	242873	1/60
6	PLS6-C6/2	242874	1/60
8	PLS6-C8/2	242875	1/60
10	PLS6-C10/2	242876	1/60
12	PLS6-C12/2	242877	1/60
13	PLS6-C13/2	242878	1/60
15	PLS6-C15/2	242879	1/60
16	PLS6-C16/2	242880	1/60
20	PLS6-C20/2	242881	1/60
25	PLS6-C25/2	242882	1/60
32	PLS6-C32/2	242883	1/60
40	PLS6-C40/2	242884	1/60
50	PLS6-C50/2	242885	1/60
63	PLS6-C63/2	242886	1/60

SG74311



Rated current I_n (A)	Type Designation	Article No.	Units per package
3-pole			
0.16	PLS6-C0.16/3	242930	1/40
0.25	PLS6-C0,25/3	242931	1/40
0.5	PLS6-C0,5/3	242933	1/40
0.75	PLS6-C0,75/3	242932	1/40
1	PLS6-C1/3	242934	1/40
1.5	PLS6-C1,5/3	242935	1/40
1.6	PLS6-C1,6/3	242936	1/40
2	PLS6-C2/3	242937	1/40
2.5	PLS6-C2,5/3	242938	1/40
3	PLS6-C3/3	242939	1/40
3.5	PLS6-C3,5/3	242940	1/40
4	PLS6-C4/3	242941	1/40
5	PLS6-C5/3	242942	1/40
6	PLS6-C6/3	242943	1/40
8	PLS6-C8/3	242944	1/40
10	PLS6-C10/3	242945	1/40
12	PLS6-C12/3	242946	1/40
13	PLS6-C13/3	242947	1/40
15	PLS6-C15/3	242948	1/40
16	PLS6-C16/3	242949	1/40
20	PLS6-C20/3	242950	1/40
25	PLS6-C25/3	242951	1/40
32	PLS6-C32/3	242952	1/40
40	PLS6-C40/3	242953	1/40
50	PLS6-C50/3	242954	1/40
63	PLS6-C63/3	242955	1/40

SG73911



Rated current I_n (A)	Type Designation	Article No.	Units per package
3+N-pole			
0.16	PLS6-C0.16/3N	242999	1/30
0.25	PLS6-C0,25/3N	243000	1/30
0.5	PLS6-C0,5/3N	243002	1/30
0.75	PLS6-C0,75/3N	243001	1/30
1	PLS6-C1/3N	243003	1/30
1.5	PLS6-C1,5/3N	243004	1/30
1.6	PLS6-C1,6/3N	243005	1/30
2	PLS6-C2/3N	243006	1/30
2.5	PLS6-C2,5/3N	243007	1/30
3	PLS6-C3/3N	243008	1/30
3.5	PLS6-C3,5/3N	243009	1/30
4	PLS6-C4/3N	243010	1/30
5	PLS6-C5/3N	243011	1/30
6	PLS6-C6/3N	243012	1/30
8	PLS6-C8/3N	243013	1/30
10	PLS6-C10/3N	243014	1/30
12	PLS6-C12/3N	243015	1/30
13	PLS6-C13/3N	243016	1/30
15	PLS6-C15/3N	243017	1/30
16	PLS6-C16/3N	243018	1/30
20	PLS6-C20/3N	243019	1/30
25	PLS6-C25/3N	243020	1/30
32	PLS6-C32/3N	243021	1/30
40	PLS6-C40/3N	243022	1/30
50	PLS6-C50/3N	243023	1/30
63	PLS6-C63/3N	243024	1/30

SG70011



Rated current I_n (A)	Type Designation	Article No.	Units per package
4-pole			
0.16	PLS6-C0.16/4	243068	1/30
0.25	PLS6-C0,25/4	243069	1/30
0.5	PLS6-C0,5/4	243071	1/30
0.75	PLS6-C0,75/4	243070	1/30
1	PLS6-C1/4	243072	1/30
1.5	PLS6-C1,5/4	243073	1/30
1.6	PLS6-C1,6/4	243074	1/30
2	PLS6-C2/4	243075	1/30
2.5	PLS6-C2,5/4	243076	1/30
3	PLS6-C3/4	243077	1/30
3.5	PLS6-C3,5/4	243078	1/30
4	PLS6-C4/4	243079	1/30
5	PLS6-C5/4	243080	1/30
6	PLS6-C6/4	243081	1/30
8	PLS6-C8/4	243082	1/30
10	PLS6-C10/4	243083	1/30
12	PLS6-C12/4	243084	1/30
13	PLS6-C13/4	243085	1/30
15	PLS6-C15/4	243086	1/30
16	PLS6-C16/4	243087	1/30
20	PLS6-C20/4	243088	1/30
25	PLS6-C25/4	243089	1/30
32	PLS6-C32/4	243090	1/30
40	PLS6-C40/4	243091	1/30
50	PLS6-C50/4	243092	1/30
63	PLS6-C63/4	243093	1/30

1.302 Protective Devices

Miniature Circuit Breakers PLS6, PLZ6 (MW)

xPole

SG28911



Rated current I_n (A)	Type Designation	Article No.	Units per package
----------------------------	---------------------	-------------	----------------------

6 kA, Characteristic D

1-pole

1	PLS6-D1	242689	12/120
1.5	PLS6-D1,5	242690	12/120
1.6	PLS6-D1,6	242691	12/120
2	PLS6-D2	242692	12/120
2.5	PLS6-D2,5	242693	12/120
3	PLS6-D3	242694	12/120
3.5	PLS6-D3,5	242695	12/120
4	PLS6-D4	242696	12/120
5	PLS6-D5	242697	12/120
6	PLS6-D6	242698	12/120
8	PLS6-D8	242699	12/120
10	PLS6-D10	242700	12/120
12	PLS6-D12	242701	12/120
13	PLS6-D13	242702	12/120
15	PLS6-D15	242703	12/120
16	PLS6-D16	242704	12/120
20	PLS6-D20	242705	12/120
25	PLS6-D25	242706	12/120
32	PLS6-D32	242707	12/120
40	PLS6-D40	242708	12/120

SG40111



1+N-pole 1.5MU

0.5	PLS6-D0,5/1N	242751	8/80
1	PLS6-D1/1N	242752	8/80
1.5	PLS6-D1,5/1N	242753	8/80
1.6	PLS6-D1,6/1N	242754	8/80
2	PLS6-D2/1N	242755	8/80
2.5	PLS6-D2,5/1N	242756	8/80
3	PLS6-D3/1N	242757	8/80
3.5	PLS6-D3,5/1N	242758	8/80
4	PLS6-D4/1N	242759	8/80
5	PLS6-D5/1N	242760	8/80
6	PLS6-D6/1N	242761	8/80
8	PLS6-D8/1N	242762	8/80
10	PLS6-D10/1N	242763	8/80
12	PLS6-D12/1N	242764	8/80
13	PLS6-D13/1N	242765	8/80
15	PLS6-D15/1N	242766	8/80
16	PLS6-D16/1N	242767	8/80
20	PLS6-D20/1N	242768	8/80
25	PLS6-D25/1N	242769	8/80

SG58211



Rated current I_n (A)	Type Designation	Article No.	Units per package
1+N-pole 2MU			
0.5	PLZ6-D0,5/1N	242818	1/60
1	PLZ6-D1/1N	242819	1/60
1.5	PLZ6-D1,5/1N	242820	1/60
1.6	PLZ6-D1,6/1N	242821	1/60
2	PLZ6-D2/1N	242822	1/60
2.5	PLZ6-D2,5/1N	242823	1/60
3	PLZ6-D3/1N	242824	1/60
3.5	PLZ6-D3,5/1N	242825	1/60
4	PLZ6-D4/1N	242826	1/60
5	PLZ6-D5/1N	242827	1/60
6	PLZ6-D6/1N	242828	1/60
8	PLZ6-D8/1N	242829	1/60
10	PLZ6-D10/1N	242830	1/60
12	PLZ6-D12/1N	242831	1/60
13	PLZ6-D13/1N	242832	1/60
15	PLZ6-D15/1N	242833	1/60
16	PLZ6-D16/1N	242834	1/60
20	PLZ6-D20/1N	242835	1/60
25	PLZ6-D25/1N	242836	1/60
32	PLZ6-D32/1N	242837	1/60
40	PLZ6-D40/1N	242838	1/60

SG77911



Rated current I_n (A)	Type Designation	Article No.	Units per package
2-pole			
0.5	PLS6-D0,5/2	242887	1/60
1	PLS6-D1/2	242888	1/60
1.5	PLS6-D1,5/2	242889	1/60
1.6	PLS6-D1,6/2	242890	1/60
2	PLS6-D2/2	242891	1/60
2.5	PLS6-D2,5/2	242892	1/60
3	PLS6-D3/2	242893	1/60
3.5	PLS6-D3,5/2	242894	1/60
4	PLS6-D4/2	242895	1/60
5	PLS6-D5/2	242896	1/60
6	PLS6-D6/2	242897	1/60
8	PLS6-D8/2	242898	1/60
10	PLS6-D10/2	242899	1/60
12	PLS6-D12/2	242900	1/60
13	PLS6-D13/2	242901	1/60
15	PLS6-D15/2	242902	1/60
16	PLS6-D16/2	242903	1/60
20	PLS6-D20/2	242904	1/60
25	PLS6-D25/2	242905	1/60
32	PLS6-D32/2	242906	1/60
40	PLS6-D40/2	242907	1/60

1.304 Protective Devices

xPole

Miniature Circuit Breakers PLS6, PLZ6 (MW)

SG74311



Rated current I_n (A)	Type Designation	Article No.	Units per package
3-pole			
0.5	PLS6-D0,5/3	242956	1/40
1	PLS6-D1/3	242957	1/40
1.5	PLS6-D1,5/3	242958	1/40
1.6	PLS6-D1,6/3	242959	1/40
2	PLS6-D2/3	242960	1/40
2.5	PLS6-D2,5/3	242961	1/40
3	PLS6-D3/3	242962	1/40
3.5	PLS6-D3,5/3	242963	1/40
4	PLS6-D4/3	242964	1/40
5	PLS6-D5/3	242965	1/40
6	PLS6-D6/3	242966	1/40
8	PLS6-D8/3	242967	1/40
10	PLS6-D10/3	242968	1/40
12	PLS6-D12/3	242969	1/40
13	PLS6-D13/3	242970	1/40
15	PLS6-D15/3	242971	1/40
16	PLS6-D16/3	242972	1/40
20	PLS6-D20/3	242973	1/40
25	PLS6-D25/3	242974	1/40
32	PLS6-D32/3	242975	1/40
40	PLS6-D40/3	242976	1/40

SG73911



Rated current I_n (A)	Type Designation	Article No.	Units per package
3+N-pole			
0.5	PLS6-D0,5/3N	243025	1/30
1	PLS6-D1/3N	243026	1/30
1.5	PLS6-D1,5/3N	243027	1/30
1.6	PLS6-D1,6/3N	243028	1/30
2	PLS6-D2/3N	243029	1/30
2.5	PLS6-D2,5/3N	243030	1/30
3	PLS6-D3/3N	243031	1/30
3.5	PLS6-D3,5/3N	243032	1/30
4	PLS6-D4/3N	243033	1/30
5	PLS6-D5/3N	243034	1/30
6	PLS6-D6/3N	243035	1/30
8	PLS6-D8/3N	243036	1/30
10	PLS6-D10/3N	243037	1/30
12	PLS6-D12/3N	243038	1/30
13	PLS6-D13/3N	243039	1/30
15	PLS6-D15/3N	243040	1/30
16	PLS6-D16/3N	243041	1/30
20	PLS6-D20/3N	243042	1/30
25	PLS6-D25/3N	243043	1/30
32	PLS6-D32/3N	243044	1/30
40	PLS6-D40/3N	243045	1/30

SG70011



Rated current I_n (A)	Type Designation	Article No.	Units per package
4-pole			
0.5	PLS6-D0,5/4	243094	1/30
1	PLS6-D1/4	243095	1/30
1.5	PLS6-D1,5/4	243096	1/30
1.6	PLS6-D1,6/4	243097	1/30
2	PLS6-D2/4	243098	1/30
2.5	PLS6-D2,5/4	243099	1/30
3	PLS6-D3/4	243100	1/30
3.5	PLS6-D3,5/4	243101	1/30
4	PLS6-D4/4	243102	1/30
5	PLS6-D5/4	243103	1/30
6	PLS6-D6/4	243104	1/30
8	PLS6-D8/4	243105	1/30
10	PLS6-D10/4	243106	1/30
12	PLS6-D12/4	243107	1/30
13	PLS6-D13/4	243108	1/30
15	PLS6-D15/4	243109	1/30
16	PLS6-D16/4	243110	1/30
20	PLS6-D20/4	243111	1/30
25	PLS6-D25/4	243112	1/30
32	PLS6-D32/4	243113	1/30
40	PLS6-D40/4	243114	1/30