





REVISION

REV	DESCRIPTION	BY	DATE	CHANGE NO.
B	LATEST STANDARDS UPDATED IN HSF OUTLINE DRAWINGS	JVM	06/09/2012	I3025



MODEL VERSION: 01 MODEL SOURCE FILE: 1000001494	MATERIAL:	VARIOUS	<small>UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE IN MILLIMETERS.</small> TOLERANCES UNLESS OTHERWISE SPECIFIED: GENERAL ± 0.2mm ANGULAR ± 1°			COOPER Bussmann (UK) Ltd Burton-on-the-Wolds, Leics, LE12 5TH Tel +44 1509 882 600 Fax +44 1509 882786	
	FINISH:	NONE	UNCONTROLLED COPY	TITLE: PV-(amp)A2XL-B-15			
	SURFACE AREA:	VARIOUSmm ²	THIS DRAWING IS CONFIDENTIAL AND THE COPYRIGHT OF COOPER BUSSMANN AND MUST NOT BE COPIED OR PASSED ON TO A THIRD PARTY WITHOUT WRITTEN CONSENT	DWG NO: 1000001494		ANGLE:	REV:
	VOLUME:			DRAWN BY:	CHECKED BY:	DATE:	SCALE:
MASS:		GT	NN	17/03/11	NTS	A3	1 OF 1