

Eaton's Custom Toolbox Solutions

Stay Organized, Be Prepared,
Reduce Downtime!

Proactively reduce the risk of being stranded without parts! Choose one, or bundle all three kits so that you will have confidence when tackling your most common pilot device (22mm / 30mm) or limit switch needs.



SENSORS-PACKOUT



M22-PACKOUT



10250T-PACKOUT



Reduce downtime by having components at your fingertips



Kits include most common replacement parts so you're always ready



Available now from your Eaton authorized distributor

EATON

Powering Business Worldwide

Milwaukee
PACKOUT

SENSORS-PACKOUT

Item	Description	Quantity
E50AR1	E50 LIMIT SWITCH, 1NO/1NC, SIDE ROTARY	1
E50DR1	E50 STANDARD SPRING RETURN HEAD	1
E50DW1	E50 WOBBLE HEAD, STD. DUTY SPG RETURN	1
E50KL355	E50 ROLLER LEVER - 1-1/2"	1
E50KL538	E50 ADJUSTABLE ROLLER LEVER	1
E50KL541	E50 FORK LEVER - METAL ROLLER	1
E50KL544	E50 FORK LEVER - METAL ROLLERS	1
E50KL581	E50 ADJUSTABLE ROD LEVER - METAL ROD	1
E50KW3	E50 WOBBLE HEAD OPERATOR - STAINLESS	1
E50RA	E50 RECEPTACLE, SINGLE POLE, 5 TERMINAL	1
E50RB	E50 RECEPTACLE - DOUBLE POLE	1
E50SA	E50 SWITCH BODY - SINGLE POLE	1
E50SAL	E50 SWITCH BODY, SNG POLE W/LED	1
E50SB	E50 SWITCH BODY - DBL POLE	1
E50SBL	E50 SWITCH BODY - DOUBLE POLE W/LED	1

M22-PACKOUT

Item	Description	Quantity
M22-DL-G	M22-DL-G ILL MOM PB SIL-BZL FLSH GRN	1
M22-DL-R	M22-DL-R ILL MOM PB SIL-BZL FLSH RED	1
M22-DR-X	M22-DR-X NON-ILL MTN PB SIL-BZL BUTTONLESS	2
M22-K01	M22-K01 CONTACT BLOCK 1NC SCREW TERM	4
M22-K10	CONTACT BLCK 1NO SCREW TERM	6
M22-LED230-W	WHT LGHT UNIT 85-264VAC SCREW TERM	2
M22-L-G	M22-L-G IND LGHT GRN	1
M22-L-R	M22-L-R IND LGHT RED	1
M22-L-Y	M22-L-Y IND LGHT YEL	1
M22-MS	M22-MS MOUNTING RING TOOL	1
M22-PRG-SCRDRV	M22 PROMOTIONAL SCREWDRIVER	1
M22-PVT	M22-PVT E-STOP TWIST-RELEASE	1
M22S-R30	ADAPTER RING SET FOR 30MM HOLES	1
M22-RJ45-SA	M22 RJ45 SOCKET	1
M22-WK3	M22-WK3 NON-ILL 3-POS MOM SEL SWTCH THB-GP SIL-BZL	1
M22-WKV	M22-WKV NON-ILL V-POS MTN SEL SWTCH THB-GP SIL-BZL	1
M22-XD-SWRGYB	FLSH BUTTON 6-PACK FOR NON-ILL PB	1
M22-FLED-RGB	MULTI-COLOUR LED INDICATOR LIGHT (RED, GREEN, BLUE, YELLOW, WHITE, VIOLET, TURQUOISE)	1

10250T-PACKOUT

Item	Description	Quantity
10250T1	PUSHBUTTON CONTACT BLOCK WITH 1NO-1NC CONTACTS	2
10250T101	FLUSH BLACK PUSHBUTTON	2
10250T102	FLUSH RED PUSHBUTTON	2
10250T103	FLUSH GREEN PUSHBUTTON	2
10250T1311	SEL. SW. OPERATOR 2 POSITION KNOB	2
10250T1323	SEL. SW. OPERATOR 3 POSITION CAM3 KNOB	2
10250T197L	IND LIGHT OPERATOR W/O LENSE OR LAMP	2
10250T2	CONTACT BLOCK 2NO	2
10250T297L	PRES-TEST OPERATOR W/O LENSE OR LAMP	2
10250T3	CONTACT BLOCK 2NC	2
10250T397L	ILL PUSHBUTTON OPERATOR W/O LENSE OR LAMP	1
10250T5	2 POS MAIN PUSH-PULL OPERATOR	2
10250T53	CONTACT BLOCK 1NO	2
10250T9	3 POS MOM-PULL, MAIN-PUSH OPERATOR	1
10250TA101	FINGER PROOF SHROUD	2
10250TA7	HOLE PLUG	4
10250TB63	PUSH-PULL RED ENGR, "EMERGENCY STOP" NON-ILLUM BUTTON	1
10250TC19N	AMBER PLASTIC LENS FOR 10250T IND LIGHT	1
10250TC1N	RED PLASTIC LENS FOR 10250T IND LIGHT	1
10250TC21	RED PLASTIC LENS FOR 10250T ILLUM PB	1
10250TC22	GREEN PLASTIC LENS FOR 10250T ILLUM PB	1
10250TC24	BLUE PLASTIC LENS FOR 10250T ILLUM PB	2
10250TC2N	GREEN PLASTIC LENS FOR 10250T IND LIGHT	1
10250TC43	AMBER PLASTIC LENS FOR 10250T ILLUM PB	2
10250TC53	PUSH-PULL RED ENGR, "EMERGENCY STOP" ILLUM LENS	1
10250TK3	THRUST WASHER	2
10250TLB	SEL. SW. OPERATOR LEVER	2
10250TM24	1/2 ROUND LEGEND PLATE "OFF"	2
10250TM25	1/2 ROUND LEGEND PLATE "ON"	2
10250TM33	1/2 ROUND LEGEND PLATE "START"	2
10250TM34	1/2 ROUND LEGEND PLATE "STOP"	2
10250TM49	S.S. LEGEND PLATE "AUTO OFF HAND" 1/2RND	2
10250TM67	NAMEPLATE - "MAN AUTO"	2
10250TM84	1/2 ROUND LEGEND PLATE "TRIP"	2
E22LED120WN	WHITE LED BULB 120V AC/DC	6
RPBKITZD01	COMPONENT KIT FOR RESET BUTTON	2

