

## Eaton HMAX Efficiency Statement

The HMAX rated for 480V operation is at least 97.5% efficient within 60-100% output frequency and between 20-100% torque for all frame sizes given a maximum switching frequency no higher than the default switching frequency of the drive at 40° C ambient temperature.

The HMAX rated for 230V operation is at least 96.5% efficient within 80-100% output frequency and between 20-70% torque for all frame sizes given a maximum switching frequency no higher than the default switching frequency of the drive at 40° C ambient temperature.



*Powering Business Worldwide*

## Additional Help

In the US or Canada: please contact the Technical Resource Center at 1-877-ETN-CARE or 1-877-326-2273.

All other supporting documentation is located on the Eaton web site at [www.eaton.com](http://www.eaton.com)

