









FR6 Dimension drawing



IP21/IP54 Metric










Type 1/12 UL



Minimum dimensions
A= Air gap around drive
B= Space between two drives or drive and e.g. cabinet
C= Free space above drive
D= Free space below drive

FR6 Dimension drawing flange mount



Minimum dimensions
A= Air gap around drive
B= Space between two drives or drive and e.g. cabinet
C= Free space above drive
D= Free space below drive