




1. TYPE XB4
2. UL LISTING NO. E187894, CLASS I, DIV. I, GROUPS C&D
AMBIENT TEMP. -67°F TO +158°F (-55° TO +70°)
3. WEIGHT:- 14.5 LBS (6.6 Kg)APPROX.
4. MATERIAL: - BODY & LID - ALUMINIUM ALLOY LM25TF
LENS - GLASS
5. IDENTITY/TAG LABEL LETTER SIZE 3/16" (5 mm) MAX.
6. TERMINALS SUITABLE FOR UP TO 10 AWG (6mm²).

DO NOT SCALE



7. 1/2" OR 3/4" NPT ENTRIES AVAILABLE AT POS. 1, 2 AND 3
8. UL LISTED SEALANT TO BE APPLIED TO ALL GLANDS
AND BLANKING PLUGS.
9. GENERAL TOLERANCE $\pm 3/32"$ (± 2 mm)



Cooper MEDC Ltd, Unit B, Sutton Parkway,
Oddicroft Lane, Sutton-in-Ashfield,
Nottinghamshire, NG17 5FB, U.K.
Tel: +44 (0) 1623 444400
web: www.coopermedc.com

DESIGNERS & MANUFACTURERS
OF ELECTRICAL & ELECTRONIC
EQUIPMENT & SYSTEMS FOR
HAZARDOUS AREAS

ISSUES	B. 13-12-00 MDS	ALL DIMENSIONS ARE IN MILLIMETRES UNLESS OTHERWISE STATED	THIS DRAWING IS CONFIDENTIAL AND IS THE PROPERTY OF MEDC AND MUST NOT BE REPRODUCED EITHER WHOLLY OR PARTLY. ALL RIGHTS IN RESPECT OF PATENTS, DESIGNS AND COPYRIGHT ARE RESERVED	DRAWN BY:	DATE:	TITLE		
	C. 13-06-02 PF			M.SELDEN	14/08/00			
	D. 17-04-07 PF	REMOVE ALL BURRS AND SHARP CORNERS		CHECKED BY:	DATE:			
	E. 14-01-15. DW	MACHINE SYMBOLS THUS 		G.HODGKINSON	14/08/00			
				APPROVED BY:	DATE:			
				M.SELDEN	14/08/00			
				SCALE:	SIZE:	DRG No.		ISSUE
				NTS	A 4	188-434		E