

i-on10 - 10 zone control panel



The i-on10 is a Grade 2 control panel with 10 zones on board and feature-packed to deliver you real benefits.

Performance bus allows the fitting of up to 4 keypads. The i-on programming menu is driven for ease and reduces programming issues.

There are a choice of i-on wired keypads to connect to:

- KEY-K01
- KEY-KP01
- i-KP01
- KEY-RKPZ-KIT
- KEY-FKPZ-xx

At a glance...

- Ten zones
- 10 user codes
- Range of keypad options
- Uses same programming menus as the i-on range



Powering Business Worldwide

Product specification

Feature	Description
Compliance	EN50131 PD6662:2017 Grade 2
Zones on board	10
Total number of buses	1
Number of users	10
Number of outputs	1 system plus 12 communicator
Number of part sets	3
Power supply	1A
Battery (maximum capacity)	1 * 7Ah
Size	239mm (h) x 250mm (w) x 90mm (d).
Weight	2.8Kg panel without battery
Temperature range	Environmental class 2 -10°C to 55°C 93% RH

Compatible products

Product Code	Description
Keypads	
KEY-K01	Wired keypad
KEY-KP01	Wired keypad with built-in proximity reader
i-KP01	Wired keypad with large display and built in proximity reader
KEY-RKPZ-KIT	2 way radio keypad with proximity reader
KEY-FKPZ-xx	Flush mount keypad with proximity reader

Note: The additional keypad zones will not be recognised.

Accessories

ADP-10CC	Allows ten 4 wire zones to be used on the panels ten FSL (Fully Supervised Loop) zones
MISC-COMPACT12	Harness to utilise plug by outputs



KEY-K01



KEY-KP01