

Specification

RE Series

Vertical Cable Manager

Part Number

SWCABLETRAY6-42U

General

Dimension (WxDxH)	160mmW*200mmD*622mmH for 1pc
Material (Base)	SPCC, Powder Coating
Material (Cover & Cable Finger)	Plastic
Color	RAL9005 (Black)
Max Static Load Rating	7 Kg
Other	Fully compatible with Open Frame Rack (4-Post)

Structure

Front Cover	Plastic & Solid panel, Easy to assemble/disassemble by push & pull
Cable Finger	Plastic
	Black color
	Multi empty slots for cable entry
	Easy to assemble/disassemble
	Smooth surface
Packing	03pcs per set
Installation	At front & sides of rack

Drawing & Image

Side View



Cable Finger



Vertically Mounting
(2-Post Rack)



Vertically Mounting
(4-Post Rack)

