

## Eaton® ServiceRanger 4 Connection Settings Quick Reference

### Did ServiceRanger connect to your vehicle but no Eaton product was detected?

Before calling the Roadranger Call Center ensure you are using the correct connection setting.

#### 1. Use an approved communication adapter.

Approved Communication Adapters	
<ul style="list-style-type: none"> <li>NEXIQ USB-Link</li> <li>DG Technologies DPA 4 Plus</li> <li>Noregon JPRO DLA+</li> <li>Cummins INLINE 6</li> </ul>	<ul style="list-style-type: none"> <li>- Supports CAN Channel 1, 2, and J1587</li> <li>- Crossover Cable required for CAN Channel 3*</li> </ul>
<ul style="list-style-type: none"> <li>NEXIQ USB-Link 2 and 3</li> <li>DG Technologies DPA 5</li> <li>Noregon JPRO DLA+ 2.0</li> <li>Cummins INLINE 7</li> </ul>	<ul style="list-style-type: none"> <li>- Supports CAN Channel 1, 2, 3 and J1587</li> <li>- Crossover Cable <b>NOT</b> required for CAN Channel 3**</li> </ul>

#### Crossover Cable

- PACCAR Y - Cable (P/N 42-02848)
- NEXIQ CAN 3 - CAN 1 (P/N 406004)

**NOTICE:** An approved communication adapter and USB connection is required to program a TECU or TCM. Do **NOT** use a wireless connection - Bluetooth or WiFi. Failure to use an approved communication adapter and USB connection may result in a damaged TECU or TCM and void component warranty.

#### 2. Add or edit a Profile in ServiceRanger 4 Connection Settings screen.

OEM	Model Year	Crossover Cable	CAN Channel	Connection	Recommended Setting
PACCAR Kenworth Peterbilt	2006 or older †		1	J1587	USB: Protocol = J1708; Speed = 9600
	2007 - 2015		1	J1939	USB: Protocol = J1939; Channel = 1; Speed = Auto
	2016 - late 2018	*Yes	3	J1939	USB: Protocol = J1939; Channel = 1; Speed = Auto
		**No	3	J1939	USB: Protocol = J1939; Channel = 3; Speed = Auto
	late 2018 - present	*Yes	w/ CECU ‡ = 3	J1939	USB: Protocol = J1939; Channel = 1; Speed = Auto
		**No	w/ CECU ‡ = 3	J1939	USB: Protocol = J1939; Channel = 3; Speed = Auto
			w/ VECU ‡ = 1	J1939	USB: Protocol = J1939; Channel = 1; Speed = Auto
Navistar International	2006 or older †		1	J1587	USB: Protocol = J1708; Speed = 9600
	2007 - present		1	J1939	USB: Protocol = J1939; Channel = 1; Speed = Auto
DTNA Freightliner Western Star	2006 or older †		1	J1587	USB: Protocol = J1708; Speed = 9600
	2007 - present		1	J1939	USB: Protocol = J1939; Channel = 1; Speed = Auto
Volvo Mack	2006 or older †		1	J1587	USB: Protocol = J1708; Speed = 9600
	2007 - 2015		1	J1939	USB: Protocol = J1939; Channel = 1; Speed = Auto
	2016 - present	*Yes	3	J1939	USB: Protocol = J1939; Channel = 1; Speed = Auto
		**No	3	J1939	USB: Protocol = J1939; Channel = 3; Speed = Auto
Bluebird	2007 - present		2	J1939	USB: Protocol = J1939; Channel = 2; Speed = Auto

† Gen2 Transmissions only

**Note:** AutoShift Gen1 Transmissions require ServiceRanger 2.80, click [here](#) for more information.

‡ Vehicle equipment, refer to OEM.













