

Eaton's wallbox dimmers, occupancy & vacancy sensors and timers reduce energy usage, improve ambiance and enhance the elegance of a room.

Products available:

Dimmers



AAL06 DAL06P SAL06P TAL06P1 RI061

Occupancy & vacancy sensors



OS106D1 OS310R OS310U OS306U



Minute & hour timers



PT18M PT18H

Colors available:

For ordering devices, include Catalog no. followed by the Color suffix: A (Almond), B (Brown), BK (Black), GY (Gray), LA (Light Almond), V (Ivory), W (White), C1 (Color Change Kit: A, W, V), C2 (Color Change Kit: LA, W, V), C4 (Color Change Kit: BK, W, V), C5 (Color Change Kit: BK, W, GY).



C1 Color kit
A (Almond), W (White), V (Ivory)

C2 Color kit
LA (Light Almond), W (White), V (Ivory)



C4 Color kit
BK (Black), W (White), V (Ivory)



C5 Color kit
BK (Black), W (White), GY (Gray)

For details on where to buy, please contact your local Eaton sales engineer or rep.

Visit our website:
www.Cooperwiringdevices.com

Electrical Sector
203 Cooper Circle
Peachtree City, GA 30269
United States
Eaton.com
Arrowhart.com

Electrical Sector
Canada Operations
5925 McLaughlin Road
Mississauga, Ontario, L5R 1B8
Canada
EatonCanada.ca
Cooperwiringdevices.com

Electrical Sector
Mexico Operations
Carr. Tlalnepantla -
Cuautitlán Km 17.8 s/n
Col. Villa Jardín esq.
Cerrada 8 de Mayo
Cuautitlán, México CP 54800
México
Eaton.mx
Cooperwiringdevices.com

Eaton
1000 Eaton Boulevard
Cleveland, OH 44122
United States
Eaton.com

© 2015 Eaton
All Rights Reserved
Printed in USA
Publication No. PA610001EN
July 2015

Eaton is a registered trademark.
All other trademarks are property of their respective owners.



Eaton's
Lighting controls line card



Lighting control you can count on



Powering Business Worldwide

Lighting controls reference

					Wattages											
	Part No.	Cat. Pg. No.	Trimming	Neutral	INC/HAL	LED / CFL	FLR	ELV	MLV	Wiring configuration	Voltage	Preset	Color / Change kits	Rapid Start	Faceplates	
0-10V dimmers	DF10P-	A-30	High-end	—		120V/1200W 277V/1600W	120V/1200W 277V/1600W			3-way	120V/277V	Yes	C1/C2/C4/C5		DCK1-	
	SF10P-	A-31	High-end	—		120V/1200W 277V/1600W	120V/1200W 277V/1600W			3-way	120V/277V	Yes	A/B/BK/GY/LA/V/W			
Phase-cut dimmers	All Load	AAL06-	A-28	High-end/ Low-end	Yes	600W	300W	600W	600W	600W	Multi-location	120V	Yes	C1/C2/C4/C5	Selectable	
		DAL06P-	A-28	Low-end	—	600W	300W	600W	600W	600W	3-way	120V	Yes	C1/C2/C4/C5	Adjustable	DCK1-
		SAL06P-	A-28	Low-end	—	600W	300W	600W	600W	600W	3-way	120V	Yes	A/BK/GY/LA/V/W	Fixed	
		TAL06P1-	A-28	Low-end	—	600W	300W	600W	600W	600W	3-way	120V	Yes	C1/C2/C4/C5	Adjustable	TCK1-
	Smart	AIM10-	A-29	Low-end	—	1000W				1000W	Multi-location	120V	Yes	A/B/BK/GY/LA/V/W/C1/C2		AMC-__-BP
		AF10-	A-29	Low-end	Yes			1000W			Multi-location	120V	Yes	A/B/BK/GY/LA/V/W/C1/C2		AMC-__-BP
		ARD-	A-29	—	—									A/B/BK/GY/LA/V/W/C1/C2		ARC-__-BP
	Decorator	DI10P-	A-30	Low-end	—	1000W				1000W	3-way	120V	Yes	A/B/BK/GY/LA/V/W		
		DF8AP-	A-30	Low-end	—			1000W			3-way	120V	Yes	A/B/BK/GY/LA/V/W		
		DF8AP7-	A-30	Low-end	—			1000W			3-way	277V	Yes	A/B/BK/GY/LA/V/W		
	Slide	SI061-	A-31	Low-end	—	600W					Single pole	120V		A/B/BK/GY/LA/V/W		
		SI06P	—	Low-end	—	600W				600W	3-way	120V	Yes	B/LA/V/W		
		SI10P-	A-31	Low-end	—	1000W				1000W	3-way	120V	Yes	A/B/BK/GY/LA/V/W		
		SF8AP7-	A-31	Low-end	—			1000W			3-way	277V	Yes	A/B/BK/GY/LA/V/W		
	Toggle	TI061-	A-32	—	—	600W					3-way	120V		A/B/BK/LA/V/W		
		TI061L	A-32	—	—	600W					3-way	120V		N/A (Clear)		
		TI3101-	A-32	—	—	1000W					3-way	120V		A/B/BK/LA/V/W		
		TI3101L	A-32	—	—	1000W					3-way	120V		N/A (Clear)		
	Rotary	RI061-	A-33	—	—	600W					Single pole	120V		A/LA/V/W		RKRD-__-BP
		RI06P-	A-33	—	—	600W					3-way	120V	Yes	A/LA/V/W		RKRD-__-BP
		RI06PL-	A-33	—	—	1000W					3-way	120V	Yes	A/LA/V/W		RKRL-__-BP
		RI101-	A-33	—	—	1000W					3-way	120V		A/LA/V/W		RKRD-__-BP
		RDC15-***	A-33	Low-end	—	300W				300W	Single pole	120V		A/LA/V/W		
		RDC25-***	A-33	Low-end	—	300W				300W	Single pole	120V		A/LA/V/W		
Sensor	OS106D1-	A-38	N/A	Yes	600W				600W	Single pole	120V	Yes	A/BK/GY/LA/V/W		SCKD-__BP	
	VS106D1-	A-38	N/A	Yes	600W				600W	Single pole	120V	Yes	A/BK/GY/LA/V/W		SCKD-__BP	
	OS310R-*	A-39	N/A	Yes	600W	600W	600W	600W	600W	3-way	120V		A/BK/GY/LA/V/W		SCKR-__-BP	
	VS310R-*	A-39	N/A	Yes	600W	600W	600W	600W	600W	3-way	120V		A/BK/GY/LA/W		SCKR-__-BP	
	OS310U-*	A-40	N/A	Yes	1000W	1000W	1000W	1000W	1000W	3-way	120V		A/BK/GY/LA/V/W		SCK1-__-BP	
	VS310U-*	A-40	N/A	Yes	1000W	1000W	1000W	1000W	1000W	3-way	120V		A/BK/GY/LA/W		SCK1-__-BP	
	OS306U-	A-41	N/A	—	600W	600W	600W	600W	600W	3-way	120V		A/BK/GY/LA/V/W		N/A	
	VS306U-	A-41	N/A	—	600W	600W	600W	600W	600W	3-way	120V		A/BK/GY/LA/V/W		N/A	
	Timer	PT18M-**	A-42	N/A	—	1800W/15A	1800W/15A	1800W/15A	1800W/15A	1800W/15A	Single pole	120V		A/B/BK/GY/LA/V/W/C1/C2		PT(1-5)MK-__P
		PT18H-**	A-42	N/A	—	1800W/15A	1800W/15A	1800W/15A	1800W/15A	1800W/15A	Single pole	120V		A/B/BK/GY/LA/V/W/C1/C2		PT(1-5)HK-__P

* Horsepower capable up to 1/6 HP. ** Horsepower capable up to 1/4 HP. *** Combination light/fan control. 1.5A for fan on RDC15 / 2.5A for fan on RDC25.