



Foto je ilustrační

Eaton UTGX712D10PZ32

Jam nut receptacle & hold down clips, without backshell, with 10 male PCB contacts, IP68/69K in unmated conditions, keying Z; UTGX712D10PZ32

General specifications

PRODUCT NAME	Eaton Souriau UTGX series ruggedized connectors for harsh environments
CATALOG NUMBER	UTGX712D10PZ32
PRODUCT LENGTH/DEPTH	24.5 mm
PRODUCT HEIGHT	31.8 mm
PRODUCT WIDTH	31.8 mm
PRODUCT WEIGHT	14 g

Technické údaje produktu

ENVIRONMENTAL CONDITIONS	Flammability rating UL94 V0 REACH RoHS
---------------------------------	--

CONNECTOR ACCESSORY OPTION	No backshell possibility
-----------------------------------	--------------------------

CONNECTOR ORIENTATION	Z
------------------------------	---

CONNECTOR TYPE	Receptacle
-----------------------	------------

CONTACT DELIVERY	Loaded
-------------------------	--------

CONTACT GENDER	Pin (Male)
-----------------------	------------

CONTACT TYPE	PCB
---------------------	-----

COUPLING TYPE	1/3 Bayonet
----------------------	-------------

LAYOUT	D10
---------------	-----

SHELL MATERIAL	Metal & Plastic
-----------------------	-----------------

SHELL SIZE	12
-------------------	----

MATING CYCLES	500
----------------------	-----

OPERATING TEMPERATURE - MAX	105 °C
------------------------------------	--------

OPERATING TEMPERATURE - MIN	-40 °C
------------------------------------	--------

RECEPTACLE TYPE	Jam Nut Receptacle
------------------------	--------------------

NUMBER OF CONTACTS	10
---------------------------	----

NUMBER OF CAVITY #20	10
-----------------------------	----

SALT SPRAY	500 hour
-------------------	----------

Zdroje

3D MODEL

[utgx712d10pz32.stp](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATUM:



Eaton Corporation Plc.

Eaton House
30 Pembroke Road
Dublin 4, Irsko
Eaton.com

© 2025 Eaton. Všechna práva vyhrazena.

Follow us on social media to get the latest product and support information.

