



Eaton FH90

Eaton A200/B100 heater, Used with A200 Starter Sizes 4, 3-Phase Only, A200 Heater, NEMA, Ambient 102-110A, Non-Comp 92-99A, Used with A200 Starter Sizes 4, 3-Phase Only, Type A and B, Thermal and Fast Trip

Allgemeine Spezifikation

PRODUCT NAME	Eaton A200/B100 heater
CATALOG NUMBER	FH90
PRODUCT LENGTH/DEPTH	2.3 in
PRODUCT HEIGHT	1.3 in
PRODUCT WIDTH	1.9 in
PRODUCT WEIGHT	0.07 lb
CERTIFICATIONS	UL Listed CSA Certified
CATALOG NOTES	Select heater coils based on full load current(FLA) shown on motor nameplate. Heater coils are rated to protect 40 degree C rise and a service factor of 1.15, Single-Phase requires 2 heaters, Three-Phase Requires 3 heaters
UPC	786678671147

Produktspezifikationen

SPECIAL FEATURES	Used with A200 Starter Sizes 4, 3-Phase Only
TYPE	A200 Heater
USED WITH	Used with A200 Starter Sizes 4, 3-Phase Only
DESIGN	NEMA
FULL LOAD CURRENT RANGE	Ambient 102-110 A, Non- Comp 92-99 A
OVERLOAD RELAY	Type A and B
TRIP TYPE	Thermal and fast trip

Downloads

INSTALLATIONSANLEITUNG	Instructions for A200, A210, A250 size 6, two- or three-pole non-reversing or reversing motor controllers
	Eaton Specification Sheet - FH90
SPEZIFIKATIONEN	

PROJEKTNAME:

PROJEKTNUMMER:

ERSTELLT VON:

DATUM:



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Irland
Eaton.com

© 2026 Eaton. Alle Rechte vorbehalten.

Folgen Sie uns in den sozialen Netzwerken und erhalten Sie aktuelle Produkt- und Supportinformationen.

