

Specifikationer

Eaton N2SW11211

Eaton Crouse-Hinds series N2S selector switch, Two position, two circuit, Through feed



Generelle specifikationer

PRODUCT NAME	Eaton Crouse-Hinds series N2S selector switch
CATALOG NUMBER	N2SW11211
UPC	782274802909
PRODUCT LENGTH/DEPTH	3.81 in
PRODUCT HEIGHT	8.375 in
PRODUCT WIDTH	6 in
PRODUCT WEIGHT	0.35 lb

Certifications and compliances

AREA CLASSIFICATION Hazardous/Classified Locations

STANDARDS TYPE NEC/CEC

NEC HAZARDOUS RATING Class I, Division 2

NEMA RATING 3
4X
7
12

Product specifications

STYLE Through feed

NORMAL POSITION Two position, two circuit

Ressourcer

CERTIFIKATER [N2S and N2SC Non-metallic Hazardous Area Control Stations UL certification](#)

CERTIFIKATER [N2S and N2SC Non-metallic Hazardous Area Control Stations Canadian certification](#)

INSTALLATIONSVEJLEDNING [IF 1084 - N2PS Pushbutton Assembly, N2SW Selector Switch and N2PL Pilot Lights](#)

KATALOGER [N2S and N2SC Series Non-metallic Control Stations catalog page](#)

SPECIFICATIONS AND DATASHEETS [Eaton Specification Sheet - N2SW11211](#)

PROJEKTNAMN:
PROJEKTNUMMER:
KLARGJORT AF:
DATO:



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Irland
Eaton.com

© 2026 Eaton. Alle rettigheder forbeholdt.

Følg os på de sociale medier for at få
de seneste produkt- og
supportnyheder.

