

Specifikationer



Eaton P034-010

Computer Power Cord, C19 to NEMA 5-15P - Heavy-Duty, 15A, 125V, 14 AWG, 10 ft. (3.05 m), Black

Generelle specifikationer

PRODUCT NAME	Eaton Tripp Lite series power cord
CATALOG NUMBER	P034-010
UPC	037332140920
PRODUCT LENGTH/DEPTH	0.5 in
PRODUCT HEIGHT	12.8 in
PRODUCT WIDTH	8.9 in
PRODUCT WEIGHT	1.1 lb
WARRANTY	Limited lifetime
COMPLIANCES	RoHS
CERTIFICATIONS	cUL Listed UL Listed

Produktspezifikationen

INPUT CURRENT -MAX	15 Ampere
OPERATING TEMPERATURE RANGE	-4° to 140°F (-20° to 60°C)
STORAGE TEMPERATURE	-4° to 140°F (-20° to 60°C)
DEVICE COMPATIBILITY	Server PDU UPS Computer Monitor/HDTV
AWG-SIZE	14
CABLE LENGTH	10 Foot
NUMBER OF CONDUCTORS	3
OPERATING HUMIDITY	10% to 65% RH
OUTER CABLE DIAMETER	9.3mm
POWER CORD JACKET TYPE	SJTW
STORAGE HUMIDITY RANGE	10% to 65% RH
WIRE SIZE (AWG) - MAX	2.08
CABLE LENGTH RANGE	9 - 14ft (2 - 4M)
CABLE JACKET RATING	VW-1
CABLE JACKET COLOR	Black
PACKAGE CONTENTS	P034-010 Computer Power Cable, C19 to 5-15P, 10-ft. (3.05 m), Black
CONNECTOR COLOR	Black
CONNECTOR TYPE	Power
CABLE JACKET MATERIAL	PVC
CONNECTOR STYLE	Straight
PRODUCT HIGHLIGHTS	Heavy-duty computer power cord replaces or upgrades cord provided by manufacturer 10-ft. (3.05 m) length allows great flexibility in placing devices in relationship to AC outlet Lifetime limited warranty (Worldwide) Thick 14 AWG wire gauge manages high power levels required for larger equipment Recommended for powering computers, servers and other network devices
PLUG COLOR	Black

Ressourcen

SIDEA CONNECTOR1	NEMA 5-15P
SIDEB CONNECTOR1	IEC-320-C19
VOLTAGE RATING	125 VAC
CONNECTOR GROUP	C19 5-15P
CONNECTOR	NEMA 5-15P IEC 320-C19

PROJEKTNAMN:

PROJEKTNUMMER:

KLARGJORT AF:

DATO:



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Irland
Eaton.com

© 2026 Eaton. Alle rettigheder forbeholdt.

Følg os på de sociale medier for at få de seneste produkt- og supportnyheder.

