

# Eaton Marauder™ HD Concrete Pumping Hose EHK007



# Part No.	Hose I.D.		Hose O.D.		Max Operating Pressure		Burst Pressure		Minimum Bend Radius		Weight		Length	
	mm	in	mm	in	bar	psi	bar	psi	mm	in	kg/m	lbs/ft	mtr	ft
EHK007-32-100	51,0	2.00	70,0	2.76	85,0	1233	200	2900	275	10.83	3,03	2.04	30,5	100
EHK007-40-100	63,5	2.50	88,0	3.46	85,0	1233	200	2900	300	11.81	4,48	3.01	30,5	100
EHK007-48-100	76,2	3.00	102,0	4.02	85,0	1233	200	2900	350	13.78	5,46	3.67	30,5	100
EHK007-64-100	101,6	4.00	130,0	5.12	85,0	1233	200	2900	400	15.75	8,46	5.69	30,5	100
EHK007-80-100	127,0	5.00	155,0	6.10	85,0	1233	200	2900	500	19.69	9,63	6.47	30,5	100
EHK007-96-100	153,0	6.00	180,0	7.09	85,0	1233	175	2538	650	25.59	10,99	7.39	30,5	100

#### Construction:

**Tube:** Natural and CBR blend

**Reinforcement:** High tensile steel cords

**Cover:** Pin-pricked synthetic rubber

#### Operating Temperature:

-40°C to +70°C  
(-40°F to +158°F)

Meets the requirements of ASME B30.27-2014

#### Application:

- For high pressure concrete pumping
- Heavy duty construction for applications needing long lasting durability

#### Markets:

- Construction
- Cement placement
- \* Boom truck

#### Type of Couplings:

- Victaulic male NPT

Contact coupling manufacturer for attachment procedure and other coupling recommendations

#### Warning

Use of damaged hose or improper use may result in bodily injury or property damage. Please consult Eaton catalog or Technical Support for proper application. Always consult coupling manufacturer for coupling specifications and assembly instructions.



Powering Business Worldwide

Eaton  
Hydraulics Group USA  
14615 Lone Oak Road  
Eden Prairie, MN 55344  
USA  
Tel: 952-937-9800  
Fax: 952-294-7722  
[www.eaton.com/hydraulics](http://www.eaton.com/hydraulics)

Eaton  
Hydraulics Group USA  
1750 Hardeman Lane  
Cleveland, TN 37312  
USA  
Tel: 800-833-3837  
Fax: 952-974-7513

Eaton  
Hydraulics Business Europe  
Route de la Longeraie 7  
1110 Morges  
Switzerland  
Tel: +41 (0) 21 811 4600  
Fax: +41 (0) 21 811 4601