



Eaton FNQ-R-1-1/2

Eaton Bussmann Series Class CC fuse, FNQ, time-delay, dual-element current limiting fuse, 1.5 A, rejection style fuse, interrupting rating of 200kA at 600Vac

Üldised spetsifikatsioonid

PRODUCT NAME	Eaton Bussmann series FNQ-R fuse
CATALOG NUMBER	FNQ-R-1-1/2
EAN	5027590449625
UPC	051712147057
PRODUCT LENGTH/DEPTH	1.5 in
PRODUCT HEIGHT	0.41 in
PRODUCT WIDTH	0.41 in
PRODUCT WEIGHT	0.015 lb
COMPLIANCES	CE Marked

Toote tehnilised andmed		Abiinfo
AMPERAGE RATING	1.5 A	
CLASS	Class CC	
INTERRUPT RATING	200 kAIC	
FUSE INDICATOR	Non-indicating	
CONNECTION	Ferrule end x ferrule end	
RESPONSE TIME	12 sec at 200%	
MATERIAL	Melamine tube	
PACKAGING TYPE	Standard	
VOLTAGE RATING	600 V	
TYPE	Current-limiting high inrush time-delay fuse	
SPECIAL FEATURES	Rejection style	
APPLICATION	Line protection, small control transformers, industrial control, branch circuits	

PROJEKTI NIMI:
PROJEKTI NUMBER:
KOOSTAJA:
KUUPÄEV: