



Eaton RT2SHEO200WLS3HIP

Eaton RoundTech Medium Surface Safety
eFocus HIGHBAY WLS 200 lm MNM 3H IP65

Üldised spetsifikatsioonid

PRODUCT NAME	Eaton RoundTech MSSEO surface emergency luminaire
CATALOG NUMBER	RT2SHEO200WLS3HIP
EAN	3660191822248
PRODUCT LENGTH/DEPTH	138 mm
PRODUCT HEIGHT	48 mm
PRODUCT WIDTH	138 mm
PRODUCT WEIGHT	0.3 kg
CERTIFICATIONS	CE

Hädaolukorra valgustite tehnilised andmed

COLOR HOUSING	White
COLOR TEMPERATURE - MAX	5700 K
COLOR TEMPERATURE - MIN	5700 K
CONDUCTOR CROSS SECTION	2.5
CONNECTION TYPE	Plug-in connection
CONSTANT LIGHT OUTPUT (CLO)	No
ENERGY EFFICIENCY CLASS	A
EXCHANGEABLE CONTROL GEAR	No
FUNCTION	Escape route lighting
IMPACT STRENGTH	IK04
LAMP HOLDER	None
LAMP TYPE	LED not exchangeable
LIGHT DISTRIBUTOR	Focal lens
LUMINAIRE WITH LIMITED SURFACE TEMPERATURE, SIGN D	No
LUMINOUS FLUX IN STANDBY MODE	60 lm
MATERIAL COVER	Without cover
MATERIAL HOUSING	Plastic
MAX. SYSTEM POWER	1.1 W
MONITORING EQUIPMENT	Safety module for monitoring (central feeded system)
MOUNTING METHOD	Ceiling surface mounting
NOMINAL OPERATION TIME - MAX	3 hour
NOMINAL OPERATION TIME - MIN	3 hour
NOMINAL VOLTAGE AC - MAX	230 V
NOMINAL VOLTAGE AC - MIN	230 V
NUMBER OF LIGHTING HEADS	1
NUMBER OF POLES (NUMERIC)	3
OUTER DIAMETER	138 mm
PICTOGRAM INCLUDED	No

Mehaaniliste lisatarvikute spetsifikatsioonid

BATTERY QUALITY	Lithium-ion
COLOR TEMPERATURE - MIN	5700 K
CONDUCTOR CROSS SECTION	2.5
CONNECTION TYPE	Plug-in connection
CONSTANT LIGHT OUTPUT (CLO)	No
DEGREE OF PROTECTION	IP65
ENERGY EFFICIENCY CLASS	A
EXCHANGEABLE CONTROL GEAR	No
FUNCTION	Escape route lighting
IMPACT STRENGTH	IK04
LAMP HOLDER	None
LAMP TYPE	LED not exchangeable
LIGHT DISTRIBUTOR	Focal lens
LUMINOUS FLUX IN STANDBY MODE	60 lm
MATERIAL COVER	Without cover
MONITORING EQUIPMENT	Safety module for monitoring (central feeded system)
MOUNTING METHOD	Ceiling surface mounting
NOMINAL OPERATION TIME - MAX	3 hour
NOMINAL OPERATION TIME - MIN	3 hour
NUMBER OF LIGHTING HEADS	1
OUTER DIAMETER	138 mm
POWER FACTOR	0.61
POWER SUPPLY SYSTEM	Peripheral (individual battery)
RAL-NUMBER (SIMILAR) HOUSING	9003
RATED AMBIENT TEMP ACC. IEC62722-2-1 - MAX	45 °C
RATED AMBIENT TEMP ACC. IEC62722-2-1 - MIN	5 °C
RATED LUMINOUS FLUX ACC. IEC 62722-2-1	200 lm
SUITABLE FOR CONTINUOUS CIRCUIT	No

POWER FACTOR	0.61
POWER SUPPLY SYSTEM	Peripheral (individual battery)
RAL-NUMBER (SIMILAR) HOUSING	9003
RATED AMBIENT TEMP ACC. IEC62722-2-1 - MAX	45 °C
RATED AMBIENT TEMP ACC. IEC62722-2-1 - MIN	5 °C
RATED LUMINOUS FLUX ACC. IEC 62722-2-1	200 lm
SUITABLE FOR CONTINUOUS CIRCUIT	No
SUITABLE FOR STANDBY SWITCHING	No
TYPE OF CONTROL GEAR	LED operating device current-controlled
TYPE OF WIRING	Suitable for through wiring
VOLTAGE TYPE	AC
WITH LIGHT SOURCE	Yes
WITH REMOTE CONTROL	No
WITH REMOTE SWITCH CONNECTION	No

SUITABLE FOR STANDBY SWITCHING	No
MAX. SYSTEM POWER	1.1 W
TYPE OF WIRING	Suitable for through wiring
VOLTAGE TYPE	AC
WITH LIGHT SOURCE	Yes
WITH REMOTE CONTROL	No
WITH REMOTE SWITCH CONNECTION	No

Abiinfo

PROJEKTI NIMI:

PROJEKTI NUMBER:

KOOSTAJA:

KUUPÄEV:



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Iirimaa
Eaton.com

Jälgige meid sotsiaalmeedias, et saada uusimat toote- ja tooteavet.



© 2026 Eaton. Kõik õigused on kaitstud.