

Caratteristiche

Eaton HC9-4R3-R



Eaton HC9 inductor, 4.67 μ H, 13 A Irms, 19.1 A ISAT, 5.9 m Ω resistance, SMT mounting, Iron Powder, 2-pins, 450 qty.

La foto è a scopo illustrativo



Specifiche generali

PRODUCT NAME	Eaton HC9 inductor
CATALOG NUMBER	HC9-4R3-R
UPC	051712824002
PRODUCT LENGTH/DEPTH	0.555 in
PRODUCT HEIGHT	0.295 in
PRODUCT WIDTH	0.516 in
PRODUCT WEIGHT	0.013 lb
COMPLIANCES	RoHS Compliant



Powering Business Worldwide

Caratteristiche prodotto

TYPE	Inductor
MOUNTING	SMT
IRMS	13 A
ISAT	19.1 A
PACKAGE QUANTITY	450
MATERIAL	Iron powder
FREQUENCY RATING	1 kHz to 500 kHz
CONTACT CONFIGURATION	Two-pin
TEMPERATURE RATING	-40 to 155 °C
RESISTANCE	5.9 mΩ
SERIES	HC9

Risorse

NOME DEL PROGETTO:

NUMERO DEL PROGETTO:

PREPARATO DA:

DATA:



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublino 4, Irlanda
Eaton.com

© 2026 Eaton. Tutti i diritti riservati.

Seguici sui social media per avere informazioni aggiornate sui prodotti e sull'assistenza.

