

Specifikacijos



Eaton CSM02479

CSM02479,MATSN-1600/630/4H□-EN

Bendrosios specifikacijos

PRODUCT NAME	Eaton MATSN automatic transfer switch
CATALOG NUMBER	CSM02479
EAN	6954871010979
PRODUCT LENGTH/DEPTH	298.5 m
PRODUCT HEIGHT	730 m
PRODUCT WIDTH	603 m
PRODUCT WEIGHT	90 kg
CERTIFICATIONS	CE



Powering Business Worldwide

Gaminio specifikacijos

Ištekliai

NOMINAL INPUT VOLTAGE	400 V
FREQUENCY RATING	50/60 Hz
INPUT VOLTAGE - MIN	400 V
NOMINAL INPUT CURRENT SHORE	4000 A
TRANSFER TIME SWITCH ON - MIN	75 ms
TRANSFER TIME SWITCH ON - MAX	75 ms
AMBIENT TEMPERATURE - MIN	-20 °C
AMBIENT TEMPERATURE - MAX	55 °C
FITTED WITH:	With LED indication

PROJEKTO PAVADINIMAS:

PROJEKTO NUMERIS:

PARENGĖ:

DATA:



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Airija
Eaton.com

© 2026 „Eaton“. Visos teisės saugomos.

Sekite mus socialiniuose tinkluose,
kur rasite naujausią informaciją apie
gamineis ir jų techninę priežiūrą.

