

Specifications

Eaton SD53-470-R



Eaton SD53 inductor, 47 μ H, 0.64 A Irms, 0.64 A ISAT, 352 m Ω resistance, SMT mounting, Ferrite, 2-pins, 2600 qty.

Photo is representative



General specifications

PRODUCT NAME	Eaton SD53 inductor
CATALOG NUMBER	SD53-470-R
UPC	051712829380
PRODUCT LENGTH/DEPTH	5.2 mm
PRODUCT HEIGHT	3 mm
PRODUCT WIDTH	5.72 mm
PRODUCT WEIGHT	0.24 g
COMPLIANCES	RoHS Compliant

Product specifications

TYPE	Inductor
MOUNTING	SMT
IRMS	0.64 A
ISAT	0.64 A
PACKAGE QUANTITY	2600
MATERIAL	Ferrite
CONTACT CONFIGURATION	Two-pin
TEMPERATURE RATING	-40 to 125 °C
RESISTANCE	352 mΩ
SERIES	SD53

Resources

SPECIFICATIONS AND DATASHEETS

[Eaton SD53 shielded power inductors data sheet](#)

[Eaton Specification Sheet - SD53-470-R](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

