

Especificaciones



La foto es representativa

Eaton E1049-1835ST-R

Eaton Crouse-Hinds series Roughneck E1049 receptacle assembly, Up to 1135A continuous, 313-777 kcmil, Red, Female, Short throw, Rubber, Double hole bus bar, 1000 Vac/dc

Especificaciones generales

PRODUCT NAME	Eaton Crouse-Hinds series Roughneck E1049 receptacle assembly
CATALOG NUMBER	E1049-1835ST-R
UPC	662275919434
PRODUCT LENGTH/DEPTH	10.25 in
PRODUCT HEIGHT	4.25 in
PRODUCT WIDTH	4.25 in
PRODUCT WEIGHT	9.5 lb

Especificaciones del producto

AREA CLASSIFICATION	Ordinary/Non-Hazardous Locations
STANDARDS TYPE	NEC/CEC
NEMA RATING	3
TYPE	Double hole bus bar
AMPERAGE RATING	Up to 1135A Continuous
VOLTAGE RATING	1000 Vac/dc
CABLE SIZE	313-777 kcmil
GENDER	Female
LATCH TYPE	Short throw
MATERIAL	Rubber
COLOR	Red

Recursos

CATÁLOGOS	Roughneck Single Pole High Amperage Plugs and Connectors catalog page
FOLLETOS	Roughneck Single Pole High-amperage Plugs and Connectors brochure
GUÍAS DE ESPECIFICACIONES DE PRODUCTO	Eaton Specification Sheet - E1049-1835ST-R
INSTRUCCIONES DE INSTALACIÓN	IF 1778 - Roughneck E1049 Series Connectors and Receptacles IF 1777 - Roughneck E1049 Series Connectors

NOMBRE DE PROYECTO:

NÚMERO DE PROYECTO:

PREPARADO POR:

FECHA:



Eaton Corporation plc Eaton House
Carretera 30 Pembroke
Dublín 4, Irlanda
Eaton.com

© 2026 Eaton. Todos los derechos reservados.

Síganos en las redes sociales para que conozca la información sobre productos y soporte más reciente.

