

Especificaciones

Eaton PDUNV



Eaton Tripp Lite series basic PDU, 1PH, 1U, C20 input with 5 Adapters, 10 ft cord, 1.9-3.8kW, 16A, 120-240V, 14 Outlets (12) C13 (2) C14

Especificaciones generales

PRODUCT NAME	Eaton Tripp Lite series basic PDU
CATALOG NUMBER	PDUNV
UPC	037332127204
PRODUCT LENGTH/DEPTH	4.25 in
PRODUCT HEIGHT	1.75 in
PRODUCT WIDTH	19 in
PRODUCT WEIGHT	3.2 lb
WARRANTY	5 year limited
COMPLIANCES	CE Marked FCC Class A RoHS TAA Compliant EAC UKCA
CERTIFICATIONS	CSA Std. C22.2 IEC 62368-1 UL 62368-1

Especificaciones del producto

FORM FACTOR	1U
PACKAGE CONTENTS	• PDUNV 1.6/3.8kW Single-Phase 120-240V Basic PDU • (5) C19 plug adapters • Mounting brackets • Owner's manual
OPERATING TEMPERATURE	32° to 104°F (0° to 40°C)
MOUNTING DIRECTION	Horizontal
MATERIAL	Metal
INPUT CONNECTION	NEMA 5-15P; NEMA 5-20P; NEMA L5-20P; NEMA L6-20P; IEC-320 C14; IEC-320 C20
CORD LENGTH	10 ft
AMPERAGE RATING	16A
ELECTRIC CURRENT - MAX	16
PHASE	Single-phase
FREQUENCY RATING	50/60 Hz
NUMBER OF OUTPUTS C13	12
NUMBER OF OUTPUTS C19	2
FEATURES	Flex Center
OUTPUT RECEPTACLES	C13 C19
GROUNDING OPTIONS	Grounding lug
MINIMUM REQUIRED RACK DEPTH	7.8 in
OUTLET SPACING	Distance between Front (C13) outlets = 28.75mm; Distance between Rear (C19) outlets = 55mm; Distance between Rear (C13) outlets = 28.75mm
OVERLOAD PROTECTION	16A circuit breaker
RECOMMENDED ELECTRICAL SERVICE	Single-phase 16/20A 120-240V service
OUTPUT RECEPTACLES DETAILS	Compatible with Eaton Tripp Lite Power Cords
RECEPTACLES	• C13 • C19
INPUT CORD LENGTH	10 ft

Recursos

PRODUCT FEATURES	C20 inlet accepts included C19-C20 cable with included plug adapters NEMA 5-15P; NEMA 5-20P; NEMA L5-20P; NEMA L6-20P; IEC-320 C14; IEC-320 C20
OPERATING ELEVATION	0-10000 ft. (0-3000 m)
OPERATING TEMPERATURE RANGE	32° to 104°F (0° to 40°C)
OUTPUT NOMINAL VOLTAGE	120-240V
RELATIVE HUMIDITY	5% to 95% non-condensing
FORM FACTORS SUPPORTED	1U rackmount, 0U vertical mount, wallmount and under-counter mounting supported
OUTPUT CAPACITY DETAILS	3.84kW (240V), 3.68kW (230V), 3.52kW (220V), 3.33kW (208V), 3.2kW (200V), 2.03kW (127V), 1.92kW (120V) / 16A total capacity; 16A max per C19 outlet; 12A (10A CE) max per C13 outlet
OUTPUT CAPACITY (KW)	1.9-3.8
STORAGE TEMPERATURE	-22° to 122°F (-30° to 50°C)
PRODUCT HIGHLIGHTS	14 total outlets—12 C13 and 2 C19; Compatible with Eaton Tripp Lite power cords to simplify deployment and enhance reliability 5-year limited warranty (Worldwide) Reversible all-metal housing Switchless design prevents accidental shutdown 16A circuit breaker protects against overloads C20 input with 10 ft. (3.1 m) cord and 5 adapters
PDU PLUG TYPE	C14 C20 5-15 5-20 L5-20 6-20
PDU TYPE	Basic
PDU INPUT VOLTAGE	120 208 230

	240
PDU FORM FACTOR	Horizontal (1U)
TOTAL OUTLETS	14
TAA COMPLIANCE	No

NOMBRE DE PROYECTO:
NÚMERO DE PROYECTO:
PREPARADO POR:
FECHA:



Eaton Corporation plc Eaton House
Carretera 30 Pembroke
Dublín 4, Irlanda
Eaton.com

© 2026 Eaton. Todos los derechos reservados.

Síguenos en las redes sociales para que conozca la información sobre productos y soporte más reciente.

