

Specifications



Photo is representative



Eaton BK/S501-2-R

Eaton S501 Series Fast-acting fuse 2A, 250 Vac or less, 32 Vdc (self certified), BK-S501-2-R

General specifications

PRODUCT NAME	Eaton Bussmann series S501 fast-acting fuse
CATALOG NUMBER	BK/S501-2-R
UPC	051712648141
PRODUCT HEIGHT	20 mm
PRODUCT DIAMETER	5.2 mm
PRODUCT WEIGHT	1.06 g
COMPLIANCES	CE Marked RoHS Compliant CCC Marked
CERTIFICATIONS	VDE

Product specifications

AMPERAGE RATING	2 A
FREQUENCY RATING - MAX	50 Hz
FREQUENCY RATING - MIN	50 Hz
VOLTAGE DROP	205 mV typical
INTERRUPT RATING	1.5 kAIC at 250 Vac
FUSE INDICATOR	Non-indicating
CONNECTION	Ferrule end x ferrule end
MATERIAL	Ceramic tube Nickel-plated endcap construction
QUANTITY	100
VOLTAGE RATING	250 Vac or less, 32 Vdc (self certified)
TYPE	Electronic
APPLICATION	Electronic circuits

Resources

SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet - BK/S501-2-R](#)

[Eaton S501 ceramic tube fuses data sheet](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

