

Specifications



Eaton TLP810NET

Protect It! 8-Outlet Surge Protector, 10 ft. Cord, 3240 Joules, Modem/Coax/Ethernet Protection, RJ45

General specifications

PRODUCT NAME	Eaton Tripp Lite series Protect It surge protector
CATALOG NUMBER	TLP810NET
UPC	037332095329
PRODUCT LENGTH/DEPTH	1.51 in
PRODUCT HEIGHT	4.86 in
PRODUCT WIDTH	9.55 in
PRODUCT WEIGHT	2.02 lb
WARRANTY	Limited lifetime
COMPLIANCES	FCC Part 68 RoHS
CERTIFICATIONS	UL 1449 NOM UL Listed cUL Listed CSA Std. C22.2 CSA C22.2.
GLOBAL CATALOG	TLP810NET
PRODUCT TYPE	Surge protector

Product specifications

STORAGE HUMIDITY RANGE	5% to 95% RH
SURGE STYLE	ST - STRIP
SWITCHES	Combination AC circuit breaker and 2-position red illuminated on/off power switch
TELEPHONE/DSL PROTECTION DETAILS	2 line
VOLTAGE COMPATIBILITY (VAC)	120
CIRCUIT BREAKER	15
FREQUENCY RATING	50/60 Hz
AUDIBLE ALARM	Audible alarm sounds to indicate damage to suppression components
DIAGNOSTIC LED DETAILS	Built-in LEDs confirm suppressor "protection present" (green) and "grounded" (red) status
EMI / RFI FILTERING	Up to 40 dB
INPUT PLUG FEATURES	Right Angle (36D)
NETWORK COMPATIBILITY	100 Mbps (Fast Ethernet)
OPERATING TEMPERATURE RANGE	32° to 104°F (0° to 40°C)
PROTECTION MODES	Includes full normal mode (H-N) and common mode (N-G / H-G) line suppression
RECEPTACLE COLOR	GRAY
RECOMMENDED ELECTRICAL SERVICE	120V (110-125V)
SLOT OR HOLE MOUNT MEASUREMENT (CENTER TO CENTER)	Distance between horizontal tabs = 75 mm; Distance between vertical tabs = 41.6 mm
STORAGE TEMPERATURE RANGE	14° to 122°F (-10° to 50°C)
TRANSFORMER ACCOMMODATION	Transformer Accommodation
UL1449 LET THROUGH RATING	330/400/400
INPUT CORD DETAILS	SJT
INPUT CORD GAUGE (AWG)	14
CORD LENGTH	10 Foot
POWER CORD COLOR	Gray

Resources

	Storm Season is Here Again Flyer (English)
	Surge Protectors and Power Strips Brochure
BROCHURES	Surge Protector and Power Strip Specification Brochure (English)
	Telecommunications Certification Addendum (Multi-language)
MANUALS AND USER GUIDES	Owner's Manual for Protect It! Surge (Multi-language)
	Owner's Manual for Protect It! ® Surge Protectors (English)

HOUSING COLOR	Gray
OUTLET ORIENTATION	Single row of 5, plus a second row of 3 for transformer accommodation
OUTLET SAFETY COVERS DETAIL	Includes built-in sliding outlet safety covers
OUTLET SPACING	Distance between standard outlets = 28.5mm; Distance between transformer outlets = 57mm
OUTLETS MEASUREMENT (CENTER TO CENTER)	Distance between standard outlets = 28.5mm; Distance between transformer outlets = 57mm
MATERIAL	Plastic
INPUT PLUG TYPE	NEMA 5-15P
OUTPUT RECEPTACLES	5-15R
PACKAGE CONTENTS	TLP810NET 6 ft. telephone cord 6 ft. network cable Instruction manual with warranty information 6 ft. coax cable
INPUT NOMINAL VOLTAGE	120 VAC 120V AC
PRODUCT FEATURES	Telephone/DSL Protection Outlet Safety Covers Network (Ethernet) Protection Automatic Shut-Off Cable (Coax) Protection Mounting Holes or Slots UL Certified Diagnostic LED(s) Right-Angle Plug
PRODUCT HIGHLIGHTS	2-line modem/fax surge protection 8 outlets / 10 ft. cord \$250,000 Ultimate Lifetime Insurance (U.S., Canada and Puerto Rico only) Ethernet surge protection Lifetime limited warranty (Worldwide) Coaxial surge protection (digital broadband quality accommodates 2.2 GHz bandwidth) 3240 joule rating
PLUG COLOR	White
AC SUPPRESSION JOULE	3240

RATING	
AC SUPPRESSION RESPONSE TIME	< 1 ns
CABLE (COAX) PROTECTION DETAILS	1 line (2.2 GHz Bandwidth)
CORD COLOR	White
CORD GAUGE TYPE	• 14 gauge • SJT
MAXIMUM SURGE AMPS	216000
OPERATING HUMIDITY RANGE	10% to 90% RH
TOTAL OUTLETS	8

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
DATE:



Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

