Fabrikant Manufacturer Hersteller Fabricant Fabricante	Chassis Chassis Chassis Châssis Chasis	Motor Engine Motor Moteur Motor Type	Versn.bak Gearbox Getriebe Boîte d.Vit. Cambio	⌛	Set Kit Kit Kit Kit Ref.	Drukgroep Clutchcover K-Druckplatte Mécanisme Mecanismo Ref.	Type	Friktieplaat Drivenplate K-Scheibe Disque Disco Ref.	∅+N	Type	Druklager Bearing Ausrücker Butée Cojinete Ref.
VOLVO											
F 4..											
F4		TD40A		7501-		**16132.0**	310DS	**13272.0**	12"x1.3/8"x10	VLO	**19809.0**
F406		TD40A		7501-		**16132.0**	310DS	**13272.0**	12"x1.3/8"x10	VLO	**19809.0**
F407		TD40A		7501-		**16132.0**	310DS	**13272.0**	12"x1.3/8"x10	VLO	**19809.0**
F408		TD40A		7501-		**16132.0**	310DS	**13272.0**	12"x1.3/8"x10	VLO	**19809.0**
F 6..											
F6		TD60A/B/C	ZF S5-35	7501-							
	>nr.25238				**60.059**	**16098.0**	14DS	**14190.0**	14"x1.1/2"x10	VLO	**19508.0**
	nr.25238>				**60.056**	**16097.0**	13DS	**13190.0**	13"x1.1/2"x10	VLO	**19506.0**
F6		TD60A/B/C	ZF S6-65	7501-	**60.057**	**16098.0**	14DS	**14293.0**	14"x1.3/4"x10	VLO	**19507.0**
F6S		TD60A/B	R52, R52B	7712-	**60.133**	**16171.0**	GM380	**14258.0**	380x1.3/4"x10	FZO	**19509.0**
F6S		TD60A/B	ZF S6-65	7712-	**60.132**	**16171.0**	GM380	**14258.0**	380x1.3/4"x10	FZO	**19506.0**
F610		TD60A/B/C	ZF S5-35	7501-							
	>nr.25238				**60.059**	**16098.0**	14DS	**14190.0**	14"x1.1/2"x10	VLO	**19508.0**
	nr.25238>				**60.056**	**16097.0**	13DS	**13190.0**	13"x1.1/2"x10	VLO	**19506.0**
F611		TD60A/B/C	ZF S5-35	7501-							
	>nr.25238				**60.059**	**16098.0**	14DS	**14190.0**	14"x1.1/2"x10	VLO	**19508.0**
	nr.25238>				**60.056**	**16097.0**	13DS	**13190.0**	13"x1.1/2"x10	VLO	**19506.0**
F612		TD60A/B/C	ZF S5-35	7501-							
	>nr.25238				**60.059**	**16098.0**	14DS	**14190.0**	14"x1.1/2"x10	VLO	**19508.0**
	nr.25238>				**60.056**	**16097.0**	13DS	**13190.0**	13"x1.1/2"x10	VLO	**19506.0**
F613		TD60A/B/C	ZF S5-35	7501-	**60.059**	**16098.0**	14DS	**14190.0**	14"x1.1/2"x10	VLO	**19508.0**
F614		TD60A/B/C	ZF S6-65	7501-	**60.057**	**16098.0**	14DS	**14293.0**	14"x1.3/4"x10	VLO	**19507.0**
F615		TD60A/B	ZF S6-65	7712-	**60.132**	**16171.0**	GM380	**14258.0**	380x1.3/4"x10	FZO	**19506.0**
F616		TD60A/B	ZF S6-65	7712-	**60.132**	**16171.0**	GM380	**14258.0**	380x1.3/4"x10	FZO	**19506.0**
F617		TD60A/B	ZF S6-65	7712-	**60.132**	**16171.0**	GM380	**14258.0**	380x1.3/4"x10	FZO	**19506.0**
F 7											
F7		TD70	R52	7712-	**68.020**		GB2/350		350x1.3/4"x10	FLO	**19253.0**
F7		TD70	R62	7712-							
	>nr.2163					**16014.0**	G380	**14258.0**	380x1.3/4"x10	FZO	**19509.0**
	nr.2163>				**60.133**	**16171.0**	GM380	**14258.0**	380x1.3/4"x10	FZO	**19509.0**
F7		TD70	R/SR62	7712-	**68.030**		GB2/350		350x2"x10	FZO	**19899.0**
F 10											
F10		TD100	MR62	7701-	**68.050**		GB2/380		350x2"x10	FZO	**19899.0**
F10		TD100	MR62B	7701-	**68.070**		GB2/380		380x2"x10	FZO	**19899.0**

Fabrikant Manufacturer Hersteller Fabricant Fabricante	Chassis Chassis Chassis Châssis Chasis	Motor Engine Motor Moteur Motor Type	Versn.bak Gearbox Getriebe Boîte d.Vit. Cambio	⌛	Set Kit Kit Kit Kit Ref.	Drukgroep Clutchcover K-Druckplatte Mécanisme Mecanismo Ref.	Type	Friktieplaat Drivenplate K-Scheibe Disque Disco Ref.	∅+N	Type	Druklager Bearing Ausrücker Butée Cojinete Ref.
VOLVO											
F10		TD100/101	R/SR62	7701-							
		350mmTWIN			**68.030**		GB2/350		350x2"x10	FZO	**19899.0**
		420mmSINGLE			**70.042**	**17025.0**	GFM420	**14203.0**	420x2"x10	FZO	**19253.0**
F10		TD101/102/103	R/SR 1400/1700	8301-							
		350mmTWIN			**68.170**		GFMZ2/350		350x2"x10	FZO	
		430mmSINGLE			**70.166**	**17087.0**	MFZ430	**14356.0**	430x2"x10	GZO	**19241.0**
F 12											
F12		TD120	MR62B	7701-	**68.070**		GB2/380		380x2"x10	FZO	**19899.0**
F12		TD120	SR62	7701-	**68.050**		GB2/380		350x2"x10	FZO	**19899.0**
F12		TD120	R/SR70/71	7701-	**68.120**		GFT2/380		380x2"x10	FSO	**19899.0**
F12		TD121F/FD	R/SR70/71	7701-							
	>nr.51894				**68.120**		GFT2/380		380x2"x10	FSO	**19899.0**
	nr.51894>				**68.121**		GFT2/380		380x2"x10	FZO	**19899.0**
F12		TD121G/GD	R/SR62/70	7701-	**68.050**		GB2/380		350x2"x10	FZO	**19899.0**
F12		TD121F/FD/GD	R/SR 1400/1700	8301-	**68.190**		GFMZ2/380		380x2"x10	FZO	
F12		TD121G	R/SR 1400/1700	8301-							
	>nr.57099				**68.170**		GFMZ2/350		350x2"x10	FZO	
	nr.57099>				**68.190**		GFMZ2/380		380x2"x10	FZO	
F12		TD122/123	R/SR 1400/1700	8701-							
		380mmTWIN			**68.190**		GFMZ2/380		380x2"x10	FZO	
		430mmSINGLE			**70.168**	**17087.0**	MFZ430	**14448.0**	430x2"x10	DZO	**19241.0**
F 16											
F16		TD162/163	SR2000	8701-							
	>nr.382113				**68.200**		GFMZ2/400		400x2"x10	GZO	
	nr.382113>				**68.250**		GFMZ2/400		400x2"x10	DZO	
F 86											
F86		TD70									
	>32ton			6601-8901		**16014.0**	G380	**14258.0**	380x1.3/4"x10	FZO	**19509.0**
	32ton>					**16802.0**	GB2/350	**14144.0** ⇒	350x1.3/4"x10	FLO	**19506.0**
F/FB 88/89											
F88 / F89 / FB89		T/TD100	MR61	7701-8501	**68.060**		GB2/380		350x1.3/4"x10	FZO	**19899.0**
F88 / F89 / FB89		T/TD100	R/SR61	7701-8501							
		350mmTWIN			**68.041**		GB2/350		350x1.3/4"x10	FZO	**19899.0**
		420mmSINGLE				**17004.0**	G420	**14219.0**	420x1.3/4"x10	FZO	**19253.0**

Fabrikant Manufacturer Hersteller Fabricant Fabricante	Chassis Chassis Chassis Châssis Chasis		Motor Engine Motor Moteur Motor Type	Versn.bak Gearbox Getriebe Boîte d.Vit. Cambio		Set Kit Kit Kit Kit Ref.	Drukgroep Clutchcover K-Druckplatte Mécanisme Mecanismo Ref.	Type	Friktieplaat Drivenplate K-Scheibe Disque Disco Ref.	∅+N	Type	Druklager Bearing Ausrücker Butée Cojinete Ref.
VOLVO												
FE 6												
FE6			TD61F/G	ZF S5-35	8412-	**60.059**	**16098.0**	14DS	**14190.0**	14"x1.1/2"x10	VLO	**19508.0**
FE6			TD61F/G	ZF S6-65	8412-							
			14"K B&B type			**60.057**	**16098.0**	14DS	**14293.0**	14"x1.3/4"x10	VLO	**19507.0**
			380mmK F&S type			**60.132**	**16171.0**	GM380	**14258.0**	380x1.3/4"x10	FZO	**19506.0**
FE6			TD61F/G	R52	8412-	**60.133**	**16171.0**	GM380	**14258.0**	380x1.3/4"x10	FZO	**19509.0**
FE6			TD61F/G	R1000	8412-	**60.132**	**16171.0**	GM380	**14258.0**	380x1.3/4"x10	FZO	**19506.0**
FE 7												
FE7			TD 71/73	R52	8501-							
			F&S type			**70.124**	**17073.0**	GFMZ430	**14316.0**	430x1.3/4"x10	FZO	**19241.0**
			VALEO type			**70.162**	**17084.0**	430DTP	**14342.0**	430x1.3/4"x10	PVO	**19293.0**
FE7			TD 71/73	R1000	8501-							
			F&S type			**70.125**	**17073.0**	GFMZ430	**14317.0**	430x2"x10	FZO	**19241.0**
			VALEO type			**70.163**	**17084.0**	430DTP	**14343.0**	430x2"x10	PVO	**19293.0**
FE Series					**2005-**							
FE 240		7.1	D7E/D7F		0604-							
				ZTO1006		**60.252**		395DBE		395x1.3/4"x10	DLO	
				ZTO1109		**60.252**		395DBE		395x1.3/4"x10	DLO	
FE 280		7.1	D7E		0604-							
				ZTO1006		**60.252**		395DBE		395x1.3/4"x10	DLO	
				ZTO1109		**60.252**		395DBE		395x1.3/4"x10	DLO	
FE 320		7.1	D7E		0604-							
				ZTO1109		**60.252**		395DBE		395x1.3/4"x10	DLO	
FH 12-340												
FH12-340			D12	SR1700 / SR1900	9301-0509							
			380mmTWIN			**68.240**		GFMZ2/380		380x2"x10	DZO	
			430mmSINGLE			**70.165**	**17092.0**	MFZ430	**14448.0**	430x2"x10	DZO	**19241.0**
FH12-340			D12	VT2014 / 2014OD	9801-	**70.264**	**17113.0**	MFZ430	**14415.0**	430x2"x10	DZO	**19560.0**
FH 12-380												
FH12-380			D12	SR1700 / SR1900	9301-0509							
			380mmTWIN			**68.240**		GFMZ2/380		380x2"x10	DZO	
			430mmSINGLE			**70.165**	**17092.0**	MFZ430	**14448.0**	430x2"x10	DZO	**19241.0**
FH12-380			D12D	VT2009B	9801-							
			380mmTWIN			**68.241**		GFMZ2/380		380x50x24	GDZO	
			430mmSINGLE			**70.269**	**17113.0**	MFZ430	**14434.0**	430x50x24	GDZO	**19558.0**

Fabrikant Manufacturer Hersteller Fabricant Fabricante	Chassis Chassis Chassis Châssis Chasis	Motor Engine Motor Moteur Motor Type	Versn.bak Gearbox Getriebe Boîte d.Vit. Cambio	⌛	**Set Kit Kit Kit Kit Ref.**	**Drukgroep Clutchcover K-Druckplatte Mécanisme Mecanismo Ref.**	Type	**Friktieplaat Drivenplate K-Scheibe Disque Disco Ref.**	∅+N	Type	**Druklager Bearing Ausrücker Butée Cojinete Ref.**
VOLVO											
FH12-380		D12D	VT2014 / 2014OD	9801-	**70.264**	**17113.0**	MFZ430	**14415.0**	430x2"x10	DZO	**19560.0**
FH12-380		D12D *400mmTWIN* *430mmSINGLE*	VT/VTO 2214B	9801-	**68.350** **70.266**	**17113.0**	MFZ2/400 MFZ430	**14434.0**	400x50x24 430x50x24	GDZO GDZO	**19560.0**
FH12-380		D12D	VT2412B	9801-	**70.265**	**17113.0**	MFZ430	**14434.0**	430x50x24	GDZO	**19561.0**
FH 12-420											
FH12-420		D12 *380mmTWIN* *430mmSINGLE*	SR1700 / SR1900	9301-9805	**68.240** **70.165**	**17092.0**	GFMZ2/380 MFZ430	**14448.0**	380x2"x10 430x2"x10	DZO DZO	**19241.0**
FH12-420		D12C E II	VT2014	9801-	**68.310**		MFZ2/400		400x2"x10	DZO	
FH12-420		D12D *380mmTWIN* *430mmSINGLE*	VT2009B	9801-	**68.241** **70.269**	**17113.0**	GFMZ2/380 MFZ430	**14434.0**	380x50x24 430x50x24	GDZO GDZO	**19558.0**
FH12-420		D12D *400mmTWIN* *430mmSINGLE*	VT2014 / 2014OD	9801-	**68.310** **70.264**	**17113.0**	MFZ2/400 MFZ430	**14415.0**	400x2"x10 430x2"x10	DZO DZO	**19560.0**
FH12-420		D12D *400mmTWIN* *430mmSINGLE*	VT/VTO 2214B	9801-	**68.350** **70.266**	**17113.0**	MFZ2/400 MFZ430	**14434.0**	400x50x24 430x50x24	GDZO GDZO	**19560.0**
FH12-420		D12D	VT2412B	9801-	**70.265**	**17113.0**	MFZ430	**14434.0**	430x50x24	GDZO	**19561.0**
FH 12-460											
FH12-460		D12C *400mmTWIN* *430mmSINGLE*	VT2014 / 2014OD		**68.310** **70.264**	**17113.0**	MFZ2/400 MFZ430	**14415.0**	400x2"x10 430x2"x10	DZO DZO	**19560.0**
FH12-460		D12C *400mmTWIN* *430mmSINGLE*	VT2514 *F&S type*	9806-	**68.310** **70.268**	**17122.0**	MFZ2/400 MFZ430	**14433.0**	400x2"x10 430x2"x10	DZO GDZO	**19560.0**
FH12-460		D12D *400mmTWIN* *430mmSINGLE*	VT/VTO 2214B	9806-	**68.350** **70.266**	**17113.0**	MFZ2/400 MFZ430	**14434.0**	400x50x24 430x50x24	GDZO GDZO	**19560.0**
FH12-460		D12D	VT2412B	9806-	**70.267**	**17122.0**	MFZ430	**14438.0**	430x50x24	GDZO	**19561.0**
FH12-460		D12D *400mmTWIN* *430mmSINGLE*	VT2514B	9806-	**68.350** **70.301**	**17122.0**	MFZ2/400 MFZ430	**14438.0**	400x50x24 430x50x24	GDZO GDZO	**19560.0**
FH12-460		D12D	VTO2514B	9806-	**68.350**		MFZ2/400		400x50x24	GDZO	

Fabrikant Manufacturer Hersteller Fabricant Fabricante	Chassis Chassis Chassis Châssis Chasis		Motor Engine Motor Moteur Motor Type	Versn.bak Gearbox Getriebe Boîte d.Vit. Cambio		Set Kit Kit Kit Kit Ref.	Drukgroep Clutchcover K-Druckplatte Mécanisme Mecanismo Ref.	Type	Friktieplaat Drivenplate K-Scheibe Disque Disco Ref.	∅+N	Type	Druklager Bearing Ausrücker Butée Cojinete Ref.
VOLVO												
FH 12-500												
FH12-500			D12D	VT2412B	0101-	**70.267**	**17122.0**	MFZ430	**14438.0**	430x50x24	GDZO	**19561.0**
FH12-500			D12D	VT/VTO 2514B	0101-	**68.350**		MFZ2/400		400x50x24	GDZO	
FH 16-470												
FH16-470			D16A		9301-0001							
				SR2000		**68.250**		GFMZ2/400		400x2"x10	DZO	
				SR/SRO 2400		**68.250**		GFMZ2/400		400x2"x10	DZO	
FH16-470			D16B	VT/VTO 2514	9301-0001	**68.310**		GFMZ2/400		400x2"x10	DZO	
FH 16-520												
FH16-520			D16A		9301-0301							
				SR2000		**68.250**		GFMZ2/400		400x2"x10	DZO	
				SR/SRO 2400		**68.250**		GFMZ2/400		400x2"x10	DZO	
FH16-520			D16B	VT/VTO 2514	9301-0301	**68.310**		GFMZ2/400		400x2"x10	DZO	
FH 16-540												
FH 16-540		16.1	D16		0901-	■						
FH 16-550												
FH 16-550		16.1	D16		0301-							
				VT/VTO 2814B		**68.350**		MFZ2/400		400x50x24	GDZO	
				AT2812C		■						
				ATO3112C		■						
FH 16-580												
FH 16-580		16.1	D16		0601-							
				VT/VTO 2814B		**68.410**		MFZ2/400		400x50x24	GDZO	
				AT2812C		■						
				ATO3112C		■						
FH 16-600												
FH 16-600		16.1	D16		0601-	■						
FH 16-610												
FH 16-610		16.1	D16		0301-							
				VT/VTO 2814B		**68.410**		MFZ2/400		400x50x24	GDZO	
				AT2812C		■						
				ATO3112C		■						

Fabrikant Manufacturer Hersteller Fabricant Fabricante	Chassis Chassis Chassis Châssis Chasis	Motor Engine Motor Moteur Motor Type	Versn.bak Gearbox Getriebe Boîte d.Vit. Cambio	⌛	Set Kit Kit Kit Kit Ref.	Drukgroep Clutchcover K-Druckplatte Mécanisme Mecanismo Ref.	Type	Friktieplaat Drivenplate K-Scheibe Disque Disco Ref.	∅+N	Type	Druklager Bearing Ausrücker Butée Cojinete Ref.
VOLVO											
FH 16-660											
FH 16-660		16.1	D16		0601-						
				AT2812C		■			430x50x24		
				ATO3112C		■			430x50x24		
FH 16-700											
FH 16-700		16.1	D16		0901-	■					
FH Series					**2005-**						
FH 400		12.8	D13A/D13B	VT/VTO2214B	0509-						
				400mmTWIN		**68.410** ⌧	✉	MFZ2/400	400x50x24	GDZO	
				430mmSINGLE		**70.301**	**17122.0**	MFZ430	**14438.0** 430x50x24	VDZO	**19560.0**
				AT2412C		**70.314** ⊥	**17130.0**	MF430	**14438.0** 430x50x24	VDZO	**19577.0** <
				AT/ATO2512C		**70.314** ⊥	**17130.0**	MF430	**14438.0** 430x50x24	VDZO	**19577.0** <
FH 420		12.8	D13C		0901-	■					
FH 440		12.8	D13A/D13B	VT/VTO2214B	0509-						
				400mmTWIN		**68.410** ⌧	✉	MFZ2/400	400x50x24	GDZO	
				430mmSINGLE		**70.301**	**17122.0**	MFZ430	**14438.0** 430x50x24	VDZO	**19560.0**
				AT2412C		**70.314** ⊥	**17130.0**	MF430	**14438.0** 430x50x24	VDZO	**19577.0** <
				AT/ATO2512C		**70.314** ⊥	**17130.0**	MF430	**14438.0** 430x50x24	VDZO	**19577.0** <
FH 460		12.8	D13C		0901-	■					
FH 480		12.8	D13A	VT/VTO2514B	0509-						
				400mmTWIN		**68.410** ⌧	✉	MFZ2/400	400x50x24	GDZO	
				430mmSINGLE		**70.301**	**17122.0**	MFZ430	**14438.0** 430x50x24	VDZO	**19560.0**
				AT2412C		**70.314** ⊥	**17130.0**	MF430	**14438.0** 430x50x24	VDZO	**19577.0** <
				AT/ATO2512C		**70.314** ⊥	**17130.0**	MF430	**14438.0** 430x50x24	VDZO	**19577.0** <
FH 500		12.8	D13B/D13C	VT/VTO2514B	0708-						
				400mmTWIN		**68.410** ⌧	✉	MFZ2/400	400x50x24	GDZO	
				430mmSINGLE		**70.301**	**17122.0**	MFZ430	**14438.0** 430x50x24	VDZO	**19560.0**
				AT2412C		**70.314** ⊥	**17130.0**	MF430	**14438.0** 430x50x24	VDZO	**19577.0** <
				AT/ATO2512C		**70.314** ⊥	**17130.0**	MF430	**14438.0** 430x50x24	VDZO	**19577.0** <
FH 520		12.8	D13A	VT/VTO2514B	0509-						
				400mmTWIN		**68.410** ⌧	✉	MFZ2/400	400x50x24	GDZO	
				430mmSINGLE		**70.301**	**17122.0**	MFZ430	**14438.0** 430x50x24	VDZO	**19560.0**
				AT2412C		**70.314** ⊥	**17130.0**	MF430	**14438.0** 430x50x24	VDZO	**19577.0** <
				AT/ATO2512C		**70.314** ⊥	**17130.0**	MF430	**14438.0** 430x50x24	VDZO	**19577.0** <
FH 540		12.8	D13C		0901-	■					

Fabrikant Manufacturer Hersteller Fabricant Fabricante	Chassis Chassis Chassis Châssis Chasis	Motor Engine Motor Moteur Motor Type	Versn.bak Gearbox Getriebe Boîte d.Vit. Cambio	⌛	Set Kit Kit Kit Kit Ref.	Drukgroep Clutchcover K-Druckplatte Mécanisme Mecanismo Ref.	Type	Friktieplaat Drivenplate K-Scheibe Disque Disco Ref.	∅+N	Type	Druklager Bearing Ausrücker Butée Cojinete Ref.
VOLVO											
FLC											
FLC 140				9601-0012							
		B&B type				**16269.0**	310DS		310x1.1/2"x10	VLO	
		F&S type				**16270.0**	MF310	**13293.0**	310x1.1/2"x10	DZ0	
FL 4..											
FL4 / Fl407 / FL408		TD41G		8412-		**16132.0**	310DS	**13272.0**	12"x1.3/8"x10	VLO	**19809.0**
FL 6.. (608 t/m 615)				**-9912**							
	>1920500		s5-35		**60.059**	**16098.0**	14DS	**14190.0**	14"x1.1/2"x10	VLO	**19508.0**
	>1920500				**60.056**	**16097.0**	13DS	**13190.0**	13"x1.1/2"x10	VLO	**19506.0**
	>1920500				**60.057**	**16098.0**	14DS	**14293.0**	14"x1.3/4"x10	VLO	**19507.0**
	>1920500				**60.132**	**16171.0**	GM380	**14258.0**	380x1.3/4"x10	FZO	**19506.0**
	1920501-1920635					**16098.0**	14DS	**14190.0**	14"x1.1/2"x10	VLO	**19507.0**
	1920501-1920635				**60.132**	**16171.0**	GM380	**14258.0**	380x1.3/4"x10	FZO	**19506.0**
	495167>		s5-35		**60.059**	**16098.0**	14DS	**14190.0**	14"x1.1/2"x10	VLO	**19508.0**
	495167>				**60.056**	**16097.0**	13DS	**13190.0**	13"x1.1/2"x10	VLO	**19506.0**
	495167>				**60.057**	**16098.0**	14DS	**14293.0**	14"x1.3/4"x10	VLO	**19507.0**
	495167>				**60.132**	**16171.0**	GM380	**14258.0**	380x1.3/4"x10	FZO	**19506.0**
	>b166079		s5-35		**60.059**	**16098.0**	14DS	**14190.0**	14"x1.1/2"x10	VLO	**19508.0**
	>b166079				**60.056**	**16097.0**	13DS	**13190.0**	13"x1.1/2"x10	VLO	**19506.0**
	>b166079				**60.057**	**16098.0**	14DS	**14293.0**	14"x1.3/4"x10	VLO	**19507.0**
	>b166079				**60.132**	**16171.0**	GM380	**14258.0**	380x1.3/4"x10	FZO	**19506.0**
	b166080-b264999					**16098.0**	14DS	**14190.0**	14"x1.1/2"x10	VLO	**19507.0**
	b166080-b264999				**60.132**	**16171.0**	GM380	**14258.0**	380x1.3/4"x10	FZO	**19506.0**
FL 6.. (616 t/m 626)				**-9912**							
	>1920500		r1100 / s6-36 / t700 / st700		**60.132**	**16171.0**	GM380	**14258.0**	380x1.3/4"x10	FZO	**19506.0**
	>1920500		r52b		**60.133**	**16171.0**	GM380	**14258.0**	380x1.3/4"x10	FZO	**19509.0**
	>1920500				**60.057**	**16098.0**	14DS	**14293.0**	14"x1.3/4"x10	VLO	**19507.0**
	>1920500				**60.132**	**16171.0**	GM380	**14258.0**	380x1.3/4"x10	FZO	**19506.0**
	1920501-1920635					**16098.0**	14DS	**14190.0**	14"x1.1/2"x10	VLO	**19507.0**
	1920501-1920635				**60.132**	**16171.0**	GM380	**14258.0**	380x1.3/4"x10	FZO	**19506.0**
	>434812		r1100 / s6-36 / t700 / st700		**60.132**	**16171.0**	GM380	**14258.0**	380x1.3/4"x10	FZO	**19506.0**
	>434812		r52b		**60.133**	**16171.0**	GM380	**14258.0**	380x1.3/4"x10	FZO	**19509.0**
	434813-495167					**16290.0**	380DS	**13294.0**	380x1.3/4"x10	VLO	
	495167>		r1100 / s6-36 / t700 / st700		**60.132**	**16171.0**	GM380	**14258.0**	380x1.3/4"x10	FZO	**19506.0**
	495167>		r52b		**60.133**	**16171.0**	GM380	**14258.0**	380x1.3/4"x10	FZO	**19509.0**
	495167>				**60.057**	**16098.0**	14DS	**14293.0**	14"x1.3/4"x10	VLO	**19507.0**
	495167>				**60.132**	**16171.0**	GM380	**14258.0**	380x1.3/4"x10	FZO	**19506.0**

Fabrikant Manufacturer Hersteller Fabricant Fabricante	Chassis Chassis Chassis Châssis Chasis	Motor Engine Motor Moteur Motor Type	Versn.bak Gearbox Getriebe Boîte d.Vit. Cambio	⌛	Set Kit Kit Kit Kit Ref.	Drukgroep Clutchcover K-Druckplatte Mécanisme Mecanismo Ref.	Type	Friktieplaat Drivenplate K-Scheibe Disque Disco Ref.	∅+N	Type	Druklager Bearing Ausrücker Butée Cojinete Ref.
VOLVO											
FL 6.. (616 t/m 626) continue				**-9912**							
	>b166079				**60.057**	**16098.0**	14DS	**14293.0**	14"x1.3/4"x10	VLO	**19507.0**
	>b166079				**60.132**	**16171.0**	GM380	**14258.0**	380x1.3/4"x10	FZO	**19506.0**
	b166080-b264999					**16098.0**	14DS	**14190.0**	14"x1.1/2"x10	VLO	**19507.0**
	b166080-b264999				**60.132**	**16171.0**	GM380	**14258.0**	380x1.3/4"x10	FZO	**19506.0**
FL (180 / 205G / 220 / 250)				**0001-**							
	1921636-1921928			0001-		**16291.0**	350DS	**13295.0**	350x1.3/4"x10	VLO	
	1921636-1921928			0001-		**16293.0**	350DS	**13295.0**	350x1.3/4"x10	VLO	
	1921636-1921928			0001-		**16290.0**	380DS	**13294.0**	380x1.3/4"x10	VLO	
	1921636-1921928			0001-		**16292.0**	380DS	**13294.0**	380x1.3/4"x10	VLO	
	2921849-2929187			0001-		**16291.0**	350DS	**13295.0**	350x1.3/4"x10	VLO	
	2921849-2929187			0001-		**16293.0**	350DS	**13295.0**	350x1.3/4"x10	VLO	
	2921849-2929187			0001-		**16290.0**	380DS	**13294.0**	380x1.3/4"x10	VLO	
	2921849-2929187			0001-		**16292.0**	380DS	**13294.0**	380x1.3/4"x10	VLO	
	b265000>			0001-		**16291.0**	350DS	**13295.0**	350x1.3/4"x10	VLO	
	b265000>			0001-		**16293.0**	350DS	**13295.0**	350x1.3/4"x10	VLO	
	b265000>			0001-		**16290.0**	380DS	**13294.0**	380x1.3/4"x10	VLO	
	b265000>			0001-		**16292.0**	380DS	**13294.0**	380x1.3/4"x10	VLO	
	s921941>			0001-		**16291.0**	350DS	**13295.0**	350x1.3/4"x10	VLO	
	s921941>			0001-		**16293.0**	350DS	**13295.0**	350x1.3/4"x10	VLO	
	s921941>			0001-		**16290.0**	380DS	**13294.0**	380x1.3/4"x10	VLO	
	s921941>			0001-		**16292.0**	380DS	**13294.0**	380x1.3/4"x10	VLO	
FL 7											
FL7		TD71	R52B	8401-	**70.124**	**17073.0**	GFMZ430	**14316.0**	430x1.3/4"x10	FZO	**19241.0**
FL7		TD71	R/SR62	8401-	**70.126**	**17073.0**	GFMZ430	**14317.0**	430x2"x10	FZO	**19242.0**
FL7		TD71	R1000								
		400mm F&S type			**60.167**	**16244.0**	MFZ400X	**14371.0**	400x2"x10	FZO	**19241.0**
		430mm F&S type			**70.125**	**17073.0**	GFMZ430	**14317.0**	430x2"x10	FZO	**19241.0**
		430mm VALEO type			**70.163**	**17084.0**	430DTP	**14343.0**	430x2"x10	PVO	**19293.0**
FL7		TD71	SR1400								
		400mm F&S type			**60.167**	**16244.0**	MFZ400X	**14371.0**	400x2"x10	FZO	**19241.0**
		430mm F&S type			**70.125**	**17073.0**	GFMZ430	**14317.0**	430x2"x10	FZO	**19241.0**
		430mm VALEO type			**70.163**	**17084.0**	430DTP	**14343.0**	430x2"x10	PVO	**19293.0**
FL7		TD71	SR1700								
		400mm F&S type			**60.167**	**16244.0**	MFZ400X	**14371.0**	400x2"x10	FZO	**19241.0**
		430mm F&S type			**70.125**	**17073.0**	GFMZ430	**14317.0**	430x2"x10	FZO	**19241.0**
		430mm VALEO type			**70.163**	**17084.0**	430DTP	**14343.0**	430x2"x10	PVO	**19293.0**

Fabrikant Manufacturer Hersteller Fabricant Fabricante	Chassis Chassis Chassis Châssis Chasis	Motor Engine Motor Moteur Motor Type	Versn.bak Gearbox Getriebe Boîte d.Vit. Cambio	⌛	Set Kit Kit Kit Kit Ref.	Drukgroep Clutchcover K-Druckplatte Mécanisme Mecanismo Ref.	Type	Friktieplaat Drivenplate K-Scheibe Disque Disco Ref.	∅+N	Type	Druklager Bearing Ausrücker Butée Cojinete Ref.
VOLVO											
FL7		TD 73	R1000								
		400mm F&S type			**60.167**	**16244.0**	MFZ400X	**14371.0**	400x2"x10	FZO	**19241.0**
		430mm F&S type			**70.125**	**17073.0**	GFMZ430	**14317.0**	430x2"x10	FZO	**19241.0**
		430mm VALEO type			**70.163**	**17084.0**	430DTP	**14343.0**	430x2"x10	PVO	**19293.0**
FL7		TD 73	SR1400/1700								
		400mm F&S type			**60.167**	**16244.0**	MFZ400X	**14371.0**	400x2"x10	FZO	**19241.0**
		430mm F&S type			**70.125**	**17073.0**	GFMZ430	**14317.0**	430x2"x10	FZO	**19241.0**
		430mm VALEO type			**70.163**	**17084.0**	430DTP	**14343.0**	430x2"x10	PVO	**19293.0**
FL 10											
FL10		TD101/102	R/SR62	8401-							
		350mmTWIN			**68.160**		GFMZ2/350		350x2"x10	FZO	
		430mmSINGLE			**70.167**	**17087.0**	MFZ430	**14356.0**	430x2"x10	GZO	**19242.0**
FL10		TD101/102/103	R/SR1400/1700	8401-							
		350mmTWIN			**68.170**		GFMZ2/350		350x2"x10	FZO	
		430mmSINGLE			**70.166**	**17087.0**	MFZ430	**14356.0**	430x2"x10	GZO	**19241.0**
FL 12											
FL12-380		D12A	R/SR 1700/1900								
		380mmTWIN			**68.240**		GFMZ2/380		380x2"x10	DZO	
		430mmSINGLE			**70.165**	**17092.0**	MFZ430	**14448.0**	430x2"x10	DZO	**19241.0**
FL12-420		D12A	R/SR 1700/1900								
		380mmTWIN			**68.240**		GFMZ2/380		380x2"x10	DZO	
		430mmSINGLE			**70.165**	**17092.0**	MFZ430	**14448.0**	430x2"x10	DZO	**19241.0**
FM 7-250											
FM7-250		DC7 E II	R/SR 1400	9806-0509	**70.281**	**17113.0**	MFZ430	**14356.0**	430x2"x10	DZO	**19558.0**
FM7-250		DC7 E II	VT2014	9806-0509	**70.264**	**17113.0**	MFZ430	**14415.0**	430x2"x10	DZO	**19560.0**
FM7-250		DC7 E II	VT2514	9806-0509	**70.264**	**17113.0**	MFZ430	**14415.0**	430x2"x10	DZO	**19560.0**
FM 7-290											
FM7-290		DC7 E II	R/SR 1400	9806-0509	**70.281**	**17113.0**	MFZ430	**14356.0**	430x2"x10	DZO	**19558.0**
FM7-290		DC7 E II	VT2014	9806-0509	**70.264**	**17113.0**	MFZ430	**14415.0**	430x2"x10	DZO	**19560.0**
FM7-290		DC7 E II	VT2514	9806-0509	**70.264**	**17113.0**	MFZ430	**14415.0**	430x2"x10	DZO	**19560.0**
FM 9-260											
FM9-260			VT1708B	0112-0509	**70.270**	**17113.0**	MFZ430	**14441.0**	430x50x24	GDZO	**19558.0**
FM9-260			VT2009B	0112-0509	**70.270**	**17113.0**	MFZ430	**14441.0**	430x50x24	GDZO	**19558.0**
FM9-260			VT2214B	0112-0509	**70.271**	**17113.0**	MFZ430	**14441.0**	430x50x24	GDZO	**19561.0**
FM9-260			VT2412B	0112-0509	**70.271**	**17113.0**	MFZ430	**14441.0**	430x50x24	GDZO	**19561.0**
FM9-260			VTO2214B	0112-0509	**70.271**	**17113.0**	MFZ430	**14441.0**	430x50x24	GDZO	**19561.0**

Fabrikant Manufacturer Hersteller Fabricant Fabricante	Chassis Chassis Chassis Châssis Chasis	Motor Engine Motor Moteur Motor Type	Versn.bak Gearbox Getriebe Boîte d.Vit. Cambio	⌛	**Set Kit Kit Kit Kit Ref.**	**Drukgroep Clutchcover K-Druckplatte Mécanisme Mecanismo Ref.**	Type	**Friktieplaat Drivenplate K-Scheibe Disque Disco Ref.**	∅+N	Type	**Druklager Bearing Ausrücker Butée Cojinete Ref.**
VOLVO											
FM 9-300											
FM9-300			VT1708B	0112-0509	**70.270**	**17113.0**	MFZ430	**14441.0**	430x50x24	GDZO	**19558.0**
FM9-300			VT2009B	0112-0509	**70.270**	**17113.0**	MFZ430	**14441.0**	430x50x24	GDZO	**19558.0**
FM9-300			VT2214B	0112-0509	**70.271**	**17113.0**	MFZ430	**14441.0**	430x50x24	GDZO	**19561.0**
FM9-300			VT2412B	0112-0509	**70.271**	**17113.0**	MFZ430	**14441.0**	430x50x24	GDZO	**19561.0**
FM9-300			VTO2214B	0112-0509	**70.271**	**17113.0**	MFZ430	**14441.0**	430x50x24	GDZO	**19561.0**
FM 9-340											
FM9-340			VT1708B	0112-0509	**70.269**	**17113.0**	MFZ430	**14434.0**	430x50x24	GDZO	**19558.0**
FM9-340			VT2009B	0112-0509	**70.269**	**17113.0**	MFZ430	**14434.0**	430x50x24	GDZO	**19558.0**
FM9-340			VT2214B	0112-0509	**70.265**	**17113.0**	MFZ430	**14434.0**	430x50x24	GDZO	**19561.0**
FM9-340			VTO2214B	0112-0509	**70.265**	**17113.0**	MFZ430	**14434.0**	430x50x24	GDZO	**19561.0**
FM 9-380											
FM9-380			VT1708B	0112-0509	**70.269**	**17113.0**	MFZ430	**14434.0**	430x50x24	GDZO	**19558.0**
FM9-380			VT2009B	0112-0509	**70.269**	**17113.0**	MFZ430	**14434.0**	430x50x24	GDZO	**19558.0**
FM9-380			VT2214B	0112-0509	**70.265**	**17113.0**	MFZ430	**14434.0**	430x50x24	GDZO	**19561.0**
FM9-380			VTO2214B	0112-0509	**70.265**	**17113.0**	MFZ430	**14434.0**	430x50x24	GDZO	**19561.0**
FM 10-320											
FM10-320		D10B E II	R1400	9901-0509	**70.256**	**17113.0**	MFZ430	**14415.0**	430x2"x10	DZO	**19558.0**
FM10-320		D10B E II	SR1400	9901-0509	**70.256**	**17113.0**	MFZ430	**14415.0**	430x2"x10	DZO	**19558.0**
FM10-320		D10B E II	R1700	9901-0509	**70.256**	**17113.0**	MFZ430	**14415.0**	430x2"x10	DZO	**19558.0**
FM10-320		D10B E II	SR1700	9901-0509	**70.256**	**17113.0**	MFZ430	**14415.0**	430x2"x10	DZO	**19558.0**
FM 10-360											
FM10-360		D10B E II	R1400	9901-0509	**70.256**	**17113.0**	MFZ430	**14415.0**	430x2"x10	DZO	**19558.0**
FM10-360		D10B E II	SR1400	9901-0509	**70.256**	**17113.0**	MFZ430	**14415.0**	430x2"x10	DZO	**19558.0**
FM10-360		D10B E II	R1700	9901-0509	**70.256**	**17113.0**	MFZ430	**14415.0**	430x2"x10	DZO	**19558.0**
FM10-360		D10B E II	SR1700	9901-0509	**70.256**	**17113.0**	MFZ430	**14415.0**	430x2"x10	DZO	**19558.0**
FM 12-340											
FM12-340		D12C	R/SR 1700/1900	9801-0509							
		380mmTWIN			**68.240**		GFMZ2/380		380x2"x10	DZO	
		430mmSINGLE			**70.256**	**17113.0**	MFZ430	**14415.0**	430x2"x10	DZO	**19558.0**
FM12-340		D12D	VT2009B	9801-0509							
		380mmTWIN			**68.241**		GFMZ2/380		380x50x24	GDZO	
		430mmSINGLE			**70.269**	**17113.0**	MFZ430	**14434.0**	430x50x24	GDZO	**19558.0**

Fabrikant Manufacturer Hersteller Fabricant Fabricante	Chassis Chassis Chassis Châssis Chasis	Motor Engine Motor Moteur Motor Type	Versn.bak Gearbox Getriebe Boîte d.Vit. Cambio	⌛	Set Kit Kit Kit Kit Ref.	Drukgroep Clutchcover K-Druckplatte Mécanisme Mecanismo Ref.	Type	Friktieplaat Drivenplate K-Scheibe Disque Disco Ref.	∅+N	Type	Druklager Bearing Ausrücker Butée Cojinete Ref.
VOLVO											
FM12-340		D12C	VT2014 / 2014OD	9801-0509							
		400mmTWIN			**68.310**		GFMZ2/400		400x2"x10	DZO	
		430mmSINGLE			**70.264**	**17113.0**	MFZ430	**14415.0**	430x2"x10	DZO	**19560.0**
FM12-340		D12D	VT/VTO 2214B	9801-0509							
		400mmTWIN			**68.350**		MFZ2/400		400x50x24	GDZO	
		430mmSINGLE			**70.266**	**17113.0**	MFZ430	**14434.0**	430x50x24	GDZO	**19560.0**
FM12-340		D12D	VT2412B	9801-0509	**70.265**	**17113.0**	MFZ430	**14434.0**	430x50x24	GDZO	**19561.0**
FM 12-380											
FM12-380		D12C	R/SR 1700/1900	9801-0509							
		380mmTWIN			**68.240**		GFMZ2/380		380x2"x10	DZO	
		430mmSINGLE			**70.256**	**17113.0**	MFZ430	**14415.0**	430x2"x10	DZO	**19558.0**
FM12-380		D12D	VT2009B	9801-0509							
		380mmTWIN			**68.241**		GFMZ2/380		380x50x24	GDZO	
		430mmSINGLE			**70.269**	**17113.0**	MFZ430	**14434.0**	430x50x24	GDZO	**19558.0**
FM12-380		D12C	VT2014 / 2014OD	9801-0509							
		400mmTWIN			**68.310**		GFMZ2/400		400x2"x10	DZO	
		430mmSINGLE			**70.264**	**17113.0**	MFZ430	**14415.0**	430x2"x10	DZO	**19560.0**
FM12-380		D12D	VT/VTO 2214B	9801-0509							
		400mmTWIN			**68.350**		MFZ2/400		400x50x24	GDZO	
		430mmSINGLE			**70.266**	**17113.0**	MFZ430	**14434.0**	430x50x24	GDZO	**19560.0**
FM12-380		D12D	VT2412B	9801-0509	**70.265**	**17113.0**	MFZ430	**14434.0**	430x50x24	GDZO	**19561.0**
FM 12-420											
FM12-420		D12C	R/SR1700/1900	9801-0509							
		380mmTWIN			**68.240**		GFMZ2/380		380x2"x10	DZO	
		430mmSINGLE			**70.256**	**17113.0**	MFZ430	**14415.0**	430x2"x10	DZO	**19558.0**
FM12-420		D12D	VT2009B	9801-0509							
		380mmTWIN			**68.241**		GFMZ2/380		380x50x24	GDZO	
		430mmSINGLE			**70.269**	**17113.0**	MFZ430	**14434.0**	430x50x24	GDZO	**19558.0**
FM12-420		D12C	VT2014 / 2014OD	9801-0509							
		400mmTWIN			**68.310**		GFMZ2/400		400x2"x10	DZO	
		430mmSINGLE			**70.264**	**17113.0**	MFZ430	**14415.0**	430x2"x10	DZO	**19560.0**
FM12-420		D12D	VT/VTO 2214B	9801-0509							
		400mmTWIN			**68.350**		MFZ2/400		400x50x24	GDZO	
		430mmSINGLE			**70.266**	**17113.0**	MFZ430	**14434.0**	430x50x24	GDZO	**19560.0**
FM12-420		D12D	VT2412B	9801-0509	**70.265**	**17113.0**	MFZ430	**14434.0**	430x50x24	GDZO	**19561.0**

Fabrikant Manufacturer Hersteller Fabricant Fabricante	Chassis Chassis Chassis Châssis Chasis		Motor Engine Motor Moteur Motor Type	Versn.bak Gearbox Getriebe Boîte d.Vit. Cambio	⌛	Set Kit Kit Kit Kit Ref.	Drukgroep Clutchcover K-Druckplatte Mécanisme Mecanismo Ref.	Type	Friktieplaat Drivenplate K-Scheibe Disque Disco Ref.	∅+N	Type	Druklager Bearing Ausrücker Butée Cojinete Ref.
VOLVO												
FM 12-460												
FM12-460			D12C	R/SR1700/1900	9801-0509							
			380mmTWIN			**68.240**		✉	GFMZ2/380		380x2"x10	DZO	
			430mmSINGLE			**70.256**	**17113.0**		MFZ430	**14415.0**	430x2"x10	DZO	**19558.0**
FM12-460			D12D	VT2009B	9801-0509							
			380mmTWIN			**68.241**		✉	GFMZ2/380		380x50x24	GDZO	
			430mmSINGLE			**70.269**	**17113.0**		MFZ430	**14434.0**	430x50x24	GDZO	**19558.0**
FM12-460			D12C	VT2014 / 2014OD	9801-0509							
			400mmTWIN			**68.310**		✉	GFMZ2/400		400x2"x10	DZO	
			430mmSINGLE			**70.264**	**17113.0**		MFZ430	**14415.0**	430x2"x10	DZO	**19560.0**
FM12-460			D12D	VT/VTO 2214B	9801-0509							
			400mmTWIN			**68.350**		✉	MFZ2/400		400x50x24	GDZO	
			430mmSINGLE			**70.266**	**17113.0**		MFZ430	**14434.0**	430x50x24	GDZO	**19560.0**
FM12-460			D12D	VT2412B	9801-0509	**70.265**	**17113.0**		MFZ430	**14434.0**	430x50x24	GDZO	**19561.0**
FM Series					**2005-**							
FM 300		9.4	D9B		0509-							
				VT2009B		**70.270**	**17113.0**		MFZ430	**14441.0**	430x50x24	VDZO	**19558.0**
				VT/VTO 2214B			**17113.0**		MFZ430	**14441.0**	430x50x24	VDZO	**19560.0**
				VT/VTO 2514B			**17113.0**		MFZ430	**14441.0**	430x50x24	VDZO	**19560.0**
				AT2412C		**70.313**	⊥ **17129.0**		MF430	**14434.0**	430x50x24	VDZO	**19577.0** <
				AT2512C		**70.313**	⊥ **17129.0**		MF430	**14434.0**	430x50x24	VDZO	**19577.0** <
FM 340		9.4	D9A/D9B		0509-							
				VT2009B		**70.269**	**17113.0**		MFZ430	**14434.0**	430x50x24	VDZO	**19558.0**
				VT/VTO 2214B		**70.266**	**17113.0**		MFZ430	**14434.0**	430x50x24	VDZO	**19560.0**
				VT/VTO 2514B		**70.266**	**17113.0**		MFZ430	**14434.0**	430x50x24	VDZO	**19560.0**
				AT2412C		**70.313**	⊥ **17129.0**		MF430	**14434.0**	430x50x24	VDZO	**19577.0** <
				AT2512C		**70.313**	⊥ **17129.0**		MF430	**14434.0**	430x50x24	VDZO	**19577.0** <
FM 360		12.8	D13A/D13B		0511-							
				VT2009B			**17122.0**		MFZ430	**14438.0**	430x50x24	VDZO	**19558.0**
				VT/VTO 2214B		**70.301**	**17122.0**		MFZ430	**14438.0**	430x50x24	VDZO	**19560.0**
				VT/VTO 2514B		**70.301**	**17122.0**		MFZ430	**14438.0**	430x50x24	VDZO	**19560.0**
				AT2412C		**70.314**	⊥ **17130.0**		MF430	**14438.0**	430x50x24	VDZO	**19577.0** <
				AT/ATO 2512C		**70.314**	⊥ **17130.0**		MF430	**14438.0**	430x50x24	VDZO	**19577.0** <
FM 380		9.4	D9A/D9B		0509-							
				VT2009B		**70.269**	**17113.0**		MFZ430	**14434.0**	430x50x24	GDZO	**19558.0**
				VT/VTO 2214B		**70.266**	**17113.0**		MFZ430	**14434.0**	430x50x24	GDZO	**19560.0**
				VT/VTO 2514B		**70.266**	**17113.0**		MFZ430	**14434.0**	430x50x24	GDZO	**19560.0**
				AT2412C		**70.313**	⊥ **17129.0**		MF430	**14434.0**	430x50x24	GDZO	**19577.0** <
				AT2512C		**70.313**	⊥ **17129.0**		MF430	**14434.0**	430x50x24	GDZO	**19577.0** <

Fabrikant Manufacturer Hersteller Fabricant Fabricante	Chassis Chassis Chassis Châssis Chasis		Motor Engine Motor Moteur Motor Type	Versn.bak Gearbox Getriebe Boîte d.Vit. Cambio	⌛	**Set Kit Kit Kit Kit Ref.**	**Drukgroep Clutchcover K-Druckplatte Mécanisme Mecanismo Ref.**	Type	**Friktieplaat Drivenplate K-Scheibe Disque Disco Ref.**	∅+N	Type	**Druklager Bearing Ausrücker Butée Cojinete Ref.**
VOLVO												
FM 390			D11B		0509-							
				VT/VTO 2214B		**70.301**	**17122.0**	MFZ430	**14438.0**	430x50x24	VDZO	**19560.0**
				VT/VTO 2514B		**70.301**	**17122.0**	MFZ430	**14438.0**	430x50x24	VDZO	**19560.0**
				AT2412C		**70.314** ⊥	**17130.0**	MF430	**14438.0**	430x50x24	VDZO	**19577.0** <
				AT/ATO 2512C		**70.314** ⊥	**17130.0**	MF430	**14438.0**	430x50x24	VDZO	**19577.0** <
FM 400		12.8	D13A/D13B		0509-							
			VT/VTO 2214B - VT/VTO 2514B									
				400mmTWIN		**68.410** ⊠	✉	MFZ2/400		400x50x24	GDZO	
				430mmSINGLE		**70.301**	**17122.0**	MFZ430	**14438.0**	430x50x24	VDZO	**19560.0**
				AT2412C		**70.314** ⊥	**17130.0**	MF430	**14438.0**	430x50x24	VDZO	**19577.0** <
				AT/ATO 2512C		**70.314** ⊥	**17130.0**	MF430	**14438.0**	430x50x24	VDZO	**19577.0** <
FM 430			D11B		0509-							
				VT2009B			**17122.0**	MFZ430	**14438.0**	430x50x24	VDZO	**19558.0**
			VT/VTO 2214B - VT/VTO 2514B									
				400mmTWIN		**68.410** ⊠	✉	MFZ2/400		400x50x24	GDZO	
				430mmSINGLE		**70.301**	**17122.0**	MFZ430	**14438.0**	430x50x24	VDZO	**19560.0**
				AT2412C		**70.314** ⊥	**17130.0**	MF430	**14438.0**	430x50x24	VDZO	**19577.0** <
				AT/ATO 2512C		**70.314** ⊥	**17130.0**	MF430	**14438.0**	430x50x24	VDZO	**19577.0** <
FM 440		12.8	D13A/D13B		0509-							
			VT/VTO 2214B - VT/VTO 2514B									
				400mmTWIN		**68.410** ⊠	✉	MFZ2/400		400x50x24	GDZO	
				430mmSINGLE		**70.301**	**17122.0**	MFZ430	**14438.0**	430x50x24	VDZO	**19560.0**
				AT2412C		**70.314** ⊥	**17130.0**	MF430	**14438.0**	430x50x24	VDZO	**19577.0** <
				AT/ATO 2512C		**70.314** ⊥	**17130.0**	MF430	**14438.0**	430x50x24	VDZO	**19577.0** <
FM 480		12.8	D13A		0509-							
			VT/VTO 2214B - VT/VTO 2514B									
				400mmTWIN		**68.410** ⊠	✉	MFZ2/400		400x50x24	GDZO	
				430mmSINGLE		**70.301**	**17122.0**	MFZ430	**14438.0**	430x50x24	VDZO	**19560.0**
				AT2412C		**70.314** ⊥	**17130.0**	MF430	**14438.0**	430x50x24	VDZO	**19577.0** <
				AT/ATO 2512C		**70.314** ⊥	**17130.0**	MF430	**14438.0**	430x50x24	VDZO	**19577.0** <
FM 500		12.8	D13B/D13C		0709-							
			VT/VTO 2214B - VT/VTO 2514B									
				400mmTWIN		**68.410** ⊠	✉	MFZ2/400		400x50x24	GDZO	
				430mmSINGLE		**70.301**	**17122.0**	MFZ430	**14438.0**	430x50x24	VDZO	**19560.0**
				AT2412C		**70.314** ⊥	**17130.0**	MF430	**14438.0**	430x50x24	VDZO	**19577.0** <
				AT/ATO 2512C		**70.314** ⊥	**17130.0**	MF430	**14438.0**	430x50x24	VDZO	**19577.0** <
FM 520		12.8	D13A		0509-							
			VT/VTO 2214B - VT/VTO 2514B									
				400mmTWIN		**68.410** ⊠	✉	MFZ2/400		400x50x24	GDZO	
				430mmSINGLE		**70.301**	**17122.0**	MFZ430	**14438.0**	430x50x24	VDZO	**19560.0**
				AT2412C		**70.314** ⊥	**17130.0**	MF430	**14438.0**	430x50x24	VDZO	**19577.0** <
				AT/ATO 2512C		**70.314** ⊥	**17130.0**	MF430	**14438.0**	430x50x24	VDZO	**19577.0** <

Fabrikant Manufacturer Hersteller Fabricant Fabricante	Chassis Chassis Chassis Châssis Chasis	Motor Engine Motor Moteur Motor Type	Versn.bak Gearbox Getriebe Boîte d.Vit. Cambio	⌛	Set Kit Kit Kit Kit Ref.	Drukgroep Clutchcover K-Druckplatte Mécanisme Mecanismo Ref.	Type	Friktieplaat Drivenplate K-Scheibe Disque Disco Ref.	∅+N	Type	Druklager Bearing Ausrücker Butée Cojinete Ref.
VOLVO											
FS 7..											
FS7		TD71.73		8501-	**60.167**	**16244.0**	MFZ400X	**14371.0**	400x2"x10	FZO	**19241.0**
FS717		TD73E									
		430mm F&S type			**70.125**	**17073.0**	GFMZ430	**14317.0**	430x2"x10	FZO	**19241.0**
		430mm VALEO type			**70.163**	**17084.0**	430DTP	**14343.0**	430x2"x10	PVO	**19293.0**
FS719		TD73E									
		430mm F&S type			**70.125**	**17073.0**	GFMZ430	**14317.0**	430x2"x10	FZO	**19241.0**
		430mm VALEO type			**70.163**	**17084.0**	430DTP	**14343.0**	430x2"x10	PVO	**19293.0**
G 88											
G88		T/TD100	MR61	7701-8501	**68.060**		GB2/380		350x1.3/4"x10	FZO	**19899.0**
G88		T/TD100	R/SR61	7701-8501		**17004.0**	G420	**14219.0**	420x1.3/4"x10	FZO	**19253.0**
G 89											
G89		T/TD110/120		-7801							
			MR61		**68.060**		GB2/380		350x1.3/4"x10	FZO	**19899.0**
			R/SR61			**17004.0**	G420	**14219.0**	420x1.3/4"x10	FZO	**19253.0**
N 7											
N7		TD70	R51	7301-							
		350mmTWIN			**68.020**		GB2/350		350x1.3/4"x10	FLO	**19253.0**
		380mmSINGLE				**16014.0**	G380	**14258.0**	380x1.3/4"x10	FZO	**19506.0**
N7		TD70	R52/R52B	7301-							
		350mmTWIN			**68.020**		GB2/350		350x1.3/4"x10	FLO	**19253.0**
		380mmSINGLE			**60.133**	**16171.0**	GM380	**14258.0**	380x1.3/4"x10	FZO	**19509.0**
N7		TD70	R/SR62	7301-	**68.030**		GB2/350		350x2"x10	FZO	**19899.0**
N 10											
N10			MR61	7301-8312	**68.060**		GB2/380		350x1.3/4"x10	FZO	**19899.0**
N10			MR62	7301-	**68.050**		GB2/380		350x2"x10	FZO	**19899.0**
N10			MR62B	7301-	**68.070**		GB2/380		380x2"x10	FZO	**19899.0**
N10			R/SR61	7301-8312							
	>nr.49000					**17004.0**	G420	**14219.0**	420x1.3/4"x10	FZO	**19253.0**
	nr.49000>				**68.041**		GB2/350		350x1.3/4"x10	FZO	**19899.0**
N10			R/SR62	7301-							
		350mmTWIN			**68.030**		GB2/350		350x2"x10	FZO	**19899.0**
		420mmSINGLE			**70.042**	**17025.0**	GFM420	**14203.0**	420x2"x10	FZO	**19253.0**
						17103.0	GFM430	**14203.0**	420x2"x10	FZO	**19253.0**

Fabrikant Manufacturer Hersteller Fabricant Fabricante	Chassis Chassis Chassis Châssis Chasis	Motor Engine Motor Moteur Motor Type	Versn.bak Gearbox Getriebe Boîte d.Vit. Cambio	⌛	**Set Kit Kit Kit Kit Ref.**	**Drukgroep Clutchcover K-Druckplatte Mécanisme Mecanismo Ref.**	Type	**Friktieplaat Drivenplate K-Scheibe Disque Disco Ref.**	∅+N	Type	**Druklager Bearing Ausrücker Butée Cojinete Ref.**
VOLVO											
N10			R/SR1400/1700	8301-							
		350mmTWIN			**68.170**		GFMZ2/350		350x2"x10	FZO	
		430mmSINGLE			**70.166**	**17087.0**	MFZ430	**14356.0**	430x2"x10	GZO	**19241.0**
N 12											
N12		TD120	MR/R/SR61	7301-8312	**68.060**		GB2/380		350x1.3/4"x10	FZO	**19899.0**
N12		TD120	MR62B	7301-	**68.070**		GB2/380		380x2"x10	FZO	**19899.0**
N12		TD120	R/SR62	7301-	**68.050**		GB2/380		350x2"x10	FZO	**19899.0**
N12		TD120	R/SR70/71	7301-	**68.050**		GB2/380		350x2"x10	FZO	**19899.0**
N12		TD121F	R/SR70/71	8301-							
	>nr.306000				**68.120**		GFT2/380		380x2"x10	FSO	**19899.0**
	nr.306000>				**68.121**		GFT2/380		380x2"x10	FZO	**19899.0**
N12		TD121F	R/SR1400	8601-	**68.190**		GFMZ2/380		380x2"x10	FZO	
N12		TD121F	R/SR1700	8601-	**68.190**		GFMZ2/380		380x2"x10	FZO	
N12		TD121G	MR62B	7301-	**68.070**		GB2/380		380x2"x10	FZO	**19899.0**
N12		TD121G	R/SR62	7301-	**68.050**		GB2/380		350x2"x10	FZO	**19899.0**
N12		TD121G	R/SR70/71	7301-	**68.050**		GB2/380		350x2"x10	FZO	**19899.0**
N12		TD121G	R/SR1400	8601-	**68.170**		GFMZ2/350		350x2"x10	FZO	
N12		TD121G	R/SR1700	8601-	**68.170**		GFMZ2/350		350x2"x10	FZO	
N12		TD122	R/SR1400	8601-	**68.170**		GFMZ2/350		350x2"x10	FZO	
N12		TD122	R/SR1700	8601-	**68.170**		GFMZ2/350		350x2"x10	FZO	
N 86											
N86		TD70		6601-8901							
	>32ton					**16014.0**	G380	**14258.0**	380x1.3/4"x10	FZO	**19509.0**
	32ton>				**68.020**		GB2/350		350x1.3/4"x10	FLO	**19295.0**
N 88											
N88		T/TD100	R/SR61	7701-8501		**17004.0**	G420	**14219.0**	420x1.3/4"x10	FZO	**19253.0**
NB 88											
NB88		T/TD100	R/SR61	7701-8501		**17004.0**	G420	**14219.0**	420x1.3/4"x10	FZO	**19253.0**
NL 10											
NL10		TD101/102/103	R/SR1400	9101-	**70.166**	**17087.0**	MFZ430	**14356.0**	430x2"x10	GZO	**19241.0**
NL10		TD101/102/103	R/SR1700	9101-	**70.166**	**17087.0**	MFZ430	**14356.0**	430x2"x10	GZO	**19241.0**

Fabrikant Manufacturer Hersteller Fabricant Fabricante	Chassis Chassis Chassis Châssis Chasis	Motor Engine Motor Moteur Motor Type	Versn.bak Gearbox Getriebe Boîte d.Vit. Cambio		Set Kit Kit Kit Kit Ref.	Drukgroep Clutchcover K-Druckplatte Mécanisme Mecanismo Ref. Type	Friktieplaat Drivenplate K-Scheibe Disque Disco Ref. ∅+N Type	Druklager Bearing Ausrücker Butée Cojinete Ref.
VOLVO								
NL 12								
NL12S		TD121G	R/SR1400	9001-				
		350mm TWIN			**68.170**	GFMZ2/350	350x2"x10 FZO	
		380mm TWIN			**68.190**	GFMZ2/380	380x2"x10 FZO	
NL12S		TD121G	R/SR1700	9001-				
		350mm TWIN			**68.170**	GFMZ2/350	350x2"x10 FZO	
		380mm TWIN			**68.190**	GFMZ2/380	380x2"x10 FZO	
NL12S		TD122/123	R/SR1400	9001-	**68.190**	GFMZ2/380	380x2"x10 FZO	
NL12S		TD122/123	R/SR1700	9001-	**68.190**	GFMZ2/380	380x2"x10 FZO	

19234.0 = ● voor/for/für/pour 19509.0
19509.0 = ⌘ binnenmaat/internal diameter/Innenmaß/mesure interne 58mm ; aanslaghoogte/height/höhe/hauteur 80mm
19295.0 = ● voor/for/fü/pour 19506.0 , 19507.0 , 19508.0
19506.0 = ⌘ binnenmaat/internal diameter/Innenmaß/mesure interne 58mm ; aanslaghoogte/height/höhe/hauteur 54mm
19507.0 = ⌘ binnenmaat/internal diameter/Innenmaß/mesure interne 58mm ; aanslaghoogte/height/höhe/hauteur 72mm
19508.0 = ⌘ binnenmaat/internal diameter/Innenmaß/mesure interne 58mm ; aanslaghoogte/height/höhe/hauteur 69mm
19253.0 = ⌘ binnenmaat/internal diameter/Innenmaß/mesure interne 66mm ; aanslaghoogte/height/höhe/hauteur 50mm
19899.0 = ⌘ binnenmaat/internal diameter/Innenmaß/mesure interne 66mm ; aanslaghoogte/height/höhe/hauteur 74mm

Volvo Wear Compensators

Wear compensators fitted to twin plate clutches require setting up after installation. See also our instructionslabels on the EATON Twin plate clutches.
Fig 1. Fitted to PUSH type clutches, this requires to be drifted into contact with the flywheel, there are drillings within the cover to allow a drift or punch to be inserted for this purpose.
Fig 2. Fitted to PULL type clutches, these fit into a machined recess on the side of the pressure plate of the cover, they must be pulled back towards the gearbox side of the slot.


Fig. 1


Fig.2

Failure to set the wear compensators will cause the intermediate plate to move improperly which will cause clutch drag and disengagement problems.

Volvo F10, 12 and 16 with Pull Type Clutches.
Because of increasing problems relating to wear compensators on VOLVO PULL type clutches, we strongly recommend that new blocks and screws are fitted with every replacement clutch.